



Models 6863, 6864
XLR / 1/4" Adapters: F / M, M / M*Model 6863 XLR (F) / 1/4" (M) Adapter**Model 6864 XLR (M) / 1/4" (M) Adapter*

Features

- Sleek light weight design.
- 3 pin XLR to 1/4" stereo.
- Tarnish resistant.

Materials

- XLR body is die cast zinc alloy with tarnish resistant nickel-plating.
- 1/4" plugs are nickel-plated machined brass.
- XLR contacts are nickel-plated brass.

Ordering Information

Model: 6863, 6864.

Specifications

Number of contacts	3 (XLR); Stereo (1/4")
Dielectric strength	1000 V dc

USA: Sales: 800-490-2361

Technical Support: technicalsupport@pomonatest.com

Fax: **425-446-5844**

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): .xx = ± 0.02 " (.51 mm), .xxx = ± 0.005 " (.127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.

Last Update: 10/1/07
D1110825, Rev. 002

Page 1 of 1