

## Thermomagnetic device circuit breaker - TMC 62C 63A - 0902302

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Thermomagnetic circuit breaker, two-pole, 63 A thermal trip. DIN rail mounted and UL 1077-recognized with optional auxiliary contact for either S or H remote signal. Protects wiring and equipment from overcurrent and short circuit faults.

### Key commercial data

|                        |                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------|
| Packing unit           | 1                                                                                                     |
| Minimum order quantity | 36                                                                                                    |
| GTIN                   | <br>4 046356 558143 |
| Custom tariff number   | 85362010                                                                                              |
| Country of origin      | HUNGARY                                                                                               |

### Technical data

|                    |                                        |
|--------------------|----------------------------------------|
| Product type       | Thermomagnetic device circuit breakers |
| Approval           | CSA                                    |
| Approval           | UL Recognized                          |
| Approval           | cUL Recognized                         |
| Approval           | cULus Recognized                       |
| Mounting type      | DIN rail: 35 mm                        |
| Nominal current IN | 63 A                                   |

### Classifications

#### eclass

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27141116 |
| eCl@ss 4.1 | 27141116 |
| eCl@ss 5.0 | 27141116 |
| eCl@ss 5.1 | 27141116 |
| eCl@ss 6.0 | 27141116 |

#### etim

|          |          |
|----------|----------|
| ETIM 3.0 | EC000899 |
| ETIM 4.0 | EC000899 |

#### unspsc

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211812 |
| UNSPSC 7.0901 | 39121411 |
| UNSPSC 11     | 39121411 |
| UNSPSC 12.01  | 39121411 |

## Thermomagnetic device circuit breaker - TMC 62C 63A - 0902302

### Classifications

unspsc

|             |          |
|-------------|----------|
| UNSPSC 13.2 | 39121411 |
|-------------|----------|

### Approvals

#### Certificates

---

#### Certification

CSA / UL Recognized / cUL Recognized / cULus Recognized

---

#### Certification EX

---

#### Certification submitted

---

### Approval details

|     |
|-----|
| CSA |
|-----|

|               |
|---------------|
| UL Recognized |
|---------------|

|                |
|----------------|
| cUL Recognized |
|----------------|

|                  |
|------------------|
| cULus Recognized |
|------------------|

### Accessories

#### Accessories

#### Bridges

Wiring bridge - MPB 18/1- 3 - 2809212



Wiring bridge for modules with connecting pitch 17.5 mm, 1-phase, 3-pos.

---

Thermomagnetic device circuit breaker - TMC 6LOCKOUT - 0902467

Locking element for TMC 6 circuit breakers

---

