

Criteria: Search = 42L2101

Part Number	Suffix	Brand	Stock Model	µF Single	µF Dual	Voltage Rating	Case Diameter	Case Style	Case Height	Product Type	Required Operating Life	Operating Temperature
23M242F200CD1H1		Genteq	Special	2400		200	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
27L533BX	BX	Genteq	Standard	30	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L3333		Genteq	Stock	0.033		2000	0.49	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F9069		Genteq	Special	25		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L667		Genteq	Standard	42	22	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J811F400DF1H1		Genteq	Special	810		400	2	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F8249		Genteq	Standard	10		600	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Y050C370CA		PROLINE	Standard	20	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9086		Genteq	Special	30		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5205		Genteq	Special	35		440	2.5	Round	3.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5050		Genteq	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F7903		Genteq	Standard	2		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F513F050DI1H1		Genteq	Special	51000		50	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
23F163F080DF1H1		Genteq	Special	16000		80	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F9898		Genteq	Standard	60	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9623BX	BX	Genteq	Standard	50		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L55BX	BX	Genteq	Standard	35	20	280	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6809		Genteq	Special	14		280	1.5	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C362F150BI1H1		Genteq	Special	3600		150	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
23F123F150FI1H1		Genteq	Special	12000		150	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
23D303F007BD1H1		Genteq	Special	30000		7.5	1.375	Round	3.125	Electrolytic	1000	-55°C to 85°C
25L6252		Genteq	Standard	7	3	400	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9751		Genteq	Special	20	4	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB650E000T440EA		PROLINE	Standard	65		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A312F150CD1H1		Genteq	Special	3100		150	1.75	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F6674BR	BR	Genteq	Special	12		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9119BX	BX	Genteq	Special	30		440	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M482F250EE1H1		Genteq	Special	4800		250	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB500Y050C370EAB X	BX	PROLINE	Standard	50	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A573F050ED1H1		Genteq	Special	57000		50	2.5	Round	3.125	Electrolytic	1000	-40°C to 85°C
23M801F350CC1H1		Genteq	Special	800		350	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23D253F035CG1H1		Genteq	Special	25000		35	1.75	Round	4.625	Electrolytic	1000	-55°C to 85°C
PB350E000P240DAB X	BX	PROLINE	Standard	35		240	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5816BX	BX	Genteq	Special	25	7.5	370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6960BX	BX	Genteq	Standard	8	2	400	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9989BX	BX	Genteq	Standard	55	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J242F250ED1H1		Genteq	Special	2400		250	2.5	Round	3.125	Electrolytic	2000	-40°C to 105°C
23B292F200DG1H1		Genteq	Special	2900		200	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F9779		Genteq	Standard	40	7.5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L573BX	BX	Genteq	Standard	40	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A163F080BH1H1		Genteq	Special	16000		80	1.375	Round	5.125	Electrolytic	1000	-40°C to 85°C
40L6221		Genteq	Stock	2.2		600	0.64	Oval	2.25	Dry-Axial Leaded	100000	-55°C to 105°C
97F9048BX	BX	Genteq	Special	20	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6660BX	BX	Genteq	Standard	12		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H571F400BG1H1		Genteq	Special	570		400	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C

23F282F200DH1H1		Genteq	Special	2800		200	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F9737BX	BX	Genteq	Standard	35	7.5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B103F075BF1H1		Genteq	Special	10000		75	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F9983BX	BX	Genteq	Standard	30	10	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F402F100BG1H1		Genteq	Special	4000		100	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
23B691F200CB1H1		Genteq	Special	690		200	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
23A123F060BD1H1		Genteq	Special	12000		60	1.375	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F6543BX	BX	Genteq	Special	28		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B333F050CH1H1		Genteq	Special	33000		50	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
23A134F060FH1H1		Genteq	Special	130000		60	3	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F9645		Genteq	Standard	45		440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6759BR	BR	Genteq	Standard	24		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F702F100DE1H1		Genteq	Special	7000		100	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F9613BX	BX	Genteq	Standard	35		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Z050S370CA		PROLINE	Standard	20	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A193F100CI1H1		Genteq	Special	19000		100	1.75	Round	5.625	Electrolytic	1000	-40°C to 85°C
23F182F100BC1H1		Genteq	Special	1800		100	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
27L6013BX	BX	Genteq	Special	5		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L5180		Genteq	Standard	35	10	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9752BX	BX	Genteq	Standard	25	4	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9968		Genteq	Standard	30	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7002		Genteq	Special	14		330	1.75	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23B273F075DG1H1		Genteq	Special	27000		75	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
23B382F100CC1H1		Genteq	Special	3800		100	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F5463		Genteq	Standard	20		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L400		Genteq	Standard	26	9	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8038		Genteq	Standard	30		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M292F200BI1H1		Genteq	Special	2900		200	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
41L7221		Genteq	Stock	2.2		700	0.96	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23C873F075FI1H1		Genteq	Special	87000		75	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB150Y050C440CABX	BX	PROLINE	Standard	15	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C473F050DF1H1		Genteq	Special	47000		50	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
23H371F400CB1H1		Genteq	Special	370		400	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23H470F450BH1H1		Genteq	Special	470		450	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23J402F300EI1H1		Genteq	Special	4000		300	2.5	Round	5.625	Electrolytic	2000	-40°C to 105°C
27L522BX	BX	Genteq	Standard	80	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1027S	S	Genteq	Stock	10		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600Z075T440EABX	BX	PROLINE	Standard	60	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB075E000P370CABX	BX	PROLINE	Standard	7.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B312F250EF1H1		Genteq	Special	3100		250	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F6764BX	BX	Genteq	Standard	5		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9248BX	BX	Genteq	Special	3.75		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C902F150EF1H1		Genteq	Special	9000		150	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9266BX	BX	Genteq	Standard	35		410	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F602F250FJ1H1		Genteq	Special	6000		250	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
PB350E000C440DA		PROLINE	Standard	35		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8252		Genteq	Standard	18		600	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H781F300DB1H1		Genteq	Special	780		300	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23A523F050CH1H1		Genteq	Special	52000		50	1.75	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F6950RR	RR	Genteq	Standard	12	12	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
25L6252BX	BX	Genteq	Standard	7	3	400	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C

23H342F400FH1H1		Genteq	Special	3400		400	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB250Y075C440DA		PROLINE	Standard	25	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F133F075CE1H1		Genteq	Special	13000		75	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
PB150Y075C370CAB X	BX	PROLINE	Standard	15	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5706S	S	Genteq	Stock	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400Z100S370DA		PROLINE	Standard	40	10	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB500E000C440EAB X	BX	PROLINE	Standard	50		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L390BX	BX	Genteq	Standard	40	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9054		Genteq	Special	30	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9048		Genteq	Special	20	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D103F035BE1H1		Genteq	Special	10000		35	1.375	Round	3.625	Electrolytic	1000	-55°C to 85°C
23A143F080BG1H1		Genteq	Special	14000		80	1.375	Round	4.625	Electrolytic	1000	-40°C to 85°C
23C142F200BF1H1		Genteq	Special	1400		200	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
23M382F300EE1H1		Genteq	Special	3800		300	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
27L651BX	BX	Genteq	Standard	80	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9628BX	BX	Genteq	Standard	17.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C122F200BE1H1		Genteq	Special	12100		200	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F8042S	S	Genteq	Stock	50		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F112F200CD1H1		Genteq	Special	1100		200	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
23H701F300BD1H1		Genteq	Special	700		300	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
23B163F075DD1H1		Genteq	Special	16000		75	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
23B463F050EE1H1		Genteq	Special	46000		50	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
23F203F100EI1H1		Genteq	Special	20000		100	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C583F100FJ1H1		Genteq	Special	58000		100	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
PB150E000A370CAB X	BX	PROLINE	Standard	15		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M501F400DB1H1		Genteq	Special	500		400	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23F342F200EF1H1		Genteq	Special	3400		200	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
23B882F150EG1H1		Genteq	Special	8800		150	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F8252BX	BX	Genteq	Standard	18		600	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5001S	S	Genteq	Stock	12.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H442F350FH1H1		Genteq	Special	4400		350	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
23B711F150BB1H1		Genteq	Special	710		150	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
23A213F075DD1H1		Genteq	Special	21000		75	2	Round	3.125	Electrolytic	1000	-40°C to 85°C
23B392F150DE1H1		Genteq	Special	3900		150	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
PB350Z050S440EAS	S	PROLINE	Stock	35	5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C352F250EE1H1		Genteq	Special	3500		250	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
23M162F200DB1H1		Genteq	Special	1600		200	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
41L7201		Genteq	Stock	2		700	0.93	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F5504BX	BX	Genteq	Special	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C123F050BD1H1		Genteq	Special	12000		50	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
23H551F450DD1H1		Genteq	Special	550		450	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9027BX	BX	Genteq	Special	45	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6836S	S	Genteq	Stock	48		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5503		Genteq	Standard	3		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250Y075C440DAB X	BX	PROLINE	Standard	25	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6886RR	RR	Genteq	Standard	27	8	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L539BX	BX	Genteq	Standard	15	11	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H162F200CC1H1		Genteq	Special	1600		200	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23H152F250CD1H1		Genteq	Special	1500		250	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
23B522F150ED1H1		Genteq	Special	5200		150	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
23F163F100EG1H1		Genteq	Special	16000		100	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
23H482F200EE1H1		Genteq	Special	4800		200	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
23J112F250BG1H1		Genteq	Special	1100		250	1.375	Round	4.625	Electrolytic	2000	-40°C to 105°C
23J142F300CF1H1		Genteq	Special	1400		300	1.75	Round	4.125	Electrolytic	2000	-40°C to 105°C
23F403F050DG1H1		Genteq	Special	40000		50	2	Round	4.625	Electrolytic	1000	-55°C to 105°C

PB350E000A370EABX	BX	PROLINE	Standard	35		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB125E000A440DA		PROLINE	Standard	12.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M212F400DI1H1		Genteq	Special	2100		400	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F5474		Genteq	Special	17.5	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9643BX	BX	Genteq	Standard	40		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8294BX	BX	Genteq	Standard	60		330	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M212F300CF1H1		Genteq	Special	2100		300	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
23B721F200BD1H1		Genteq	Special	720		200	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F8066S	S	Genteq	Stock	35		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8061S	S	Genteq	Stock	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9265		Genteq	Standard	25		410	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Z075S440DABX	BX	PROLINE	Standard	30	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J152F350EE1H1		Genteq	Special	1500		350	2.5	Round	3.625	Electrolytic	2000	-40°C to 105°C
97F6761BR	BR	Genteq	Standard	17.5		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9805		Genteq	Standard	45		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D622F055BE1H1		Genteq	Special	6200		55	1.375	Round	3.625	Electrolytic	1000	-55°C to 85°C
23B162F200BI1H1		Genteq	Special	1600		200	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
23A673F050DH1H1		Genteq	Special	67000		50	2	Round	5.125	Electrolytic	1000	-40°C to 85°C
23F402F250EI1H1		Genteq	Special	4000		250	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
PB150Y075C440CA		PROLINE	Standard	15	7.5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB125E000P440CAS	S	PROLINE	Stock	12.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100Y100C370BABX	BX	PROLINE	Standard	10	10	370	1.75	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J262F350FF1H1		Genteq	Special	2600		350	3	Round	4.125	Electrolytic	2000	-40°C to 105°C
PB550Z075T370DA		PROLINE	Standard	55	7.5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M501F450BG1H1		Genteq	Special	500		450	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
23C293F075DG1H1		Genteq	Special	29000		75	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
23B583F060EG1H1		Genteq	Special	58000		60	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
23F192F200CG1H1		Genteq	Special	1900		200	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
23M541F450CD1H1		Genteq	Special	540		450	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
23J232F300EE1H1		Genteq	Special	2300		300	2.5	Round	3.625	Electrolytic	2000	-40°C to 105°C
PB250Z100S440DABX	BX	PROLINE	Standard	25	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A144F075FL1H1		Genteq	Special	140000		75	3	Round	8.625	Electrolytic	1000	-40°C to 85°C
97F5491BX	BX	Genteq	Special	30	4	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B503F075EH1H1		Genteq	Special	50000		75	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F9602BX	BX	Genteq	Standard	20		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L573		Genteq	Standard	40	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C343F100EH1H1		Genteq	Special	34000		100	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F6788		Genteq	Standard	2.5		330	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A143F050CB1H1		Genteq	Special	14000		50	1.75	Round	2.125	Electrolytic	1000	-40°C to 85°C
23M322F350FD1H1		Genteq	Special	3200		350	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9613S	S	Genteq	Stock	35		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F342F250FE1H1		Genteq	Special	3400		250	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
23A323F075CH1H1		Genteq	Special	32000		75	1.75	Round	5.125	Electrolytic	1000	-40°C to 85°C
23C482F200DI1H1		Genteq	Special	4800		200	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB040E000P370CABX	BX	PROLINE	Standard	4		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A153F060BE1H1		Genteq	Special	15000		60	1.375	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F8051		Genteq	Standard	95		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H102F400DF1H1		Genteq	Special	1000		400	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F6872		Genteq	Standard	48		280	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6510		Genteq	Special	50		260	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B352F075BB1H1		Genteq	Special	3500		75	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
23B112F250BH1H1		Genteq	Special	1100		250	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C

23F232F100FG1H1		Genteq	Special	23000		100	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
23H961F250DB1H1		Genteq	Special	960		250	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23A104F080FI1H1		Genteq	Special	100000		80	3	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F9020		Genteq	Special	25	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6919BR	BR	Genteq	Standard	16		540	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B383F050DG1H1		Genteq	Special	38000		50	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F9644		Genteq	Standard	45		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1022S	S	Genteq	Stock	3		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B363F080EG1H1		Genteq	Special	36000		80	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
27L388BX	BX	Genteq	Special	60		440	2	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L946		Genteq	Standard	40	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L850BX	BX	Genteq	Standard	11.5	7	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F173F075DE1H1		Genteq	Special	17000		75	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F9993BX	BX	Genteq	Standard	25	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B811F250BF1H1		Genteq	Special	810		250	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
23J122F400DI1H1		Genteq	Special	1200		400	2	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F9337BX	BX	Genteq	Standard	55		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H371F350BC1H1		Genteq	Special	370		350	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
23M432F300EF1H1		Genteq	Special	4300		300	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
27L562		Genteq	Special	45	19	330	1.75	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6694BR	BR	Genteq	Special	20		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5461		Genteq	Special	15		370	1.75	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9881		Genteq	Standard	35	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9046BX	BX	Genteq	Special	15	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M581F450BH1H1		Genteq	Special	580		450	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23A863F075FG1H1		Genteq	Special	86000		75	3	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F8068		Genteq	Standard	45		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C583F075FF1H1		Genteq	Special	58000		75	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F5103BX	BX	Genteq	Special	30		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C783F075FH1H1		Genteq	Special	78000		75	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F9673		Genteq	Standard	20	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A332F150BH1H1		Genteq	Special	3300		150	1.375	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F5814BX	BX	Genteq	Special	25	5	370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J582F300FI1H1		Genteq	Special	5800		300	3	Round	5.625	Electrolytic	2000	-40°C to 105°C
23D104F007CH1H1		Genteq	Special	100000		7.5	1.75	Round	5.125	Electrolytic	1000	-55°C to 85°C
97F9073BX	BX	Genteq	Special	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L633		Genteq	Standard	70	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9838BX	BX	Genteq	Standard	40	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C203F050BG1H1		Genteq	Special	20000		50	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F9081		Genteq	Special	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C393F060DF1H1		Genteq	Special	39000		60	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9995		Genteq	Standard	30	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H252F450FH1H1		Genteq	Special	2500		450	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB450E000P370EA		PROLINE	Standard	45		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F142F200CE1H1		Genteq	Special	1400		200	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
23C144F050FI1H1		Genteq	Special	140000		50	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
27L1025S	S	Genteq	Stock	6		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB500E000S440FABX	BX	PROLINE	Standard	50		440	2	Round	5.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A353F075CI1H1		Genteq	Special	35000		75	1.75	Round	5.625	Electrolytic	1000	-40°C to 85°C
23A273F075DE1H1		Genteq	Special	27000		75	2	Round	3.625	Electrolytic	1000	-40°C to 85°C

27L1020BX	BX	Genteq	Standard	2		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H222F400FE1H1		Genteq	Special	2200		400	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB400Y050C370DABX	BX	PROLINE	Standard	40	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L1027BX	BX	Genteq	Standard	10		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J122F350ED1H1		Genteq	Special	1200		350	2.5	Round	3.125	Electrolytic	2000	-40°C to 105°C
97F6881BR	BR	Genteq	Standard	42	14	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M992F300F1H1		Genteq	Special	9900		300	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F733F075FJ1H1		Genteq	Special	73000		75	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
97F9207		Genteq	Standard	25		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C492F150DE1H1		Genteq	Special	4900		150	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
23A113F080CC1H1		Genteq	Special	11000		80	1.75	Round	2.625	Electrolytic	1000	-40°C to 85°C
23C213F060CD1H1		Genteq	Special	21000		60	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F6882RC	RC	Genteq	Standard	24	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
41L7501		Genteq	Stock	5		700	1.2	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
23C883F050EH1H1		Genteq	Special	88000		50	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
23M592F200DH1H1		Genteq	Special	5900		200	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9494		Genteq	Standard	35	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J692F250FH1H1		Genteq	Special	6900		250	3	Round	5.125	Electrolytic	2000	-40°C to 105°C
23C222F250CG1H1		Genteq	Special	2200		250	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F8059BX	BX	Genteq	Standard	10		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H641F200BB1H1		Genteq	Special	640		200	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
23H122F400DG1H1		Genteq	Special	1200		400	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F8258BX	BX	Genteq	Standard	45		600	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C832F080BE1H1		Genteq	Special	8300		80	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
23C602F250EI1H1		Genteq	Special	6000		250	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
23H291F450DB1H1		Genteq	Special	290		450	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23B612F250FH1H1		Genteq	Special	6100		250	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
23B103F150EH1H1		Genteq	Special	10000		150	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
23D363F016BI1H1		Genteq	Special	36000		16	1.375	Round	5.625	Electrolytic	1000	-55°C to 85°C
23F183F050CD1H1		Genteq	Special	18000		50	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
PB200Y075C440DA		PROLINE	Standard	20	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5241		Genteq	Standard	65		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8076BX	BX	Genteq	Special	50		480	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M142F450EE1H1		Genteq	Special	1400		450	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F9864		Genteq	Standard	35	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D153F055CG1H1		Genteq	Special	15000		55	1.75	Round	4.625	Electrolytic	1000	-55°C to 85°C
97F6769		Genteq	Standard	16		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A383F080DH1H1		Genteq	Special	38000		80	2	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F8082BX	BX	Genteq	Special	30		480	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F303F060EE1H1		Genteq	Special	30000		60	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
23M801F350BF1H1		Genteq	Special	800		350	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
PB600Z050T370DABX	BX	PROLINE	Standard	60	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C172F150BD1H1		Genteq	Special	1700		150	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
23D932F055CD1H1		Genteq	Special	9300		55	1.75	Round	3.125	Electrolytic	1000	-55°C to 85°C
23M601F300BC1H1		Genteq	Special	600		300	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
27L443BR	BR	Genteq	Standard	17	7	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L53		Genteq	Standard	26	15	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450Y075D440EA		PROLINE	Standard	45	7.5	440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J361F350BD1H1		Genteq	Special	360		350	1.375	Round	3.125	Electrolytic	2000	-40°C to 105°C
23H741F400DD1H1		Genteq	Special	740		400	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23A124F050FF1H1		Genteq	Special	120000		50	3	Round	4.125	Electrolytic	1000	-40°C to 85°C
27L413		Genteq	Standard	35	16	300	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB100E000A440CABX	BX	PROLINE	Standard	10		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M382F250ED1H1		Genteq	Special	3800		250	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C

PB200Y100C440DA		PROLINE	Standard	20	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J362F300EH1H1		Genteq	Special	3600		300	2.5	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F9998		Genteq	Standard	15	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400E000S440EABX	BX	PROLINE	Standard	40		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9858BX	BX	Genteq	Standard	50	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J561F250BC1H1		Genteq	Special	560		250	1.375	Round	2.625	Electrolytic	2000	-40°C to 105°C
PB200E000A440EABX	BX	PROLINE	Standard	20		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H352F450FL1H1		Genteq	Special	3500		450	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
97F5043BX	BX	Genteq	Special	10		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M442F200DF1H1		Genteq	Special	4400		200	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F5541		Genteq	Special	45	7.5	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6690BX	BX	Genteq	Special	36	12	260	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB300Y075C370DABX	BX	PROLINE	Standard	30	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H142F300BI1H1		Genteq	Special	1400		300	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9036		Genteq	Standard	7.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B541F200BC1H1		Genteq	Special	540		200	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
23C353F050DD1H1		Genteq	Special	35000		50	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F6883BX	BX	Genteq	Standard	36	20	280	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J262F250CI1H1		Genteq	Special	2600		250	1.75	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F9501		Genteq	Standard	2.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8264		Genteq	Standard	45		600	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F353F050CH1H1		Genteq	Special	35000		50	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
PB350Z050S370DABX	BX	PROLINE	Standard	35	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F103F075DC1H1		Genteq	Special	10000		75	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F9681		Genteq	Standard	30	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6890RR	RR	Genteq	Standard	18	10	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A252F150BF1H1		Genteq	Special	2500		150	1.375	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9009		Genteq	Standard	50		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L497BX	BX	Genteq	Standard	80		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B132F250DD1H1		Genteq	Special	1300		250	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
23A103F080DB1H1		Genteq	Special	10000		80	2	Round	2.125	Electrolytic	1000	-40°C to 85°C
97F8020BX	BX	Genteq	Special	54		440	2.5	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L827BX	BX	Genteq	Standard	18	10	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
40L6151		Genteq	Stock	1.5		600	0.73	Oval	1.5	Dry-Axial Leaded	100000	-55°C to 105°C
23B273F100FG1H1		Genteq	Special	27000		100	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
23B862F100CG1H1		Genteq	Special	8600		100	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
23C901F200CB1H1		Genteq	Special	900		200	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
23D143F016BC1H1		Genteq	Special	14000		16	1.375	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F5818		Genteq	Special	25	10	370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9609BX	BX	Genteq	Standard	30		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H652F250EI1H1		Genteq	Special	6500		250	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23M672F200DI1H1		Genteq	Special	6700		200	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
27L709BX	BX	Genteq	Standard	26		400	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A553F080EG1H1		Genteq	Special	55000		80	2.5	Round	4.625	Electrolytic	1000	-40°C to 85°C
27L539		Genteq	Standard	15	11	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M142F250BF1H1		Genteq	Special	1400		250	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
27L954		Genteq	Standard	60	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H172F400EF1H1		Genteq	Special	1700		400	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
23F242F200CI1H1		Genteq	Special	2400		200	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
23F142F250DE1H1		Genteq	Special	1400		250	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F9593		Genteq	Standard	50	10	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H911F250CB1H1		Genteq	Special	910		250	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C

97F6766RC	RC	Genteq	Standard	7		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB100Y100C370BA		PROLINE	Standard	10	10	370	1.75	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F123F100EE1H1		Genteq	Special	12000		100	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
23J412F250EG1H1		Genteq	Special	4100		250	2.5	Round	4.625	Electrolytic	2000	-40°C to 105°C
23A143F150FF1H1		Genteq	Special	14000		150	3	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F8073BX	BX	Genteq	Standard	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C183F100DG1H1		Genteq	Special	18000		100	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
23B173F050CD1H1		Genteq	Special	17000		50	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
27L1023S	S	Genteq	Stock	4		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6763S	S	Genteq	Stock	10		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L589		Genteq	Standard	10	5	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9318		Genteq	Special	55	5	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C563F100FI1H1		Genteq	Special	56000		100	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
27L877S	S	Genteq	Stock	30	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C733F080FH1H1		Genteq	Special	73000		80	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F6694RC	RC	Genteq	Special	20		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5067		Genteq	Standard	12.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8057S	S	Genteq	Stock	6		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6766BX	BX	Genteq	Standard	7		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A163F100DF1H1		Genteq	Special	16000		100	2	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9833BX	BX	Genteq	Standard	30	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9006		Genteq	Standard	25		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8067S	S	Genteq	Stock	40		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8077BX	BX	Genteq	Special	5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB500Z100S370EA		PROLINE	Standard	50	10	370	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F172F250CH1H1		Genteq	Special	1700		250	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F5541BX	BX	Genteq	Special	45	7.5	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L954BX	BX	Genteq	Standard	60	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L427BX	BX	Genteq	Standard	15	10	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M133F250FJ1H1		Genteq	Special	13000		250	3	Round	5.875	Electrolytic	2000	-40°C to 85°C
PB040E000A370AABX	BX	PROLINE	Standard	4		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9265BX	BX	Genteq	Standard	25		410	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B692F080BE1H1		Genteq	Special	6900		80	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
23M832F350FL1H1		Genteq	Special	8300		350	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
23F112F250CE1H1		Genteq	Special	1100		250	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F6514BX	BX	Genteq	Special	20		170	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M282F450FG1H1		Genteq	Special	2800		450	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J711F250BD1H1		Genteq	Special	710		250	1.375	Round	3.125	Electrolytic	2000	-40°C to 105°C
PB125E000P440CA		PROLINE	Standard	12.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L1052		Genteq	Standard	55		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A583F050CI1H1		Genteq	Special	58000		50	1.75	Round	5.625	Electrolytic	1000	-40°C to 85°C
23D553F007CD1H1		Genteq	Special	55000		7.5	1.75	Round	3.125	Electrolytic	1000	-55°C to 85°C
97F6753		Genteq	Special	7		330	1.5	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M142F250CC1H1		Genteq	Special	1400		250	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23A612F150CH1H1		Genteq	Special	6100		150	1.75	Round	5.125	Electrolytic	1000	-40°C to 85°C
27L176BX	BX	Genteq	Special	7.5		540	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A593F075EG1H1		Genteq	Special	59000		75	2.5	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F9843		Genteq	Standard	40	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8060BX	BX	Genteq	Standard	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6783		Genteq	Special	25		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

27L961		Genteq	Standard	25		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H702F200FE1H1		Genteq	Special	7000		200	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB500E000S370DA		PROLINE	Standard	50		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F143F050CC1H1		Genteq	Special	14000		50	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
23A193F100DG1H1		Genteq	Special	19000		100	2	Round	4.625	Electrolytic	1000	-40°C to 85°C
PB350Y075C440EA		PROLINE	Standard	35	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L7008BX	BX	Genteq	Special	11	6	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F9828		Genteq	Standard	30	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L1222		Genteq	Stock	0.22		850	0.47	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23A273F060CE1H1		Genteq	Special	27000		60	1.75	Round	3.625	Electrolytic	1000	-40°C to 85°C
23M512F400FJ1H1		Genteq	Special	5100		400	3	Round	5.875	Electrolytic	2000	-40°C to 85°C
97F8042		Genteq	Standard	50		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5011BX	BX	Genteq	Standard	10		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Y050C370CAB X	BX	PROLINE	Standard	20	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6854RC	RC	Genteq	Standard	34		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB500Z075T440EABX	BX	PROLINE	Standard	50	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6725		Genteq	Special	29		330	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350E000C370DAB X	BX	PROLINE	Standard	35		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M312F300CI1H1		Genteq	Special	3100		300	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23A593F050DG1H1		Genteq	Special	59000		50	2	Round	4.625	Electrolytic	1000	-40°C to 85°C
41L6221		Genteq	Stock	2.2		600	0.77	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
PB500Z050T370DABX	BX	PROLINE	Standard	50	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H302F300EE1H1		Genteq	Special	3000		300	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
23M112F450CH1H1		Genteq	Special	1100		450	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB075E000P440CA		PROLINE	Standard	7.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A523F100FH1H1		Genteq	Special	52000		100	3	Round	5.125	Electrolytic	1000	-40°C to 85°C
23H222F200BI1H1		Genteq	Special	2200		200	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6521		Genteq	Standard	28		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J142F250DD1H1		Genteq	Special	1400		250	2	Round	3.125	Electrolytic	2000	-40°C to 105°C
27L444BX	BX	Genteq	Special	37	11	300	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C902F250FJ1H1		Genteq	Special	9000		250	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
23A173F075BH1H1		Genteq	Special	17000		75	1.375	Round	5.125	Electrolytic	1000	-40°C to 85°C
23B472F200EG1H1		Genteq	Special	4700		200	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F6685BX	BX	Genteq	Special	15		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6868BR	BR	Genteq	Standard	26		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L6017		Genteq	Special	10		660	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5452		Genteq	Special	30	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6733		Genteq	Special	40		330	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6506BR	BR	Genteq	Standard	14		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A104F050EG1H1		Genteq	Special	100000		50	2.5	Round	4.625	Electrolytic	1000	-40°C to 85°C
PB500E000C440EA		PROLINE	Standard	50		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C313F050CF1H1		Genteq	Special	31000		50	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9084		Genteq	Standard	55		440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150Y100C370CAB X	BX	PROLINE	Standard	15	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B503F060FD1H1		Genteq	Special	50000		60	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
23B102F250BG1H1		Genteq	Special	1000		250	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
23A234F050FL1H1		Genteq	Special	230000		50	3	Round	8.625	Electrolytic	1000	-40°C to 85°C
97F9047BX	BX	Genteq	Standard	20	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400Z075S440EABX	BX	PROLINE	Standard	40	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A632F080BC1H1		Genteq	Special	6300		80	1.375	Round	2.625	Electrolytic	1000	-40°C to 85°C

97F8247BX	BX	Genteq	Standard	7		600	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F183F050DC1H1		Genteq	Special	18000		50	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F8065BX	BX	Genteq	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F472F150EE1H1		Genteq	Special	4700		150	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
23F183F075CG1H1		Genteq	Special	18000		75	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
27L5200BX	BX	Genteq	Standard	50	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B133F080DD1H1		Genteq	Special	13000		80	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F9059		Genteq	Special	55	5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9016BX	BX	Genteq	Special	20	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B293F050CG1H1		Genteq	Special	29000		50	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
27L1026		Genteq	Standard	8		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9023		Genteq	Special	35	10	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H412F300EG1H1		Genteq	Special	4100		300	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9641BX	BX	Genteq	Standard	40		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C532F200FD1H1		Genteq	Special	5300		200	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F9602		Genteq	Standard	20		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B213F060DD1H1		Genteq	Special	21000		60	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F5066		Genteq	Standard	10		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F373F100FL1H1		Genteq	Special	37000		100	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
23C563F080EI1H1		Genteq	Special	56000		80	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB075E000A370BAS	S	PROLINE	Stock	7.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9612		Genteq	Standard	35		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L724BR	BR	Genteq	Standard	24	11	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9081BX	BX	Genteq	Special	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L866BX	BX	Genteq	Standard	70	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M522F200DG1H1		Genteq	Special	5200		200	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9874		Genteq	Standard	55	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9888BX	BX	Genteq	Standard	35	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8257BX	BX	Genteq	Standard	40		600	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F432F075BC1H1		Genteq	Special	4300		75	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
27L7004		Genteq	Special	24		360	1.25	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 100°C
PB300E000C370CAB X	BX	PROLINE	Standard	30		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB200E000A370DA		PROLINE	Standard	20		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L797BR	BR	Genteq	Standard	15	7.5	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C323F100FE1H1		Genteq	Special	32000		100	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F6927BR	BR	Genteq	Special	11.5	3	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6535BX	BX	Genteq	Standard	24		400	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6773BX	BX	Genteq	Standard	22.5		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9892BX	BX	Genteq	Standard	35	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H252F400FF1H1		Genteq	Special	2500		400	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
PB500Y075C370EA		PROLINE	Standard	50	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J272F300FD1H1		Genteq	Special	2700		300	3	Round	3.125	Electrolytic	2000	-40°C to 105°C
23J152F400EG1H1		Genteq	Special	1500		400	2.5	Round	4.625	Electrolytic	2000	-40°C to 105°C
23C223F075CG1H1		Genteq	Special	22000		75	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
PB050E000P370CAB X	BX	PROLINE	Standard	5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C881F150BB1H1		Genteq	Special	880		150	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
23M742F300FG1H1		Genteq	Special	7400		300	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6656		Genteq	Standard	7.5		400	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H502F350FI1H1		Genteq	Special	5000		350	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
23A353F060DE1H1		Genteq	Special	35000		60	2	Round	3.625	Electrolytic	1000	-40°C to 85°C

PB300E000S440DA		PROLINE	Standard	30		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9834BX	BX	Genteq	Standard	35	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A463F075DI1H1		Genteq	Special	46000		75	2	Round	5.625	Electrolytic	1000	-40°C to 85°C
23A213F060DC1H1		Genteq	Special	21000		60	2	Round	2.625	Electrolytic	1000	-40°C to 85°C
97F6519BX	BX	Genteq	Standard	16		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J152F300CG1H1		Genteq	Special	1500		300	1.75	Round	4.625	Electrolytic	2000	-40°C to 105°C
23C152F250BI1H1		Genteq	Special	1500		250	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F9830BX	BX	Genteq	Standard	35	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9831		Genteq	Standard	40	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L3102		Genteq	Stock	0.1		2000	0.81	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F9645BX	BX	Genteq	Standard	45		440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6726		Genteq	Standard	30		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
41L4151		Genteq	Stock	1.5		400	0.57	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23F382F150CI1H1		Genteq	Special	3800		150	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
23H122F450DI1H1		Genteq	Special	1200		450	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
23H261F450BD1H1		Genteq	Special	260		450	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6929		Genteq	Standard	12		400	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB175E000A370DAS	S	PROLINE	Stock	17.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C132F250CD1H1		Genteq	Special	1300		250	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
27L1021BX	BX	Genteq	Standard	2		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350E000C240DA		PROLINE	Standard	35		240	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5436BX	BX	Genteq	Standard	6		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J142F350DH1H1		Genteq	Special	1400		350	2	Round	5.125	Electrolytic	2000	-40°C to 105°C
23A763F075EI1H1		Genteq	Special	76000		75	2.5	Round	5.625	Electrolytic	1000	-40°C to 85°C
PB550E000S370DA		PROLINE	Standard	55		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D223F028BI1H1		Genteq	Special	22000		28	1.375	Round	5.625	Electrolytic	1000	-55°C to 85°C
23B114F060FI1H1		Genteq	Special	11000 0		60	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
27L1002		Genteq	Standard	20		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F322F150DF1H1		Genteq	Special	3200		150	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
PB200E000S370CAB X	BX	PROLINE	Standard	20		370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C173F075DD1H1		Genteq	Special	17000		75	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
PB250Y050C370CAB X	BX	PROLINE	Standard	25	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F871F250CD1H1		Genteq	Special	870		250	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
PB200Z050S440CABX	BX	PROLINE	Standard	20	5	440	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M392F200DE1H1		Genteq	Special	3900		200	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6698		Genteq	Standard	13		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6930BX	BX	Genteq	Standard	10		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L797		Genteq	Standard	15	7.5	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5729		Genteq	Standard	50	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C802F200EI1H1		Genteq	Special	8000		200	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
23M992F300FJ1H1		Genteq	Special	9900		300	3	Round	5.875	Electrolytic	2000	-40°C to 85°C
23F523F060EI1H1		Genteq	Special	52000		60	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F6759RC	RC	Genteq	Standard	24		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5914		Genteq	Standard	32.5		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9667		Genteq	Standard	25		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J352F250FD1H1		Genteq	Special	3500		250	3	Round	3.125	Electrolytic	2000	-40°C to 105°C
23C683F075FG1H1		Genteq	Special	68000		75	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
23A313F075DF1H1		Genteq	Special	31000		75	2	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9855BX	BX	Genteq	Standard	40	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A183F080BI1H1		Genteq	Special	18000		80	1.375	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F8077		Genteq	Special	5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M541F350CB1H1		Genteq	Special	540		350	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C

23H581F450CE1H1		Genteq	Special	580		450	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
23B673F080FI1H1		Genteq	Special	67000		80	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B124F050FJ1H1		Genteq	Special	120000		50	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
97F8293BR	BR	Genteq	Standard	48		330	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H742F250FG1H1		Genteq	Special	7400		250	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J851F300DC1H1		Genteq	Special	850		300	2	Round	2.625	Electrolytic	2000	-40°C to 105°C
23F563F050EF1H1		Genteq	Special	56000		50	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F8063S	S	Genteq	Stock	20		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F223F050BI1H1		Genteq	Special	22000		50	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F9041		Genteq	Standard	35		440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L7101		Genteq	Stock	1		700	0.81	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23B133F050CC1H1		Genteq	Special	13000		50	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F8069S	S	Genteq	Stock	50		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J541F300BD1H1		Genteq	Special	540		300	1.375	Round	3.125	Electrolytic	2000	-40°C to 105°C
27L5538BX	BX	Genteq	Special	60	10	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A243F100DI1H1		Genteq	Special	24000		100	2	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F5001		Genteq	Standard	12.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D123F035CC1H1		Genteq	Special	12000		35	1.75	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F6885		Genteq	Standard	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB550Z050T440EABX	BX	PROLINE	Standard	55	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C682F250FG1H1		Genteq	Special	6800		250	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
23A184F060FL1H1		Genteq	Special	180000		60	3	Round	8.625	Electrolytic	1000	-40°C to 85°C
23H162F400DI1H1		Genteq	Special	1600		400	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
23C353F075EE1H1		Genteq	Special	35000		75	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
23F393F080EI1H1		Genteq	Special	39000		80	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F5710BX	BX	Genteq	Special	10		370	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C302F150CD1H1		Genteq	Special	3000		150	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
PB150E000P370CABX	BX	PROLINE	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB150E000A370CA		PROLINE	Standard	15		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C212F200BI1H1		Genteq	Special	2100		200	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
23B343F060ED1H1		Genteq	Special	34000		60	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F6644		Genteq	Special	45		300	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9631BX	BX	Genteq	Standard	20		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5706		Genteq	Standard	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D383F016CE1H1		Genteq	Special	38000		16	1.75	Round	3.625	Electrolytic	1000	-55°C to 85°C
PB500Z050S370DABX	BX	PROLINE	Standard	50	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5339BX	BX	Genteq	Standard	5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B124F050FI1H1		Genteq	Special	120000		50	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
PB200Y075C370CA		PROLINE	Standard	20	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB400Z050T440CA		PROLINE	Standard	40	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L651		Genteq	Standard	80	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B253F080DH1H1		Genteq	Special	25000		80	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
27L6016		Genteq	Special	8		660	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7009		Genteq	Special	24		400	1.25	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F9012		Genteq	Standard	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5251BX	BX	Genteq	Standard	70		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F103F050BD1H1		Genteq	Special	10000		50	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F9017		Genteq	Special	20	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Y050C440EABX	BX	PROLINE	Standard	35	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8037BX	BX	Genteq	Standard	25		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23F123F060BH1H1		Genteq	Special	12000		60	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
27L973		Genteq	Standard	15	9	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5504		Genteq	Special	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6863BX	BX	Genteq	Special	22.5		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F193F060CG1H1		Genteq	Special	19000		60	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
23H871F250BD1H1		Genteq	Special	870		250	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9732BX	BX	Genteq	Standard	25	7.5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5707		Genteq	Special	7.5		370	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9015		Genteq	Special	15	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F122F150DB1H1		Genteq	Special	1200		150	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F9849BX	BX	Genteq	Standard	40	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M422F350EH1H1		Genteq	Special	4200		350	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
23C473F075EG1H1		Genteq	Special	47000		75	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F9831BX	BX	Genteq	Standard	40	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Y050C440DA		PROLINE	Standard	30	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M701F400BG1H1		Genteq	Special	700		400	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
23D243F028CE1H1		Genteq	Special	24000		28	1.75	Round	3.625	Electrolytic	1000	-55°C to 85°C
97F8082		Genteq	Special	30		480	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C501F200BB1H1		Genteq	Special	500		200	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
97F6679BX	BX	Genteq	Special	24		480	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F263F080EF1H1		Genteq	Special	26000		80	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
23C892F075DB1H1		Genteq	Special	8900		75	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23C142F250BH1H1		Genteq	Special	1400		250	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
23J881F200CB1H1		Genteq	Special	880		200	1.75	Round	2.125	Electrolytic	2000	-40°C to 105°C
23A113F060CB1H1		Genteq	Special	11000		60	1.75	Round	2.125	Electrolytic	1000	-40°C to 85°C
27L200		Genteq	Special	90		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB050E000A440BAS	S	PROLINE	Stock	5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB350E000C440DAS	S	PROLINE	Stock	35		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9088		Genteq	Special	35		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A802F080CB1H1		Genteq	Special	8000		80	1.75	Round	2.125	Electrolytic	1000	-40°C to 85°C
97F5211		Genteq	Standard	50		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9815BX	BX	Genteq	Standard	55	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9780		Genteq	Standard	40	10	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C363F075DI1H1		Genteq	Special	36000		75	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
23B153F060BG1H1		Genteq	Special	15000		60	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
23F133F100EF1H1		Genteq	Special	13000		100	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F6861BX	BX	Genteq	Standard	20		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C183F150FH1H1		Genteq	Special	18000		150	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
27L541		Genteq	Standard	14	10.5	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L382		Genteq	Standard	8.5	3.5	280	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB175E000A440EA		PROLINE	Standard	17.5		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9883		Genteq	Standard	45	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M102F350DC1H1		Genteq	Special	1000		350	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F9501BX	BX	Genteq	Standard	2.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6516		Genteq	Standard	22.5		280	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9967BX	BX	Genteq	Standard	20	10	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9694		Genteq	Standard	15	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L551BX	BX	Genteq	Standard	20		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H561F300BC1H1		Genteq	Special	560		300	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
23C263F080ED1H1		Genteq	Special	26000		80	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
23C462F100BD1H1		Genteq	Special	4600		100	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C

23H481F350CB1H1		Genteq	Special	480		350	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
27L514		Genteq	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L2100		Genteq	Stock	10		250	0.79	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23M302F200CE1H1		Genteq	Special	3000		200	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
23C172F200DC1H1		Genteq	Special	1700		200	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
23H282F300DH1H1		Genteq	Special	2800		300	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB050E000P370CA		PROLINE	Standard	5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
42L2101		Genteq	Stock	1		1200	1.32	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F9994		Genteq	Standard	30	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400Y075C370DAB X	BX	PROLINE	Standard	40	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C372F200ED1H1		Genteq	Special	3700		200	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
23F722F075DB1H1		Genteq	Special	7200		75	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F9080BX	BX	Genteq	Standard	12.5		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B113F150FF1H1		Genteq	Special	11000		150	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
23B263F075ED1H1		Genteq	Special	26000		75	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
23M142F300CD1H1		Genteq	Special	1400		300	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C872F060BC1H1		Genteq	Special	8700		60	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
23F453F080FG1H1		Genteq	Special	45000		80	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F5573		Genteq	Special	10		370	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M192F350DF1H1		Genteq	Special	1900		350	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F5222		Genteq	Special	30		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB075E000P370CA		PROLINE	Standard	7.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100Y100C440CA		PROLINE	Standard	10	10	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6934		Genteq	Standard	26		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C622F050BB1H1		Genteq	Special	6200		50	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
27L801		Genteq	Standard	80	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6643RC	RC	Genteq	Special	30		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F462F100BH1H1		Genteq	Special	4600		100	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F9142		Genteq	Standard	17.5	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F413F060EG1H1		Genteq	Special	41000		60	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
23A103F150EF1H1		Genteq	Special	10000		150	2.5	Round	4.125	Electrolytic	1000	-40°C to 85°C
23A263F100EF1H1		Genteq	Special	26000		100	2.5	Round	4.125	Electrolytic	1000	-40°C to 85°C
23C282F250DG1H1		Genteq	Special	2800		250	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
23B343F100FI1H1		Genteq	Special	34000		100	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
27L567S	S	Genteq	Stock	15		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B183F100EG1H1		Genteq	Special	18000		100	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
23B172F150DB1H1		Genteq	Special	1700		150	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F9202		Genteq	Standard	5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6880		Genteq	Standard	20	12	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F511F150BB1H1		Genteq	Special	510		150	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
42L4152		Genteq	Stock	0.15		3000	1.26	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F6506BX	BX	Genteq	Standard	14		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6951		Genteq	Standard	22.5		540	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5115BX	BX	Genteq	Special	35		440	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A153F080DC1H1		Genteq	Special	15000		80	2	Round	2.625	Electrolytic	1000	-40°C to 85°C
27L6012		Genteq	Special	4		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6866BX	BX	Genteq	Standard	40		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB250Y100C370CA		PROLINE	Standard	25	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J122F200CC1H1		Genteq	Special	1200		200	1.75	Round	2.625	Electrolytic	2000	-40°C to 105°C
97F9635		Genteq	Standard	30		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8041		Genteq	Standard	45		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6515BX	BX	Genteq	Standard	10		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

PB300E000A370EAS	S	PROLINE	Stock	30		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A113F150EG1H1		Genteq	Special	11000		150	2.5	Round	4.625	Electrolytic	1000	-40°C to 85°C
23M142F350CF1H1		Genteq	Special	1400		350	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F5266		Genteq	Special	45		370	2.5	Round	3.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L571BX	BX	Genteq	Standard	4		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L204RR	RR	Genteq	Standard	35	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F123F100DI1H1		Genteq	Special	12000		100	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F6522RC	RC	Genteq	Standard	24		280	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B912F200FJ1H1		Genteq	Special	9100		200	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
23H952F250FI1H1		Genteq	Special	9500		250	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F5222BX	BX	Genteq	Special	30		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F842F080DC1H1		Genteq	Special	8400		80	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
27L1052BX	BX	Genteq	Standard	55		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F732F250FL1H1		Genteq	Special	7300		250	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
PB450Z050T440DABX	BX	PROLINE	Standard	45	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9526		Genteq	Standard	15	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B222F250DG1H1		Genteq	Special	2200		250	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
PB450Z050S370DA		PROLINE	Standard	45	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A583F100FI1H1		Genteq	Special	58000		100	3	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F8255		Genteq	Standard	30		600	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5209BX	BX	Genteq	Standard	45		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9011BX	BX	Genteq	Standard	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M133F200FG1H1		Genteq	Special	13000		200	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6686BX	BX	Genteq	Special	11.5		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB300Z100S440DA		PROLINE	Standard	30	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5209		Genteq	Standard	45		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D253F016BF1H1		Genteq	Special	25000		16	1.375	Round	4.125	Electrolytic	1000	-55°C to 85°C
PB500Y100D370EAB X	BX	PROLINE	Standard	50	10	370	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D512F055BD1H1		Genteq	Special	5100		55	1.375	Round	3.125	Electrolytic	1000	-55°C to 85°C
23C103F075BF1H1		Genteq	Special	10000		75	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
23C252F200CF1H1		Genteq	Special	2500		200	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
41L6100		Genteq	Stock	10		600	1.36	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
23B282F100BD1H1		Genteq	Special	2800		100	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F8244BX	BX	Genteq	Special	4		600	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C372F200CI1H1		Genteq	Special	3700		200	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
23C103F100BI1H1		Genteq	Special	10000		100	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
23C213F075DE1H1		Genteq	Special	21000		75	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
23A443F075EE1H1		Genteq	Special	44000		75	2.5	Round	3.625	Electrolytic	1000	-40°C to 85°C
23F153F150FL1H1		Genteq	Special	15000		150	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
97F6679		Genteq	Special	24		480	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F102F200BG1H1		Genteq	Special	1000		200	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
23F243F080DI1H1		Genteq	Special	24000		80	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
23J232F350FE1H1		Genteq	Special	2300		350	3	Round	3.625	Electrolytic	2000	-40°C to 105°C
27L1008BX	BX	Genteq	Standard	60	10	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F593F060FG1H1		Genteq	Special	59000		60	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
27L973BX	BX	Genteq	Standard	15	9	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L630		Genteq	Standard	19	7	300	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9123		Genteq	Special	17.5		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A393F050CF1H1		Genteq	Special	39000		50	1.75	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9689		Genteq	Standard	40	5	370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB050E000A370AABX	BX	PROLINE	Standard	5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6521BX	BX	Genteq	Standard	28		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F5474BX	BX	Genteq	Special	17.5	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9811		Genteq	Standard	15	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9967		Genteq	Standard	20	10	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8293BX	BX	Genteq	Standard	48		330	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9061		Genteq	Standard	55	10	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A512F150DE1H1		Genteq	Special	5100		150	2	Round	3.625	Electrolytic	1000	-40°C to 85°C
23C113F250FL1H1		Genteq	Special	11000		250	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
23B163F080DE1H1		Genteq	Special	16000		80	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
27L868BX	BX	Genteq	Special	80	10	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J122F250BH1H1		Genteq	Special	1200		250	1.375	Round	5.125	Electrolytic	2000	-40°C to 105°C
27L1024		Genteq	Standard	5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D363F007BE1H1		Genteq	Special	36000		7.5	1.375	Round	3.625	Electrolytic	1000	-55°C to 85°C
97F9002		Genteq	Standard	10		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9337		Genteq	Standard	55		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Z050S370DA		PROLINE	Standard	35	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9804BX	BX	Genteq	Standard	25		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5052BX	BX	Genteq	Special	20		370	1.75	Round	3.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C543F075EH1H1		Genteq	Special	54000		75	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F7075		Genteq	Special	90		370	2.5	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250Y100C440EABX	BX	PROLINE	Standard	25	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9036BX	BX	Genteq	Standard	7.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B193F060BI1H1		Genteq	Special	19000		60	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B113F150EI1H1		Genteq	Special	11000		150	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9170BX	BX	Genteq	Special	35		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A292F150BG1H1		Genteq	Special	2900		150	1.375	Round	4.625	Electrolytic	1000	-40°C to 85°C
27L853BX	BX	Genteq	Standard	24	10	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB250Z050S440DAS	S	PROLINE	Stock	25	5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C402F250EF1H1		Genteq	Special	4000		250	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F6887BR	BR	Genteq	Standard	38	17	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8038S	S	Genteq	Stock	30		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B612F150DH1H1		Genteq	Special	6100		150	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
23C903F060FF1H1		Genteq	Special	90000		60	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
23F243F060CI1H1		Genteq	Special	24000		60	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
23D662F035BC1H1		Genteq	Special	6600		35	1.375	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F9991BX	BX	Genteq	Standard	20	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L1221		Genteq	Stock	2.2		850	1.18	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F9842BX	BX	Genteq	Standard	35	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F233F075CI1H1		Genteq	Special	23000		75	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F9827		Genteq	Standard	25	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB700Z075T370EABX	BX	PROLINE	Standard	70	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A153F060DB1H1		Genteq	Special	15000		60	2	Round	2.125	Electrolytic	1000	-40°C to 85°C
23C543F050DG1H1		Genteq	Special	54000		50	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
23D732F055CC1H1		Genteq	Special	7300		55	1.75	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F9838		Genteq	Standard	40	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H891F200BC1H1		Genteq	Special	890		200	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
27L6089BX	BX	Genteq	Special	18		660	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6691BX	BX	Genteq	Standard	24	4	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L797BX	BX	Genteq	Standard	15	7.5	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L7000BR	BR	Genteq	Standard	48		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23F122F150BE1H1		Genteq	Special	1200		150	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C

97F6517BR	BR	Genteq	Standard	15		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5459		Genteq	Standard	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H392F200DG1H1		Genteq	Special	3900		200	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23C442F150CF1H1		Genteq	Special	4400		150	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
23D453F020CG1H1		Genteq	Special	45000		20	1.75	Round	4.625	Electrolytic	1000	-55°C to 85°C
97F6883RC	RC	Genteq	Standard	36	20	280	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450E000C440EA		PROLINE	Standard	45		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9030		Genteq	Special	50	10	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A723F050EE1H1		Genteq	Special	72000		50	2.5	Round	3.625	Electrolytic	1000	-40°C to 85°C
PB600Z100T370EABX	BX	PROLINE	Standard	60	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C113F150EG1H1		Genteq	Special	11000		150	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F6538		Genteq	Standard	35		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F233F080EE1H1		Genteq	Special	23000		80	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F9595		Genteq	Standard	6		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9816		Genteq	Standard	60	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5035		Genteq	Special	5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L349		Genteq	Special	75		440	2.5	Round	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H162F450FE1H1		Genteq	Special	1600		450	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
23B902F100DF1H1		Genteq	Special	9000		100	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
23F932F100ED1H1		Genteq	Special	9300		100	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F6778BR	BR	Genteq	Standard	45		330	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H232F200DD1H1		Genteq	Special	2300		200	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23D842F020BB1H1		Genteq	Special	8400		20	1.375	Round	2.125	Electrolytic	1000	-55°C to 85°C
40L3201		Genteq	Stock	2		400	0.48	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
97F8070		Genteq	Standard	55		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F542F100CE1H1		Genteq	Special	5400		100	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
23F102F250BI1H1		Genteq	Special	1000		250	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C162F150CB1H1		Genteq	Special	1600		150	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
23B113F080BH1H1		Genteq	Special	11000		80	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F5564BX	BX	Genteq	Standard	8		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L114		Genteq	Standard	70	7.5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D402F055BC1H1		Genteq	Special	4000		55	1.375	Round	2.625	Electrolytic	1000	-55°C to 85°C
27L390		Genteq	Standard	40	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M742F250EH1H1		Genteq	Special	7400		250	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9016		Genteq	Special	20	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Z050T440CABX	BX	PROLINE	Standard	35	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB350E000P370DABX	BX	PROLINE	Standard	35		370	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8066		Genteq	Standard	35		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C103F100CE1H1		Genteq	Special	10000		100	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F9003		Genteq	Standard	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H202F350DI1H1		Genteq	Special	2000		350	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F5706BX	BX	Genteq	Standard	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A463F060ED1H1		Genteq	Special	46000		60	2.5	Round	3.125	Electrolytic	1000	-40°C to 85°C
23A452F150CF1H1		Genteq	Special	4500		150	1.75	Round	4.125	Electrolytic	1000	-40°C to 85°C
PB350E000C240DAS	S	PROLINE	Stock	35		240	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100E000P370CA		PROLINE	Standard	10		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB800Z100T370EA		PROLINE	Standard	80	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8046		Genteq	Standard	70		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M632F300FF1H1		Genteq	Special	6300		300	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
42L1682		Genteq	Stock	0.68		850	0.81	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F9510		Genteq	Special	30	3	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

97F6846BX	BX	Genteq	Standard	29		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6681		Genteq	Special	5		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H382F400FI1H1		Genteq	Special	3800		400	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
PB500E000P370EABX	BX	PROLINE	Standard	50		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C833F050FE1H1		Genteq	Special	83000		50	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
23H112F300BG1H1		Genteq	Special	1100		300	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB700Z050T440GABX	BX	PROLINE	Standard	70	5	440	2.5	Round	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F153F075CF1H1		Genteq	Special	15000		75	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
42L4223		Genteq	Stock	0.022		3000	0.65	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F5927BX	BX	Genteq	Standard	70	7.5	440	2.5	Round	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6788BX	BX	Genteq	Standard	2.5		330	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6886BR	BR	Genteq	Standard	27	8	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9851BX	BX	Genteq	Standard	45	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L413BX	BX	Genteq	Standard	35	16	300	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L558BX	BX	Genteq	Standard	25	10	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M862F200EG1H1		Genteq	Special	8600		200	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J931F200DB1H1		Genteq	Special	930		200	2	Round	2.125	Electrolytic	2000	-40°C to 105°C
97F9643		Genteq	Standard	40		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B703F050FE1H1		Genteq	Special	70000		50	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6918BX	BX	Genteq	Special	28		480	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L7003BX	BX	Genteq	Standard	26		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F9970		Genteq	Standard	50	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H232F400EH1H1		Genteq	Special	2300		400	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9608BX	BX	Genteq	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8050BX	BX	Genteq	Standard	90		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C322F150BH1H1		Genteq	Special	3200		150	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
23B771F250CC1H1		Genteq	Special	770		250	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F6509BX	BX	Genteq	Standard	38		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9073		Genteq	Special	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F293F050DE1H1		Genteq	Special	29000		50	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
23B353F100FJ1H1		Genteq	Special	35000		100	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
PB400E000P370DABX	BX	PROLINE	Standard	40		370	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A293F050BH1H1		Genteq	Special	29000		50	1.375	Round	5.125	Electrolytic	1000	-40°C to 85°C
PB100E000A440CAS	S	PROLINE	Stock	10		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B472F250EI1H1		Genteq	Special	4700		250	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
23H852F250FH1H1		Genteq	Special	8500		250	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
23A323F080ED1H1		Genteq	Special	32000		80	2.5	Round	3.125	Electrolytic	1000	-40°C to 85°C
27L6023BX	BX	Genteq	Special	30		660	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6948BX	BX	Genteq	Standard	14.5		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H352F300FD1H1		Genteq	Special	3500		300	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
PB300E000C440DABX	BX	PROLINE	Standard	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5913BX	BX	Genteq	Standard	30		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5160		Genteq	Standard	25		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6504		Genteq	Standard	15		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L567		Genteq	Standard	15		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F332F100CC1H1		Genteq	Special	3300		100	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
42L2682		Genteq	Stock	0.68		1200	1.08	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F8062		Genteq	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A223F060CD1H1		Genteq	Special	22000		60	1.75	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F5450		Genteq	Special	30	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

97F6505BR	BR	Genteq	Standard	17.5		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F302F100BE1H1		Genteq	Special	3000		100	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
23B142F200BH1H1		Genteq	Special	1400		200	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F6769BX	BX	Genteq	Standard	16		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J222F200CF1H1		Genteq	Special	2200		200	1.75	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F9971BX	BX	Genteq	Standard	50	7.5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Z075S440EA		PROLINE	Standard	35	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9739		Genteq	Standard	40	5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H252F250CG1H1		Genteq	Special	2500		250	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F5160BX	BX	Genteq	Standard	25		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8052BX	BX	Genteq	Standard	100		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B703F080FJ1H1		Genteq	Special	70000		80	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
23H931F400DE1H1		Genteq	Special	930		400	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F5241BX	BX	Genteq	Standard	65		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J532F250EI1H1		Genteq	Special	5300		250	2.5	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F6862		Genteq	Standard	20		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D183F020BE1H1		Genteq	Special	18000		20	1.375	Round	3.625	Electrolytic	1000	-55°C to 85°C
23C413F060CH1H1		Genteq	Special	41000		60	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F6758RC	RC	Genteq	Standard	15		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB600Z075T370EA		PROLINE	Standard	60	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB300E000S370CABX	BX	PROLINE	Standard	30		370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB250Y050C370CA		PROLINE	Standard	25	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C253F060BI1H1		Genteq	Special	25000		60	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6538BX	BX	Genteq	Standard	35		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M392F400FG1H1		Genteq	Special	3900		400	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
23C812F100DC1H1		Genteq	Special	8100		100	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
PB300Z050S370CABX	BX	PROLINE	Standard	30	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F582F250FI1H1		Genteq	Special	5800		250	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
PB250Z050S370CA		PROLINE	Standard	25	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6948		Genteq	Standard	14.5		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9381BX	BX	Genteq	Standard	35		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C163F100DF1H1		Genteq	Special	16000		100	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
23B273F060CG1H1		Genteq	Special	27000		60	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
23J312F300EG1H1		Genteq	Special	3100		300	2.5	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F6674RC	RC	Genteq	Special	12		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C163F050CC1H1		Genteq	Special	16000		50	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
27L204BR	BR	Genteq	Standard	35	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C102F250BF1H1		Genteq	Special	1000		250	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
23C233F050BH1H1		Genteq	Special	23000		50	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
PB500Z050T440HABX	BX	PROLINE	Standard	50	5	440	2.5	Round	4.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5368		Genteq	Special	35	5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9088BX	BX	Genteq	Special	35		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8248BX	BX	Genteq	Standard	8		600	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB800E000T440GABX	BX	PROLINE	Standard	80		440	2.5	Round	5.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6926BR	BR	Genteq	Standard	26		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6919BX	BX	Genteq	Standard	16		540	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F432F200FE1H1		Genteq	Special	4300		200	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F5522BX	BX	Genteq	Special	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6641BX	BX	Genteq	Special	52		170	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9975BX	BX	Genteq	Standard	20	5	440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

97F6709		Genteq	Special	14		330	1.5	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L2121		Genteq	Stock	1.2		1200	1.14	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
41L7151		Genteq	Stock	1.5		700	0.81	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F9975		Genteq	Standard	20	5	440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L4471		Genteq	Stock	4.7		400	0.83	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23F972F075BG1H1		Genteq	Special	9700		75	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F9796		Genteq	Standard	35	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L3472		Genteq	Stock	0.47		2000	1.32	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F9623		Genteq	Standard	50		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6836		Genteq	Standard	48		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6659BX	BX	Genteq	Standard	12		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F772F060BE1H1		Genteq	Special	7700		60	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
PB350E000C370DA		PROLINE	Standard	35		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB550Z100T440EABX	BX	PROLINE	Standard	55	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M182F400DH1H1		Genteq	Special	1800		400	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB050E000A440BABX	BX	PROLINE	Standard	5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M142F450DH1H1		Genteq	Special	1400		450	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9850BX	BX	Genteq	Standard	50	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C813F080FI1H1		Genteq	Special	81000		80	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
23H172F200DC1H1		Genteq	Special	1700		200	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
PB075E000A440CAS	S	PROLINE	Stock	7.5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B743F060EI1H1		Genteq	Special	74000		60	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B422F250EH1H1		Genteq	Special	4200		250	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
23H332F200DF1H1		Genteq	Special	3300		200	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8069		Genteq	Standard	50		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F522F100BI1H1		Genteq	Special	5200		100	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
27L758		Genteq	Special	50		440	2	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D453F016CF1H1		Genteq	Special	45000		16	1.75	Round	4.125	Electrolytic	1000	-55°C to 85°C
97F5502BX	BX	Genteq	Standard	2		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C193F075CF1H1		Genteq	Special	19000		75	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F6708BX	BX	Genteq	Standard	13		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6918RC	RC	Genteq	Special	28		480	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M163F200FI1H1		Genteq	Special	16000		200	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
23H102F300BF1H1		Genteq	Special	1000		300	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F9606		Genteq	Standard	25		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L880		Genteq	Standard	45	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8242BX	BX	Genteq	Special	2.5		600	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A313F060CF1H1		Genteq	Special	31000		60	1.75	Round	4.125	Electrolytic	1000	-40°C to 85°C
23B243F075CH1H1		Genteq	Special	24000		75	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
23J182F200CE1H1		Genteq	Special	1800		200	1.75	Round	3.625	Electrolytic	2000	-40°C to 105°C
23A633F080EH1H1		Genteq	Special	63000		80	2.5	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F8250		Genteq	Standard	12		600	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F393F050ED1H1		Genteq	Special	39000		50	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
23H102F400CG1H1		Genteq	Special	1000		400	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
23M301F400BC1H1		Genteq	Special	300		400	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
23M162F200BE1H1		Genteq	Special	1600		200	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
23F503F060FF1H1		Genteq	Special	50000		60	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F9982BX	BX	Genteq	Standard	30	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9992		Genteq	Standard	15	7.5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6777BR	BR	Genteq	Special	35		330	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8047BX	BX	Genteq	Standard	75		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB060E000A370BAS	S	PROLINE	Stock	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C

97F6873		Genteq	Standard	24		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F312F200DI1H1		Genteq	Special	3100		200	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
23H392F350FG1H1		Genteq	Special	3900		350	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB350Z100T440DABX	BX	PROLINE	Standard	35	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A104F075FH1H1		Genteq	Special	100000		75	3	Round	5.125	Electrolytic	1000	-40°C to 85°C
23D183F016CB1H1		Genteq	Special	18000		16	1.75	Round	2.125	Electrolytic	1000	-55°C to 85°C
97F6621		Genteq	Standard	15		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6759BX	BX	Genteq	Standard	24		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C163F060CC1H1		Genteq	Special	16000		60	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
23B762F080CC1H1		Genteq	Special	7600		80	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
23C273F060DD1H1		Genteq	Special	27000		60	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
PB450Y050C370DABX	BX	PROLINE	Standard	45	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8061BX	BX	Genteq	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L572S	S	Genteq	Stock	12.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H832F200EI1H1		Genteq	Special	8300		200	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F5051BX	BX	Genteq	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8060S	S	Genteq	Stock	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9973		Genteq	Standard	55	7.5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
25L261BX	BX	Genteq	Standard	80	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A403F100EI1H1		Genteq	Special	40000		100	2.5	Round	5.625	Electrolytic	1000	-40°C to 85°C
23H103F200FH1H1		Genteq	Special	10000		200	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
23B701F250BE1H1		Genteq	Special	700		250	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6526		Genteq	Standard	10		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L877		Genteq	Standard	30	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B463F080EI1H1		Genteq	Special	46000		80	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F5503BX	BX	Genteq	Standard	3		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L63		Genteq	Standard	80		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8037		Genteq	Standard	25		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A113F100CE1H1		Genteq	Special	11000		100	1.75	Round	3.625	Electrolytic	1000	-40°C to 85°C
23A114F075FI1H1		Genteq	Special	110000		75	3	Round	5.625	Electrolytic	1000	-40°C to 85°C
23C762F150DH1H1		Genteq	Special	7600		150	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F5727BX	BX	Genteq	Special	25	15	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9617BX	BX	Genteq	Standard	45		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D213F020CC1H1		Genteq	Special	21000		20	1.75	Round	2.625	Electrolytic	1000	-55°C to 85°C
PB450Y100C370DABX	BX	PROLINE	Standard	45	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6823S	S	Genteq	Stock	28		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9242		Genteq	Special	20		440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5283BX	BX	Genteq	Special	30		370	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J132F400FD1H1		Genteq	Special	1300		400	3	Round	3.125	Electrolytic	2000	-40°C to 105°C
27L945		Genteq	Standard	45		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A173F060BF1H1		Genteq	Special	17000		60	1.375	Round	4.125	Electrolytic	1000	-40°C to 85°C
23H952F200FG1H1		Genteq	Special	9500		200	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6504BX	BX	Genteq	Standard	15		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L572		Genteq	Standard	12.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B102F150BC1H1		Genteq	Special	1000		150	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
23B372F200DI1H1		Genteq	Special	3700		200	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
PB500E000P370EA		PROLINE	Standard	50		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6674		Genteq	Special	12		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6538RC	RC	Genteq	Standard	35		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F9981BX	BX	Genteq	Standard	30	5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L2151		Genteq	Stock	1.5		250	0.39	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23C462F200EE1H1		Genteq	Special	4600		200	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
23M431F450BF1H1		Genteq	Special	430		450	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
23A194F050FJ1H1		Genteq	Special	19000 0		50	3	Round	5.875	Electrolytic	1000	-40°C to 85°C
97F9969		Genteq	Standard	45	7.5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6682BR	BR	Genteq	Special	31.5		420	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1051BX	BX	Genteq	Special	50	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200E000P440CAS	S	PROLINE	Stock	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B381F200BB1H1		Genteq	Special	380		200	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F9018BX	BX	Genteq	Standard	20	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F782F150FF1H1		Genteq	Special	7800		150	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F9025BX	BX	Genteq	Special	40	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H641F400CD1H1		Genteq	Special	640		400	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
42L1151		Genteq	Stock	1.5		850	0.96	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23C813F060FE1H1		Genteq	Special	81000		60	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F6764		Genteq	Standard	5		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H452F200DH1H1		Genteq	Special	4500		200	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
23D323F016CD1H1		Genteq	Special	32000		16	1.75	Round	3.125	Electrolytic	1000	-55°C to 85°C
97F9849		Genteq	Standard	40	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Z100S370DA		PROLINE	Standard	30	10	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8054BX	BX	Genteq	Standard	3		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A193F075BI1H1		Genteq	Special	19000		75	1.375	Round	5.625	Electrolytic	1000	-40°C to 85°C
23M112F300CC1H1		Genteq	Special	1100		300	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F9982		Genteq	Standard	30	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J722F200FG1H1		Genteq	Special	7200		200	3	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F6517		Genteq	Standard	15		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B532F150CI1H1		Genteq	Special	5300		150	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
23C902F200FG1H1		Genteq	Special	9000		200	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F8247		Genteq	Standard	7		600	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C113F050CB1H1		Genteq	Special	11000		50	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
23B263F075CI1H1		Genteq	Special	26000		75	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9614		Genteq	Standard	40		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L402BX	BX	Genteq	Standard	24	8	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5520BX	BX	Genteq	Special	45	5	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M752F200FD1H1		Genteq	Special	7500		200	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
23H102F300CC1H1		Genteq	Special	1000		300	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23A592F100BE1H1		Genteq	Special	5900		100	1.375	Round	3.625	Electrolytic	1000	-40°C to 85°C
PB150Z075S440DABX	BX	PROLINE	Standard	15	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B102F250CD1H1		Genteq	Special	1000		250	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
23C382F075BB1H1		Genteq	Special	3800		75	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
PB800Z075T370EABX	BX	PROLINE	Standard	80	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L880BX	BX	Genteq	Standard	45	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400E000P370DA		PROLINE	Standard	40		370	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J132F200BG1H1		Genteq	Special	1300		200	1.375	Round	4.625	Electrolytic	2000	-40°C to 105°C
23M532F350FG1H1		Genteq	Special	5300		350	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
25L2005		Genteq	Special	35		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L567BX	BX	Genteq	Standard	15		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8057BX	BX	Genteq	Standard	6		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6692		Genteq	Special	8.5		480	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J661F350BH1H1		Genteq	Special	660		350	1.375	Round	5.125	Electrolytic	2000	-40°C to 105°C
23M292F250DE1H1		Genteq	Special	2900		250	2	Round	3.625	Electrolytic	2000	-40°C to 85°C

97F9510BX	BX	Genteq	Special	30	3	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200E000P440CA		PROLINE	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L6501		Genteq	Stock	5		600	1.12	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F8258		Genteq	Standard	45		600	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB450Y100C370DA		PROLINE	Standard	45	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H562F200FD1H1		Genteq	Special	5600		200	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
23F123F080CF1H1		Genteq	Special	12000		80	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
23H512F250EG1H1		Genteq	Special	5100		250	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
27L865RR	RR	Genteq	Standard	15	6	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A473F060CI1H1		Genteq	Special	47000		60	1.75	Round	5.625	Electrolytic	1000	-40°C to 85°C
23J292F200ED1H1		Genteq	Special	2900		200	2.5	Round	3.125	Electrolytic	2000	-40°C to 105°C
23M202F450EG1H1		Genteq	Special	2000		450	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J122F200BF1H1		Genteq	Special	1200		200	1.375	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F9617		Genteq	Standard	45		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9796BX	BX	Genteq	Standard	35	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L114BX	BX	Genteq	Standard	70	7.5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A373F060CG1H1		Genteq	Special	37000		60	1.75	Round	4.625	Electrolytic	1000	-40°C to 85°C
27L531BX	BX	Genteq	Standard	16	10	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8060		Genteq	Standard	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M291F450CB1H1		Genteq	Special	290		450	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23M641F450BI1H1		Genteq	Special	640		450	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
23H632F250FF1H1		Genteq	Special	6300		250	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F9462BX	BX	Genteq	Standard	40	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB050E000P440CAB X	BX	PROLINE	Standard	5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8040S	S	Genteq	Stock	40		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J671F350CD1H1		Genteq	Special	670		350	1.75	Round	3.125	Electrolytic	2000	-40°C to 105°C
23C122F200DB1H1		Genteq	Special	1200		200	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23A843F060FE1H1		Genteq	Special	84000		60	3	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F6506RC	RC	Genteq	Standard	14		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB400Z050S370DABX	BX	PROLINE	Standard	40	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB300Y100C370DAB X	BX	PROLINE	Standard	30	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
40L3681		Genteq	Stock	6.8		400	0.67	Oval	2.25	Dry-Axial Leaded	100000	-55°C to 105°C
27L570		Genteq	Standard	5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7004BX	BX	Genteq	Special	24		360	1.25	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F8084BX	BX	Genteq	Standard	60		440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8058BX	BX	Genteq	Standard	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1045BX	BX	Genteq	Standard	60		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7001BX	BX	Genteq	Standard	10		400	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F6867BX	BX	Genteq	Standard	52		280	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5513		Genteq	Special	4		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9803BX	BX	Genteq	Standard	25	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB550Z100T370DA		PROLINE	Standard	55	10	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F772F060DB1H1		Genteq	Special	7700		60	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F9971		Genteq	Standard	50	7.5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6857		Genteq	Standard	8		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9115BX	BX	Genteq	Special	45		370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F153F080CG1H1		Genteq	Special	15000		80	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
27L990		Genteq	Special	35		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8067BX	BX	Genteq	Standard	40		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23F283F060DH1H1		Genteq	Special	28000		60	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
PB450Y050C440EA		PROLINE	Standard	45	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8064BX	BX	Genteq	Standard	25		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350E000C240DABX	BX	PROLINE	Standard	35		240	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A123F080BF1H1		Genteq	Special	12000		80	1.375	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F5502		Genteq	Standard	2		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L53BX	BX	Genteq	Standard	26	15	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B912F050CB1H1		Genteq	Special	9100		50	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
23H102F450DH1H1		Genteq	Special	1000		450	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
41L2501		Genteq	Stock	5		250	0.67	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F6950BR	BR	Genteq	Standard	12	12	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D153F020BD1H1		Genteq	Special	15000		20	1.375	Round	3.125	Electrolytic	1000	-55°C to 85°C
97F6678		Genteq	Special	4.5		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M551F400CC1H1		Genteq	Special	550		400	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F6858RC	RC	Genteq	Standard	10		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M132F300DC1H1		Genteq	Special	1300		300	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
23A603F100FJ1H1		Genteq	Special	60000		100	3	Round	5.875	Electrolytic	1000	-40°C to 85°C
97F9264BX	BX	Genteq	Standard	20		410	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250Z075S440DA		PROLINE	Standard	25	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B122F250BI1H1		Genteq	Special	1200		250	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B301F250BB1H1		Genteq	Special	300		250	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
PB200E000P240CA		PROLINE	Standard	20		240	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L4150		Genteq	Stock	15		400	1.26	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
97F6531BX	BX	Genteq	Standard	7		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9612BX	BX	Genteq	Standard	35		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Y050C370DABX	BX	PROLINE	Standard	35	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F562F100DD1H1		Genteq	Special	5600		100	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F6530BR	BR	Genteq	Standard	40		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D153F028BF1H1		Genteq	Special	15000		28	1.375	Round	4.125	Electrolytic	1000	-55°C to 85°C
23F682F080BF1H1		Genteq	Special	6800		80	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F6533		Genteq	Standard	30		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6758BR	BR	Genteq	Standard	15		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9024BX	BX	Genteq	Special	40	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F183F080ED1H1		Genteq	Special	18000		80	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
23B114F060FJ1H1		Genteq	Special	110000		60	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
97F8245		Genteq	Standard	5		600	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB800Z100T370EABX	BX	PROLINE	Standard	80	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F173F050BG1H1		Genteq	Special	17000		50	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F9840		Genteq	Standard	40	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150Y050C370CA		PROLINE	Standard	15	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H412F200CI1H1		Genteq	Special	4100		200	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F742F200FI1H1		Genteq	Special	7400		200	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C273F080DG1H1		Genteq	Special	27000		80	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
23M232F450EH1H1		Genteq	Special	2300		450	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB500E000T440DA		PROLINE	Standard	50		440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C453F060ED1H1		Genteq	Special	45000		60	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
41L6471		Genteq	Stock	4.7		600	1.08	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
PB350Z100S370DABX	BX	PROLINE	Standard	35	10	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6934RC	RC	Genteq	Standard	26		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6540BX	BX	Genteq	Standard	45		280	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6824		Genteq	Standard	28		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

23D493F007BG1H1		Genteq	Special	49000		7.5	1.375	Round	4.625	Electrolytic	1000	-55°C to 85°C
97F6755S	S	Genteq	Stock	26		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450Z075S370DA		PROLINE	Standard	45	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5300BX	BX	Genteq	Standard	10		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L402RC	RC	Genteq	Standard	24	8	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F7075BX	BX	Genteq	Special	90		370	2.5	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L378BX	BX	Genteq	Standard	45	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6675BX	BX	Genteq	Special	16		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A223F150FJ1H1		Genteq	Special	22000		150	3	Round	5.875	Electrolytic	1000	-40°C to 85°C
23B242F150DC1H1		Genteq	Special	2400		150	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
23H222F250CF1H1		Genteq	Special	2200		250	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
PB250Z050S440DA		PROLINE	Standard	25	5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L727BX	BX	Genteq	Standard	45	19	300	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8051BX	BX	Genteq	Standard	95		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D193F035CE1H1		Genteq	Special	19000		35	1.75	Round	3.625	Electrolytic	1000	-55°C to 85°C
23J381F350CB1H1		Genteq	Special	380		350	1.75	Round	2.125	Electrolytic	2000	-40°C to 105°C
97F9011S	S	Genteq	Stock	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B302F150CE1H1		Genteq	Special	3000		150	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
23M652F250EG1H1		Genteq	Special	6500		250	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9743		Genteq	Standard	17.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6890BX	BX	Genteq	Standard	18	10	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A392F150CE1H1		Genteq	Special	3900		150	1.75	Round	3.625	Electrolytic	1000	-40°C to 85°C
PB700E000T440EABX	BX	PROLINE	Standard	70		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5437		Genteq	Standard	3		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C172F250DD1H1		Genteq	Special	1700		250	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
23C763F060EG1H1		Genteq	Special	76000		60	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
PB450E000C440EAS	S	PROLINE	Stock	45		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L801BX	BX	Genteq	Standard	80	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A173F150FG1H1		Genteq	Special	17000		150	3	Round	4.625	Electrolytic	1000	-40°C to 85°C
23H152F400EE1H1		Genteq	Special	1500		400	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
23M152F300BH1H1		Genteq	Special	1500		300	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB100E000P370CAB X	BX	PROLINE	Standard	10		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5401BX	BX	Genteq	Special	45	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A503F075EF1H1		Genteq	Special	50000		75	2.5	Round	4.125	Electrolytic	1000	-40°C to 85°C
PB450E000S370DAB X	BX	PROLINE	Standard	45		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J562F200EH1H1		Genteq	Special	5600		200	2.5	Round	5.125	Electrolytic	2000	-40°C to 105°C
23J541F400BI1H1		Genteq	Special	540		400	1.375	Round	5.625	Electrolytic	2000	-40°C to 105°C
23M242F300CG1H1		Genteq	Special	2400		300	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
27L1054		Genteq	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8253		Genteq	Standard	20		600	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9804		Genteq	Standard	25		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C662F100BF1H1		Genteq	Special	6600		100	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F6526BX	BX	Genteq	Standard	10		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6824BX	BX	Genteq	Standard	28		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D623F007BI1H1		Genteq	Special	62000		7.5	1.375	Round	5.625	Electrolytic	1000	-55°C to 85°C
97F6927RC	RC	Genteq	Special	11.5	3	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D903F007CG1H1		Genteq	Special	90000		7.5	1.75	Round	4.625	Electrolytic	1000	-55°C to 85°C
97F6862BX	BX	Genteq	Standard	20		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6881RC	RC	Genteq	Standard	42	14	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L427		Genteq	Standard	15	10	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F5276		Genteq	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A383F100FF1H1		Genteq	Special	38000		100	3	Round	4.125	Electrolytic	1000	-40°C to 85°C
PB600E000S370DAB X	BX	PROLINE	Standard	60		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6952BX	BX	Genteq	Standard	36		540	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B202F250CH1H1		Genteq	Special	2000		250	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB350Z075S370DA		PROLINE	Standard	35	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D952F055BH1H1		Genteq	Special	9500		55	1.375	Round	5.125	Electrolytic	1000	-55°C to 85°C
PB400E000S440EA		PROLINE	Standard	40		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB800E000T440GA		PROLINE	Standard	80		440	2.5	Round	5.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B132F200DC1H1		Genteq	Special	1300		200	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F9839		Genteq	Standard	55	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6014BX	BX	Genteq	Special	6		660	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A783F060EG1H1		Genteq	Special	78000		60	2.5	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F9965BX	BX	Genteq	Standard	15	10	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8241BX	BX	Genteq	Special	2		600	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F223F060CH1H1		Genteq	Special	22000		60	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
23A703F080EI1H1		Genteq	Special	70000		80	2.5	Round	5.625	Electrolytic	1000	-40°C to 85°C
23H142F250BG1H1		Genteq	Special	1400		250	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
27L589BX	BX	Genteq	Standard	10	5	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB030E000A440AAS	S	PROLINE	Stock	3		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F192F250CI1H1		Genteq	Special	1900		250	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
23B473F075FE1H1		Genteq	Special	47000		75	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6887		Genteq	Standard	38	17	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F233F050DD1H1		Genteq	Special	23000		50	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
23J342F300FE1H1		Genteq	Special	3400		300	3	Round	3.625	Electrolytic	2000	-40°C to 105°C
97F9829BX	BX	Genteq	Standard	35	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6805BX	BX	Genteq	Standard	10		280	1.5	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J392F350FI1H1		Genteq	Special	3900		350	3	Round	5.625	Electrolytic	2000	-40°C to 105°C
23C523F060DH1H1		Genteq	Special	52000		60	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F8045		Genteq	Standard	65		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D323F035CI1H1		Genteq	Special	32000		35	3	Round	8.625	Electrolytic	1000	-55°C to 85°C
PB100E000P440CAB X	BX	PROLINE	Standard	10		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB450Z050S370DABX	BX	PROLINE	Standard	45	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8043BX	BX	Genteq	Standard	55		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H172F400FD1H1		Genteq	Special	1700		400	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
40L3100		Genteq	Stock	10		400	0.7	Oval	2.25	Dry-Axial Leaded	100000	-55°C to 105°C
23C902F080CC1H1		Genteq	Special	9000		80	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
23J751F350BI1H1		Genteq	Special	750		350	1.375	Round	5.625	Electrolytic	2000	-40°C to 105°C
23M151F450BB1H1		Genteq	Special	150		450	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
27L7002BX	BX	Genteq	Special	14		330	1.75	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23F362F250EH1H1		Genteq	Special	3600		250	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
25L501		Genteq	Standard	40		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6015BX	BX	Genteq	Special	7		660	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9815		Genteq	Standard	55	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6884RC	RC	Genteq	Standard	33	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B502F075BC1H1		Genteq	Special	5000		75	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
23C662F080BD1H1		Genteq	Special	6600		80	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
23H352F300EF1H1		Genteq	Special	3500		300	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
23M522F200CI1H1		Genteq	Special	5200		200	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23C213F050CD1H1		Genteq	Special	21000		50	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F8264BX	BX	Genteq	Standard	45		600	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C443F080EG1H1		Genteq	Special	44000		80	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
23B92F080DB1H1		Genteq	Special	6900		80	2	Round	2.125	Electrolytic	3000	-40°C to 85°C

23F393F050C1H1		Genteq	Special	39000		50	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F6865		Genteq	Standard	35		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J291F400DB1H1		Genteq	Special	290		400	2	Round	2.125	Electrolytic	2000	-40°C to 105°C
97F6658		Genteq	Standard	18		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9152BX	BX	Genteq	Standard	40		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B713F050EH1H1		Genteq	Special	71000		50	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F6865BR	BR	Genteq	Standard	35		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6864		Genteq	Standard	24		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C502F250FE1H1		Genteq	Special	5000		250	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
23B153F075CE1H1		Genteq	Special	15000		75	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
23M122F450DG1H1		Genteq	Special	1200		450	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23F302F075BB1H1		Genteq	Special	3000		75	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
23F193F080DG1H1		Genteq	Special	19000		80	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
PB350Z075S370DABX	BX	PROLINE	Standard	35	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C122F150BC1H1		Genteq	Special	1200		150	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
23B163F100FD1H1		Genteq	Special	16000		100	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB040E000P370CA		PROLINE	Standard	4		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9632BX	BX	Genteq	Standard	25		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D433F007CC1H1		Genteq	Special	43000		7.5	1.75	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F6873BX	BX	Genteq	Standard	24		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6534		Genteq	Special	28		170	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9010BX	BX	Genteq	Standard	55		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6759S	S	Genteq	Stock	24		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F691F250BF1H1		Genteq	Special	690		250	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
23C343F060DE1H1		Genteq	Special	34000		60	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
25L6252BR	BR	Genteq	Standard	7	3	400	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H851F300BE1H1		Genteq	Special	850		300	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
23M502F250DI1H1		Genteq	Special	5000		250	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F123F050DB1H1		Genteq	Special	12000		50	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
23C134F050FH1H1		Genteq	Special	13000 0		50	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
23C282F250CI1H1		Genteq	Special	2800		250	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
27L987BX	BX	Genteq	Standard	3		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B283F080DI1H1		Genteq	Special	28000		80	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
PB250Z050S440DABX	BX	PROLINE	Standard	25	5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L4251		Genteq	Stock	2.5		400	0.73	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F9639		Genteq	Standard	35		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M901F450DE1H1		Genteq	Special	900		450	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6926		Genteq	Standard	26		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B123F075DC1H1		Genteq	Special	12000		75	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
27L6023		Genteq	Special	30		660	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J222F200DE1H1		Genteq	Special	2200		200	2	Round	3.625	Electrolytic	2000	-40°C to 105°C
23J252F200DF1H1		Genteq	Special	2500		200	2	Round	4.125	Electrolytic	2000	-40°C to 105°C
41L4201		Genteq	Stock	2		400	0.65	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
PB060E000A370BA		PROLINE	Standard	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A543F060DH1H1		Genteq	Special	54000		60	2	Round	5.125	Electrolytic	1000	-40°C to 85°C
25L6252RR	RR	Genteq	Standard	7	3	400	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB600Z075T370EABX	BX	PROLINE	Standard	60	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6823		Genteq	Standard	28		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6764RC	RC	Genteq	Standard	5		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L827BR	BR	Genteq	Standard	18	10	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M612F400FL1H1		Genteq	Special	6100		400	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
97F9018		Genteq	Standard	20	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

97F6854BR	BR	Genteq	Standard	34		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6660		Genteq	Standard	12		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5513BX	BX	Genteq	Special	4		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B652F150EE1H1		Genteq	Special	6500		150	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
23M692F250FE1H1		Genteq	Special	6900		250	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
41L7401		Genteq	Stock	4		700	1.3	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F6918		Genteq	Special	28		480	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F942F100CI1H1		Genteq	Special	9400		100	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
40L3472		Genteq	Stock	0.47		400	0.28	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
23B402F200EF1H1		Genteq	Special	4000		200	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F6872BR	BR	Genteq	Standard	48		280	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B443F075EG1H1		Genteq	Special	44000		75	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
42L4102		Genteq	Stock	0.1		3000	1.04	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
27L630BX	BX	Genteq	Standard	19	7	300	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F222F200CH1H1		Genteq	Special	2200		200	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F6853		Genteq	Special	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6951BX	BX	Genteq	Standard	22.5		540	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M232F350DG1H1		Genteq	Special	2300		350	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23C212F150DB1H1		Genteq	Special	2100		150	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23M501F250BB1H1		Genteq	Special	500		250	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
23J481F400CD1H1		Genteq	Special	480		400	1.75	Round	3.125	Electrolytic	2000	-40°C to 105°C
42L1152		Genteq	Stock	0.15		850	0.39	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23M102F250BD1H1		Genteq	Special	1000		250	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6681BX	BX	Genteq	Special	5		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5388BX	BX	Genteq	Standard	12.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L92		Genteq	Special	80	7.5	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L695S	S	Genteq	Stock	7.5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M123F250FI1H1		Genteq	Special	12000		250	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9621BX	BX	Genteq	Standard	50		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9248		Genteq	Special	3.75		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6868		Genteq	Standard	26		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350E000S370CA		PROLINE	Standard	35		370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9615BX	BX	Genteq	Standard	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L862BX	BX	Genteq	Standard	35	24	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F852F060CC1H1		Genteq	Special	8500		60	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
23C273F050CE1H1		Genteq	Special	27000		50	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
27L600		Genteq	Standard	39	13	330	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M113F250FH1H1		Genteq	Special	11000		250	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9635BX	BX	Genteq	Standard	30		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6661		Genteq	Standard	14		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L573BR	BR	Genteq	Standard	40	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9802		Genteq	Standard	50		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8053S	S	Genteq	Stock	120		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400Y075C440EABX	BX	PROLINE	Standard	40	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J791F300CC1H1		Genteq	Special	790		300	1.75	Round	2.625	Electrolytic	2000	-40°C to 105°C
27L533		Genteq	Standard	30	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C263F060CE1H1		Genteq	Special	26000		60	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
27L33		Genteq	Standard	25	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M152F450DI1H1		Genteq	Special	1500		450	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6658BX	BX	Genteq	Standard	18		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F6919RC	RC	Genteq	Standard	16		540	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L591RR	RR	Genteq	Standard	35	15	300	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J921F400ED1H1		Genteq	Special	920		400	2.5	Round	3.125	Electrolytic	2000	-40°C to 105°C
23B223F080DG1H1		Genteq	Special	22000		80	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
23M442F300FD1H1		Genteq	Special	4400		300	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6715		Genteq	Standard	19		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9730		Genteq	Standard	25	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6603BX	BX	Genteq	Special	24		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5051		Genteq	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6521BR	BR	Genteq	Standard	28		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9491BX	BX	Genteq	Standard	30		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A222F150BE1H1		Genteq	Special	2200		150	1.375	Round	3.625	Electrolytic	1000	-40°C to 85°C
23J182F300ED1H1		Genteq	Special	1800		300	2.5	Round	3.125	Electrolytic	2000	-40°C to 105°C
PB250E000P370CA		PROLINE	Standard	25		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H332F350FF1H1		Genteq	Special	3300		350	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
23B172F200DD1H1		Genteq	Special	1700		200	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB600Z050T440EABX	BX	PROLINE	Standard	60	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9090BX	BX	Genteq	Standard	40		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J152F250CE1H1		Genteq	Special	1500		250	1.75	Round	3.625	Electrolytic	2000	-40°C to 105°C
23J102F400DH1H1		Genteq	Special	1000		400	2	Round	5.125	Electrolytic	2000	-40°C to 105°C
PB150E000P440CABX	BX	PROLINE	Standard	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6868BX	BX	Genteq	Standard	26		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9204		Genteq	Standard	7.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J342F200DH1H1		Genteq	Special	3400		200	2	Round	5.125	Electrolytic	2000	-40°C to 105°C
23F272F250FD1H1		Genteq	Special	2700		250	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
23M192F200BF1H1		Genteq	Special	1900		200	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F5320BX	BX	Genteq	Standard	50		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6018		Genteq	Special	12		660	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L556BX	BX	Genteq	Standard	70	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9619BX	BX	Genteq	Standard	45		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5300		Genteq	Standard	10		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F7903BX	BX	Genteq	Standard	2		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6951RC	RC	Genteq	Standard	22.5		540	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B472F150CH1H1		Genteq	Special	4700		150	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F8047		Genteq	Standard	75		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9677BX	BX	Genteq	Standard	25	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D113F055CE1H1		Genteq	Special	11000		55	1.75	Round	3.625	Electrolytic	1000	-55°C to 85°C
97F9611BX	BX	Genteq	Standard	35		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F881F200BF1H1		Genteq	Special	880		200	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F6946RC	RC	Genteq	Standard	21		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C143F200FL1H1		Genteq	Special	14000		200	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
97F8257		Genteq	Standard	40		600	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F392F250FF1H1		Genteq	Special	3900		250	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
23M452F250DH1H1		Genteq	Special	4500		250	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
23A273F100FD1H1		Genteq	Special	27000		100	3	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F9995BX	BX	Genteq	Standard	30	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L1332		Genteq	Stock	0.33		850	0.57	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
PB175E000A440EABX	BX	PROLINE	Standard	17.5		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB250Y100C440EA		PROLINE	Standard	25	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9803		Genteq	Standard	25	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23J822F200FH1H1		Genteq	Special	8200		200	3	Round	5.125	Electrolytic	2000	-40°C to 105°C
23M152F400ED1H1		Genteq	Special	1500		400	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
23M102F250CB1H1		Genteq	Special	1000		250	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23C114F075FL1H1		Genteq	Special	11000 0		75	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
97F9892		Genteq	Standard	35	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9817BX	BX	Genteq	Standard	60	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A683F080FF1H1		Genteq	Special	68000		80	3	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9444		Genteq	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9698		Genteq	Special	25	4	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L2250		Genteq	Stock	25		250	1.24	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23F783F060FJ1H1		Genteq	Special	78000		60	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
23B153F150FH1H1		Genteq	Special	15000		150	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB800E000T370EABX	BX	PROLINE	Standard	80		370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F483F050EE1H1		Genteq	Special	48000		50	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
23J182F250DE1H1		Genteq	Special	1800		250	2	Round	3.625	Electrolytic	2000	-40°C to 105°C
23B143F050BF1H1		Genteq	Special	14000		50	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
23H372F250EE1H1		Genteq	Special	3700		250	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
23F862F080CD1H1		Genteq	Special	8600		80	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
23F892F060BF1H1		Genteq	Special	8900		60	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
23F842F100CH1H1		Genteq	Special	8400		100	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
23J102F250CC1H1		Genteq	Special	1000		250	1.75	Round	2.625	Electrolytic	2000	-40°C to 105°C
97F6763BR	BR	Genteq	Standard	10		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A912F100BH1H1		Genteq	Special	9100		100	1.375	Round	5.125	Electrolytic	1000	-40°C to 85°C
23D163F035BH1H1		Genteq	Special	16000		35	1.375	Round	5.125	Electrolytic	1000	-55°C to 85°C
PB450Y075D440EAB X	BX	PROLINE	Standard	45	7.5	440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D323F028CG1H1		Genteq	Special	32000		28	1.75	Round	4.625	Electrolytic	1000	-55°C to 85°C
23M182F300CE1H1		Genteq	Special	1800		300	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F9694BX	BX	Genteq	Standard	15	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6677BX	BX	Genteq	Special	4		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9201BX	BX	Genteq	Standard	4		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F323F075EF1H1		Genteq	Special	32000		75	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
23B313F080FD1H1		Genteq	Special	31000		80	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F8293RC	RC	Genteq	Standard	48		330	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9001		Genteq	Standard	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B134F060FL1H1		Genteq	Special	13000 0		60	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
23F303F100FJ1H1		Genteq	Special	30000		100	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
23B222F200CG1H1		Genteq	Special	2200		200	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F5704BX	BX	Genteq	Standard	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H182F250DD1H1		Genteq	Special	1800		250	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C632F200EG1H1		Genteq	Special	6300		200	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
27L866		Genteq	Standard	70	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8090BX	BX	Genteq	Standard	20		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8249BX	BX	Genteq	Standard	10		600	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8067		Genteq	Standard	40		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C243F075DF1H1		Genteq	Special	24000		75	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
41L4401		Genteq	Stock	4		400	0.77	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23H152F450EG1H1		Genteq	Special	1500		450	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
42L1251		Genteq	Stock	2.5		850	1.24	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F5159BX	BX	Genteq	Standard	40		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L569		Genteq	Special	50	5	440	2.5	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5054BX	BX	Genteq	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9675		Genteq	Standard	25	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
25L502		Genteq	Standard	35		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C

97F6643		Genteq	Special	30		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9882BX	BX	Genteq	Standard	40	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M122F450CI1H1		Genteq	Special	1200		450	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F323F075FD1H1		Genteq	Special	32000		75	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
23J182F350EF1H1		Genteq	Special	1800		350	2.5	Round	4.125	Electrolytic	2000	-40°C to 105°C
23J871F400CH1H1		Genteq	Special	870		400	1.75	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F9530		Genteq	Standard	2.5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9040		Genteq	Standard	25		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9848BX	BX	Genteq	Standard	35	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B123F050BE1H1		Genteq	Special	12000		50	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
23A412F150DD1H1		Genteq	Special	4100		150	2	Round	3.125	Electrolytic	1000	-40°C to 85°C
23H812F200FF1H1		Genteq	Special	8100		200	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
23F113F080DD1H1		Genteq	Special	11000		80	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
27L204		Genteq	Standard	35	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B102F200BF1H1		Genteq	Special	1000		200	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F9602S	S	Genteq	Stock	20		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6744		Genteq	Special	12.5		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6885RR	RR	Genteq	Standard	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5063		Genteq	Special	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A113F075DB1H1		Genteq	Special	11000		75	2	Round	2.125	Electrolytic	1000	-40°C to 85°C
23C442F100CB1H1		Genteq	Special	4400		100	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
23H781F400CE1H1		Genteq	Special	780		400	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
23F443F060FE1H1		Genteq	Special	44000		60	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F9695BX	BX	Genteq	Standard	20	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H771F450CG1H1		Genteq	Special	770		450	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
23F943F060FL1H1		Genteq	Special	94000		60	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
23H282F350FE1H1		Genteq	Special	2800		350	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
23C483F050DI1H1		Genteq	Special	48000		50	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
23F142F200DD1H1		Genteq	Special	1400		200	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F9619		Genteq	Standard	45		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8072S	S	Genteq	Stock	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C133F100DE1H1		Genteq	Special	13000		100	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F9985BX	BX	Genteq	Standard	40	10	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B103F080CD1H1		Genteq	Special	70000		80	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
23M362F450FI1H1		Genteq	Special	3600		450	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6680BX	BX	Genteq	Special	24		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L33BX	BX	Genteq	Standard	25	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB125E000A440DAB X	BX	PROLINE	Standard	12.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H122F200DB1H1		Genteq	Special	1200		200	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
PB200E000A370DAS	S	PROLINE	Stock	20		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB450Y100C440EA		PROLINE	Standard	45	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H151F450BB1H1		Genteq	Special	150		450	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
PB500E000S440FA		PROLINE	Standard	50		440	2	Round	5.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6763BX	BX	Genteq	Standard	10		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B144F050FL1H1		Genteq	Special	140000		50	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
97F6945RC	RC	Genteq	Standard	24		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6788RC	RC	Genteq	Standard	2.5		330	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9082BX	BX	Genteq	Standard	20		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9638		Genteq	Standard	35		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J211F400BC1H1		Genteq	Special	210		400	1.375	Round	2.625	Electrolytic	2000	-40°C to 105°C
97F9600		Genteq	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

27L6095BX	BX	Genteq	Special	2		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C102F200BD1H1		Genteq	Special	1000		200	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F6830		Genteq	Special	35		280	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6774		Genteq	Standard	24		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB075E000A440CAB X	BX	PROLINE	Standard	7.5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9970S	S	Genteq	Stock	50	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8057		Genteq	Standard	6		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L3683		Genteq	Stock	0.068		2000	0.67	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F9760		Genteq	Standard	45	7.5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H232F300CH1H1		Genteq	Special	2300		300	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
25L6753BX	BX	Genteq	Standard	35	13	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450Y075C370DA		PROLINE	Standard	45	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J601F300DB1H1		Genteq	Special	600		300	2	Round	2.125	Electrolytic	2000	-40°C to 105°C
97F9052		Genteq	Special	30	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L865		Genteq	Standard	15	6	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6716		Genteq	Standard	20		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
25L6755		Genteq	Standard	20	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M512F200ED1H1		Genteq	Special	5100		200	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F5211BX	BX	Genteq	Standard	50		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F222F150CE1H1		Genteq	Special	2200		150	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F6880BX	BX	Genteq	Standard	20	12	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8042BX	BX	Genteq	Standard	50		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6018BX	BX	Genteq	Special	12		660	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B823F075FI1H1		Genteq	Special	82000		75	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F6655		Genteq	Standard	50		260	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9010		Genteq	Standard	55		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A263F060BI1H1		Genteq	Special	26000		60	1.375	Round	5.625	Electrolytic	1000	-40°C to 85°C
PB400Y100C370DAB X	BX	PROLINE	Standard	40	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6760		Genteq	Standard	12		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F703F075FI1H1		Genteq	Special	70000		75	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C363F060CG1H1		Genteq	Special	36000		60	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
23C103F080BF1H1		Genteq	Special	10000		80	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F5001BX	BX	Genteq	Standard	12.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M412F200CG1H1		Genteq	Special	4100		200	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9020BX	BX	Genteq	Special	25	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A413F080EE1H1		Genteq	Special	41000		80	2.5	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F9266		Genteq	Standard	35		410	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6022BX	BX	Genteq	Special	25		660	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6683RC	RC	Genteq	Special	21		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9802S	S	Genteq	Stock	50		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F182F200DE1H1		Genteq	Special	1800		200	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
23C113F060CB1H1		Genteq	Special	11000		60	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
23B642F100CE1H1		Genteq	Special	6400		100	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6682RC	RC	Genteq	Special	31.5		420	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B901F200DB1H1		Genteq	Special	900		200	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
23M122F350BI1H1		Genteq	Special	1200		350	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9856BX	BX	Genteq	Standard	40	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C192F250CF1H1		Genteq	Special	1900		250	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
27L945BX	BX	Genteq	Standard	45		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A353F050DD1H1		Genteq	Special	35000		50	2	Round	3.125	Electrolytic	1000	-40°C to 85°C

97F6677		Genteq	Special	4		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D133F028BE1H1		Genteq	Special	13000		28	1.375	Round	3.625	Electrolytic	1000	-55°C to 85°C
23M501F400BE1H1		Genteq	Special	500		400	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB500Z100T440EABX	BX	PROLINE	Standard	50	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
25L756BX	BX	Genteq	Standard	60	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6784		Genteq	Standard	36		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6780BX	BX	Genteq	Standard	29		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB020E000A440AABX	BX	PROLINE	Standard	2		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F672F150FE1H1		Genteq	Special	6700		150	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
23A283F075CG1H1		Genteq	Special	28000		75	1.75	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F6691		Genteq	Standard	24	4	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8251BX	BX	Genteq	Standard	15		600	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L442		Genteq	Standard	28	7	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L6073BX	BX	Genteq	Special	15		660	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9060		Genteq	Special	55	7.5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6890BR	BR	Genteq	Standard	18	10	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB075E000A370BABX	BX	PROLINE	Standard	7.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB600Z050T440EA		PROLINE	Standard	60	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D313F007CB1H1		Genteq	Special	31000		7.5	1.75	Round	2.125	Electrolytic	1000	-55°C to 85°C
PB300Z075S370DABX	BX	PROLINE	Standard	30	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9636		Genteq	Standard	30		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C133F150EH1H1		Genteq	Special	13000		150	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
23B203F150FL1H1		Genteq	Special	20000		150	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
97F9899BX	BX	Genteq	Standard	35	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Z100S370DABX	BX	PROLINE	Standard	30	10	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB250E000A440EABX	BX	PROLINE	Standard	25		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L6094		Genteq	Special	3		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6860BX	BX	Genteq	Standard	15		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB550E000D440EA		PROLINE	Standard	55		440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M162F350DE1H1		Genteq	Special	1600		350	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB200Z100S370CA		PROLINE	Standard	20	10	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H312F250DG1H1		Genteq	Special	3100		250	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9026BX	BX	Genteq	Special	40	10	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M222F350ED1H1		Genteq	Special	2200		350	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
27L476BX	BX	Genteq	Standard	33	15	330	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9593BX	BX	Genteq	Standard	50	10	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB030E000P370CABX	BX	PROLINE	Standard	3		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J861F250BE1H1		Genteq	Special	860		250	1.375	Round	3.625	Electrolytic	2000	-40°C to 105°C
27L827		Genteq	Standard	18	10	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L576RR	RR	Genteq	Special	20	8	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B113F060DB1H1		Genteq	Special	11000		60	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
23M832F250E1H1		Genteq	Special	8300		250	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23A372F150BI1H1		Genteq	Special	3700		150	1.375	Round	5.625	Electrolytic	1000	-40°C to 85°C
23M122F200BC1H1		Genteq	Special	1200		200	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
23C153F050BE1H1		Genteq	Special	15000		50	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F6540		Genteq	Standard	45		280	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L200BX	BX	Genteq	Special	90		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9391		Genteq	Special	80		370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C

97F9841		Genteq	Standard	45	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F883F075FL1H1		Genteq	Special	80000		75	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
97F6861		Genteq	Standard	20		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6776		Genteq	Standard	28		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A902F075BD1H1		Genteq	Special	9000		75	1.375	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F8059S	S	Genteq	Stock	10		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8008		Genteq	Special	50		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9976		Genteq	Standard	20	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H262F250DF1H1		Genteq	Special	2600		250	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F6531		Genteq	Standard	7		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200Y075C440DAB X	BX	PROLINE	Standard	20	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB400E000C440DAS	S	PROLINE	Stock	40		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C203F060BG1H1		Genteq	Special	20000		60	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
23F333F080FE1H1		Genteq	Special	33000		80	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
PB250E000A370DAB X	BX	PROLINE	Standard	25		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J162F300DF1H1		Genteq	Special	1600		300	2	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F8256BX	BX	Genteq	Standard	35		600	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C283F075CI1H1		Genteq	Special	28000		75	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB175E000P370CAB X	BX	PROLINE	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9810BX	BX	Genteq	Standard	15	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M173F200FJ1H1		Genteq	Special	17000		200	3	Round	5.875	Electrolytic	2000	-40°C to 85°C
23H113F250FL1H1		Genteq	Special	11000		250	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
97F9829		Genteq	Standard	35	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A882F150DI1H1		Genteq	Special	8800		150	2	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F6850BX	BX	Genteq	Standard	45		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB600E000P370EA		PROLINE	Standard	60		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9883BX	BX	Genteq	Standard	45	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9526BX	BX	Genteq	Standard	15	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F162F150BG1H1		Genteq	Special	1600		150	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
23A253F050BG1H1		Genteq	Special	25000		50	1.375	Round	4.625	Electrolytic	1000	-40°C to 85°C
23F931F250BH1H1		Genteq	Special	930		250	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
23H622F350FL1H1		Genteq	Special	6200		350	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
97F8073		Genteq	Standard	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D482F035BB1H1		Genteq	Special	4800		35	1.375	Round	2.125	Electrolytic	1000	-55°C to 85°C
23J172F300CH1H1		Genteq	Special	1700		300	1.75	Round	5.125	Electrolytic	2000	-40°C to 105°C
PB500Y100D370EA		PROLINE	Standard	50	10	370	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9675BX	BX	Genteq	Standard	25	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400Z100S440EA		PROLINE	Standard	40	10	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M312F400EH1H1		Genteq	Special	3100		400	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
23B732F100CF1H1		Genteq	Special	7300		100	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23F332F060BB1H1		Genteq	Special	3300		60	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
23B582F200FF1H1		Genteq	Special	5800		200	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
23A293F080CH1H1		Genteq	Special	29000		80	1.75	Round	5.125	Electrolytic	1000	-40°C to 85°C
23H302F400FG1H1		Genteq	Special	3000		400	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
23M701F350DB1H1		Genteq	Special	700		350	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23B133F075BH1H1		Genteq	Special	13000		75	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F6711		Genteq	Special	16		330	1.5	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB250E000A370DAS	S	PROLINE	Stock	25		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5170		Genteq	Special	20		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9251		Genteq	Standard	25	3.2	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M182F300DD1H1		Genteq	Special	1800		300	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C154F050FJ1H1		Genteq	Special	150000		50	3	Round	5.875	Electrolytic	1000	-45°C to 95°C

PB150Y100C440DAB X	BX	PROLINE	Standard	15	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB500Y100D440GA		PROLINE	Standard	50	10	440	2	Oval	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5052		Genteq	Special	20		370	1.75	Round	3.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9625		Genteq	Standard	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9989		Genteq	Standard	55	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6517BX	BX	Genteq	Standard	15		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H671F350CC1H1		Genteq	Special	670		350	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23H302F250ED1H1		Genteq	Special	3000		250	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
23J312F350FG1H1		Genteq	Special	3100		350	3	Round	4.625	Electrolytic	2000	-40°C to 105°C
PB250E000A440EA		PROLINE	Standard	25		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8241		Genteq	Special	2		600	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B902F060BD1H1		Genteq	Special	9000		60	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F6760RC	RC	Genteq	Standard	12		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6685		Genteq	Special	15		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J961F350DE1H1		Genteq	Special	960		350	2	Round	3.625	Electrolytic	2000	-40°C to 105°C
97F9477		Genteq	Standard	45	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6621RC	RC	Genteq	Standard	15		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J352F250EF1H1		Genteq	Special	3500		250	2.5	Round	4.125	Electrolytic	2000	-40°C to 105°C
PB150E000A440EAS	S	PROLINE	Stock	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9780BX	BX	Genteq	Standard	40	10	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250E000P370CAB X	BX	PROLINE	Standard	25		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
42L4153		Genteq	Stock	0.015		3000	0.55	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
27L729		Genteq	Special	20	4	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H511F400CC1H1		Genteq	Special	510		400	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23M521F450DC1H1		Genteq	Special	520		450	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
23J741F250CB1H1		Genteq	Special	740		250	1.75	Round	2.125	Electrolytic	2000	-40°C to 105°C
23F601F250DB1H1		Genteq	Special	600		250	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F5377		Genteq	Special	35	10	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B223F080CI1H1		Genteq	Special	22000		80	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9451		Genteq	Standard	20	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6776BX	BX	Genteq	Standard	28		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B822F100DE1H1		Genteq	Special	8200		100	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6702		Genteq	Special	7		330	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200Y100C440DAB X	BX	PROLINE	Standard	20	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8063		Genteq	Standard	20		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1054BX	BX	Genteq	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C672F150DG1H1		Genteq	Special	6700		150	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F9611		Genteq	Standard	35		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9638BX	BX	Genteq	Standard	35		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6013		Genteq	Special	5		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L637BX	BX	Genteq	Special	80	5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Y100C370DAB X	BX	PROLINE	Standard	20	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB400Z050S370DA		PROLINE	Standard	40	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9814BX	BX	Genteq	Standard	20	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6606BR	BR	Genteq	Standard	10		400	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9023BX	BX	Genteq	Special	35	10	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150Z100S440DA		PROLINE	Standard	15	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C

97F6777		Genteq	Special	35		330	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1053		Genteq	Standard	7.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H961F350DD1H1		Genteq	Special	960		350	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F5465BX	BX	Genteq	Special	30		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H281F400BC1H1		Genteq	Special	280		400	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F6812BR	BR	Genteq	Standard	17.5		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F123F050BE1H1		Genteq	Special	12000		50	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
23J282F250DH1H1		Genteq	Special	2800		250	2	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F6749		Genteq	Standard	13.5		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9119		Genteq	Special	30		440	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB700Z075T440GABX	BX	PROLINE	Standard	70	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L7000RC	RC	Genteq	Standard	48		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F9696		Genteq	Standard	20	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M162F450FD1H1		Genteq	Special	1600		450	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9021		Genteq	Special	35	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8062BX	BX	Genteq	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L591BR	BR	Genteq	Standard	35	15	300	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D253F020BG1H1		Genteq	Special	25000		20	1.375	Round	4.625	Electrolytic	1000	-55°C to 85°C
23C772F250FH1H1		Genteq	Special	7700		250	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F9985		Genteq	Standard	40	10	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6768RC	RC	Genteq	Standard	14		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB250Z100S370CABX	BX	PROLINE	Standard	25	10	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6623BX	BX	Genteq	Standard	24		400	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L2222		Genteq	Stock	0.22		1200	0.81	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23M231F450BC1H1		Genteq	Special	230		450	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F6922		Genteq	Special	8		525	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H282F450FI1H1		Genteq	Special	2800		450	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
23B113F075BG1H1		Genteq	Special	11000		75	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F6521RC	RC	Genteq	Standard	28		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L531		Genteq	Standard	16	10	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F342F150CH1H1		Genteq	Special	3400		150	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
27L6089		Genteq	Special	18		660	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5608		Genteq	Special	35	7.5	370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6782BX	BX	Genteq	Special	18.5		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A795F150DH1H1		Genteq	Special	7900		150	2	Round	5.125	Electrolytic	1000	-40°C to 85°C
23H132F450FD1H1		Genteq	Special	1300		450	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
PB400Y050C370DA		PROLINE	Standard	40	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F132F250CF1H1		Genteq	Special	1300		250	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F9874S	S	Genteq	Stock	55	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B533F050FD1H1		Genteq	Special	53000		50	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
23F462F250FG1H1		Genteq	Special	4600		250	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
24DB300B370PA		Genteq	Standard	30		370	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
97F9969BX	BX	Genteq	Standard	45	7.5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6749S	S	Genteq	Stock	13.5		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5457		Genteq	Special	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB500Y075C370EAB X	BX	PROLINE	Standard	50	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6712		Genteq	Special	17.5		330	1.5	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6882		Genteq	Standard	24	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F5522		Genteq	Special	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B233F100FF1H1		Genteq	Special	23000		100	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
PB250E000A370DA		PROLINE	Standard	25		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6751		Genteq	Special	9.25		330	1.25	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9760BX	BX	Genteq	Standard	45	7.5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L872BX	BX	Genteq	Standard	60	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9695		Genteq	Standard	20	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5304BX	BX	Genteq	Special	15		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6200BX	BX	Genteq	Special	9.4		290	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9625S	S	Genteq	Stock	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C213F100DH1H1		Genteq	Special	21000		100	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
PB500Z075S370EABX	BX	PROLINE	Standard	50	7.5	370	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9851		Genteq	Standard	45	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Z100S370CABX	BX	PROLINE	Standard	20	10	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5377BX	BX	Genteq	Special	35	10	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M232F250CE1H1		Genteq	Special	2300		250	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
23D872F035CB1H1		Genteq	Special	87000		35	1.75	Round	2.125	Electrolytic	1000	-55°C to 85°C
23C852F150DI1H1		Genteq	Special	8500		150	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6533BX	BX	Genteq	Standard	30		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6601RC	RC	Genteq	Standard	10		400	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8095BX	BX	Genteq	Standard	30	30	150	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L576BR	BR	Genteq	Special	20	8	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L442BR	BR	Genteq	Standard	28	7	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6858BX	BX	Genteq	Standard	10		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB600Z050T370DA		PROLINE	Standard	60	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H192F250CE1H1		Genteq	Special	1900		250	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F9062BX	BX	Genteq	Standard	60	5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9842		Genteq	Standard	35	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB700Z100T370EABX	BX	PROLINE	Standard	70	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A243F075CF1H1		Genteq	Special	24000		75	1.75	Round	4.125	Electrolytic	1000	-40°C to 85°C
23C172F200CD1H1		Genteq	Special	1700		200	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
23J262F300EF1H1		Genteq	Special	2600		300	2.5	Round	4.125	Electrolytic	2000	-40°C to 105°C
23B353F060DG1H1		Genteq	Special	35000		60	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
PB400E000C440DA		PROLINE	Standard	40		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F192F150BH1H1		Genteq	Special	1900		150	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
23H901F450ED1H1		Genteq	Special	900		450	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C862F250FI1H1		Genteq	Special	8600		250	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
23B104F060FH1H1		Genteq	Special	10000 0		60	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F5330		Genteq	Special	25	4	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150Y075C370CA		PROLINE	Standard	15	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C772F200FF1H1		Genteq	Special	7700		200	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
27L1023		Genteq	Standard	4		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C643F060EF1H1		Genteq	Special	64000		60	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
23B173F060BH1H1		Genteq	Special	17000		60	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F6703BR	BR	Genteq	Standard	8		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150Z100S370CABX	BX	PROLINE	Standard	15	10	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6522BR	BR	Genteq	Standard	24		280	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L400BX	BX	Genteq	Standard	26	9	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F9681BX	BX	Genteq	Standard	30	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F183F100EH1H1		Genteq	Special	18000		100	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
PB1502050S370CA		PROLINE	Standard	15	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L6022		Genteq	Special	25		660	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F582F200FG1H1		Genteq	Special	5800		200	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F6602RC	RC	Genteq	Standard	15		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB400Z100S370DABX	BX	PROLINE	Standard	40	10	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A123F150FE1H1		Genteq	Special	12000		150	3	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F9051		Genteq	Special	25	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J132F350DG1H1		Genteq	Special	1300		350	2	Round	4.625	Electrolytic	2000	-40°C to 105°C
PB250Z075S370CABX	BX	PROLINE	Standard	25	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L558		Genteq	Standard	25	10	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F242F100BD1H1		Genteq	Special	2400		100	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
PB550E000T370DABX	BX	PROLINE	Standard	55		370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L724		Genteq	Standard	24	11	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B313F080EF1H1		Genteq	Special	31000		80	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
23C282F250ED1H1		Genteq	Special	2800		250	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F8052S	S	Genteq	Stock	100		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M902F200FE1H1		Genteq	Special	9000		200	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F8068BX	BX	Genteq	Standard	45		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9997BX	BX	Genteq	Standard	15	5	440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M402F300DI1H1		Genteq	Special	4000		300	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
23J192F300DG1H1		Genteq	Special	1900		300	2	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F9972		Genteq	Standard	50	10	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6920BX	BX	Genteq	Standard	16		540	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C222F200CE1H1		Genteq	Special	2200		200	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
PB200Z100S440DABX	BX	PROLINE	Standard	20	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F633F075FH1H1		Genteq	Special	63000		75	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F9667BX	BX	Genteq	Standard	25		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H691F450DE1H1		Genteq	Special	690		450	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
23A733F075FF1H1		Genteq	Special	73000		75	3	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9637		Genteq	Standard	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L349BX	BX	Genteq	Special	75		440	2.5	Round	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H252F300DG1H1		Genteq	Special	2500		300	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23F322F250EG1H1		Genteq	Special	3200		250	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
23F563F050FD1H1		Genteq	Special	56000		50	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
23B223F050CE1H1		Genteq	Special	22000		50	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
23A103F150FD1H1		Genteq	Special	10000		150	3	Round	3.125	Electrolytic	1000	-40°C to 85°C
23C522F150CG1H1		Genteq	Special	5200		150	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F9669		Genteq	Standard	40		440	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB550E000P370EA		PROLINE	Standard	55		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9735		Genteq	Standard	35	5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H122F400ED1H1		Genteq	Special	1200		400	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6923		Genteq	Special	32		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C163F100CH1H1		Genteq	Special	16000		100	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F9966BX	BX	Genteq	Standard	20	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B392F250FE1H1		Genteq	Special	3900		250	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6766		Genteq	Standard	7		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L543		Genteq	Standard	9.5	6.5	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6760BR	BR	Genteq	Standard	12		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1025		Genteq	Standard	6		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23A114F060FG1H1		Genteq	Special	11000 0		60	3	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F8068S	S	Genteq	Stock	45		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B602F200EI1H1		Genteq	Special	6000		200	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F6763		Genteq	Standard	10		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB400Y100C370DA		PROLINE	Standard	40	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L1030		Genteq	Standard	2.5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F382F150DG1H1		Genteq	Special	3800		150	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
23J442F250FE1H1		Genteq	Special	4400		250	3	Round	3.625	Electrolytic	2000	-40°C to 105°C
23F912F080BH1H1		Genteq	Special	9100		80	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F5465		Genteq	Special	30		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B173F080CG1H1		Genteq	Special	17000		80	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
23J182F350FD1H1		Genteq	Special	1800		350	3	Round	3.125	Electrolytic	2000	-40°C to 105°C
23F173F100FE1H1		Genteq	Special	17000		100	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
27L889		Genteq	Standard	45	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9639BX	BX	Genteq	Standard	35		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6082		Genteq	Special	20		660	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8095		Genteq	Standard	30	30	150	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B133F060BF1H1		Genteq	Special	13000		60	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
23J272F200CH1H1		Genteq	Special	2700		200	1.75	Round	5.125	Electrolytic	2000	-40°C to 105°C
23F132F200BI1H1		Genteq	Special	1300		200	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
23H831F350BH1H1		Genteq	Special	830		350	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
41L2221		Genteq	Stock	2.2		250	0.45	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23C154F060FJ1H1		Genteq	Special	15000 0		60	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
97F6725BX	BX	Genteq	Special	29		330	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F143F060CE1H1		Genteq	Special	14000		60	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
23B502F200FE1H1		Genteq	Special	5000		200	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
23H652F200EG1H1		Genteq	Special	6500		200	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6763RC	RC	Genteq	Standard	10		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H731F300CB1H1		Genteq	Special	730		300	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F9839BX	BX	Genteq	Standard	55	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB700Z050T440GA		PROLINE	Standard	70	5	440	2.5	Round	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6858BR	BR	Genteq	Standard	10		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6621BR	BR	Genteq	Standard	15		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F252F200DG1H1		Genteq	Special	2500		200	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
23A893F060EH1H1		Genteq	Special	89000		60	2.5	Round	5.125	Electrolytic	1000	-40°C to 85°C
PB030E000A370AABX	BX	PROLINE	Standard	3		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L213		Genteq	Standard	7.5		400	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5583BX	BX	Genteq	Standard	2		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A163F060CC1H1		Genteq	Special	16000		60	1.75	Round	2.625	Electrolytic	1000	-40°C to 85°C
97F9037BX	BX	Genteq	Standard	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6878BX	BX	Genteq	Standard	20	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350E000C440DAB X	BX	PROLINE	Standard	35		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6830BX	BX	Genteq	Special	35		280	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9864BX	BX	Genteq	Standard	35	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6518		Genteq	Standard	8		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9888		Genteq	Standard	35	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B902F080BG1H1		Genteq	Special	9000		80	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
23A312F150DC1H1		Genteq	Special	3100		150	2	Round	2.625	Electrolytic	1000	-40°C to 85°C
23J172F400EH1H1		Genteq	Special	1700		400	2.5	Round	5.125	Electrolytic	2000	-40°C to 105°C
27L907BR	BR	Genteq	Special	55		240	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C

PB800Z050T440EA		PROLINE	Standard	80	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9970BX	BX	Genteq	Standard	50	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8312		Genteq	Standard	90		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M203F200FL1H1		Genteq	Special	20000		200	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
97F5727		Genteq	Special	25	15	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9851S	S	Genteq	Stock	45	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200E000P240CABX	BX	PROLINE	Standard	20		240	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9884BX	BX	Genteq	Standard	45		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A433F050DE1H1		Genteq	Special	43000		50	2	Round	3.625	Electrolytic	1000	-40°C to 85°C
23D113F028CB1H1		Genteq	Special	11000		28	1.75	Round	2.125	Electrolytic	1000	-55°C to 85°C
23F251F250BB1H1		Genteq	Special	250		250	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F5452BX	BX	Genteq	Special	30	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C232F150CC1H1		Genteq	Special	2300		150	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
97F6670		Genteq	Special	38.5		370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D173F007BB1H1		Genteq	Special	17000		7.5	1.375	Round	2.125	Electrolytic	1000	-55°C to 85°C
97F9530BX	BX	Genteq	Standard	2.5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B172F250DE1H1		Genteq	Special	1700		250	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F5035BX	BX	Genteq	Special	5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C352F080BB1H1		Genteq	Special	3500		80	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
97F6703		Genteq	Standard	8		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M122F250BE1H1		Genteq	Special	1200		250	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F9994BX	BX	Genteq	Standard	30	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9044		Genteq	Special	15	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A442F080BB1H1		Genteq	Special	4400		80	1.375	Round	2.125	Electrolytic	1000	-40°C to 85°C
27L7000		Genteq	Standard	48		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F6682		Genteq	Special	31.5		420	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L4683		Genteq	Stock	0.068		3000	0.87	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23A333F080CI1H1		Genteq	Special	33000		80	1.75	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F6809BX	BX	Genteq	Special	14		280	1.5	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M232F200DC1H1		Genteq	Special	2300		200	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
23C133F075CD1H1		Genteq	Special	13000		75	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F9974		Genteq	Standard	55	10	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L695		Genteq	Standard	7.5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6726BX	BX	Genteq	Standard	30		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350Z100S370DA		PROLINE	Standard	35	10	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H511F350DB1H1		Genteq	Special	510		350	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F7050BX	BX	Genteq	Special	120		240	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B192F200CF1H1		Genteq	Special	1900		200	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23A184F050FI1H1		Genteq	Special	180000		50	3	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F8244		Genteq	Special	4		600	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9833		Genteq	Standard	30	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C252F250CH1H1		Genteq	Special	2500		250	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F9976BX	BX	Genteq	Standard	20	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1025BX	BX	Genteq	Standard	6		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9063		Genteq	Standard	60	7.5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F292F150CG1H1		Genteq	Special	2900		150	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
23F462F200EH1H1		Genteq	Special	4600		200	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F9640BX	BX	Genteq	Standard	35		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6514		Genteq	Special	20		170	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

PB500Z050S370DA		PROLINE	Standard	50	5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M102F350BG1H1		Genteq	Special	1000		350	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9895		Genteq	Standard	45	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200E000P440CABX	BX	PROLINE	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5276S	S	Genteq	Stock	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150Y100C440DA		PROLINE	Standard	15	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L541BX	BX	Genteq	Standard	14	10.5	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H153F200FL1H1		Genteq	Special	15000		200	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
23J122F350CH1H1		Genteq	Special	1200		350	1.75	Round	5.125	Electrolytic	2000	-40°C to 105°C
23M392F250CI1H1		Genteq	Special	3900		250	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6530BX	BX	Genteq	Standard	40		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H152F300CE1H1		Genteq	Special	1500		300	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6887RR	RR	Genteq	Standard	38	17	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150Z075S440DA		PROLINE	Standard	15	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J561F400DD1H1		Genteq	Special	560		400	2	Round	3.125	Electrolytic	2000	-40°C to 105°C
23C863F060EH1H1		Genteq	Special	86000		60	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
23M322F350EF1H1		Genteq	Special	3200		350	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
23C902F150FD1H1		Genteq	Special	9000		150	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
23A283F060DD1H1		Genteq	Special	28000		60	2	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F5482BX	BX	Genteq	Special	30	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A153F080CD1H1		Genteq	Special	15000		80	1.75	Round	3.125	Electrolytic	1000	-40°C to 85°C
23B802F075BE1H1		Genteq	Special	8000		75	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
23A503F050DF1H1		Genteq	Special	50000		50	2	Round	4.125	Electrolytic	1000	-40°C to 85°C
23M612F350FH1H1		Genteq	Special	6100		350	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB200E000P370CABX	BX	PROLINE	Standard	20		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A103F080BE1H1		Genteq	Special	10000		80	1.375	Round	3.625	Electrolytic	1000	-40°C to 85°C
27L443		Genteq	Standard	17	7	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H542F250FE1H1		Genteq	Special	5400		250	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
23F253F060DG1H1		Genteq	Special	25000		60	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
23A513F075FD1H1		Genteq	Special	51000		75	3	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F6622BX	BX	Genteq	Standard	24		400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F162F250DF1H1		Genteq	Special	1600		250	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F6836BX	BX	Genteq	Standard	48		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A452F100CB1H1		Genteq	Special	4500		100	1.75	Round	2.125	Electrolytic	1000	-40°C to 85°C
97F6927BX	BX	Genteq	Special	11.5	3	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB175E000A370DABX	BX	PROLINE	Standard	17.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F193F050BH1H1		Genteq	Special	19000		50	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F9003BX	BX	Genteq	Standard	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B203F100FE1H1		Genteq	Special	20000		100	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
23A253F080DE1H1		Genteq	Special	25000		80	2	Round	3.625	Electrolytic	1000	-40°C to 85°C
PB800Z050T440EABX	BX	PROLINE	Standard	80	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9015BX	BX	Genteq	Special	15	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6940RC	RC	Genteq	Standard	35		580	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6883BR	BR	Genteq	Standard	36	20	280	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M122F450ED1H1		Genteq	Special	1200		450	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
23B192F150BF1H1		Genteq	Special	1900		150	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
23B672F075BD1H1		Genteq	Special	6700		75	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F9974BX	BX	Genteq	Standard	55	10	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1003BR	BR	Genteq	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9008BX	BX	Genteq	Standard	45		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F601F250BE1H1		Genteq	Special	600		250	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
42L2472		Genteq	Stock	0.47		1200	0.91	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
PB500Y050D440GA		PROLINE	Standard	50	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C

PB125E000A370CAB X	BX	PROLINE	Standard	12.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H941F350BI1H1		Genteq	Special	940		350	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F5023		Genteq	Standard	30		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9603		Genteq	Standard	20		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F463F060EH1H1		Genteq	Special	46000		60	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
27L1026BX	BX	Genteq	Standard	8		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600Z100T440EABX	BX	PROLINE	Standard	60	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB800E000T370EA		PROLINE	Standard	80		370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9677		Genteq	Standard	25	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F103F075CD1H1		Genteq	Special	10000		75	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
PB400E000C370DAB X	BX	PROLINE	Standard	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A183F050DB1H1		Genteq	Special	18000		50	2	Round	2.125	Electrolytic	1000	-40°C to 85°C
27L6095		Genteq	Special	2		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J272F350EI1H1		Genteq	Special	2700		350	2.5	Round	5.625	Electrolytic	2000	-40°C to 105°C
PB700Z050T370EA		PROLINE	Standard	70	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M371F450DB1H1		Genteq	Special	370		450	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23M252F450EI1H1		Genteq	Special	2500		450	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23M472F200CH1H1		Genteq	Special	4700		200	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
23M132F400CG1H1		Genteq	Special	1300		400	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
23B104F075FL1H1		Genteq	Special	10000 0		75	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
97F6853BX	BX	Genteq	Special	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5818BX	BX	Genteq	Special	25	10	370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9741		Genteq	Standard	45	5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9758		Genteq	Standard	45	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B132F150CB1H1		Genteq	Special	1300		150	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
27L877BX	BX	Genteq	Standard	30	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J772F250FI1H1		Genteq	Special	7700		250	3	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F9836		Genteq	Special	30	4	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D283F020BH1H1		Genteq	Special	28000		20	1.375	Round	5.125	Electrolytic	1000	-55°C to 85°C
23B702F050BC1H1		Genteq	Special	7000		50	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
23B273F080EE1H1		Genteq	Special	27000		80	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
27L956		Genteq	Standard	10	10	370	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9882		Genteq	Standard	40	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600Z075T440EA		PROLINE	Standard	60	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L5538		Genteq	Special	60	10	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B412F080BC1H1		Genteq	Special	4100		80	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
27L1023BX	BX	Genteq	Standard	4		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250Y050C440DA		PROLINE	Standard	25	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6780		Genteq	Standard	29		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6925BR	BR	Genteq	Special	48		300	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M442F400FH1H1		Genteq	Special	4400		400	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
23H501F400BF1H1		Genteq	Special	500		400	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
23J212F250DF1H1		Genteq	Special	2100		250	2	Round	4.125	Electrolytic	2000	-40°C to 105°C
PB300E000P370DA		PROLINE	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J951F350CF1H1		Genteq	Special	950		350	1.75	Round	4.125	Electrolytic	2000	-40°C to 105°C
23C104F060EI1H1		Genteq	Special	10000 0		60	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
23A343F050CE1H1		Genteq	Special	34000		50	1.75	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F6946BX	BX	Genteq	Standard	21		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M222F350CI1H1		Genteq	Special	2200		350	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F572F075BD1H1		Genteq	Special	5700		75	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
23C123F100CF1H1		Genteq	Special	12000		100	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C

97F8072		Genteq	Standard	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L497		Genteq	Standard	80		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8046BX	BX	Genteq	Standard	70		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A672F150ED1H1		Genteq	Special	6700		150	2.5	Round	3.125	Electrolytic	1000	-40°C to 85°C
23J382F200DI1H1		Genteq	Special	3800		200	2	Round	5.625	Electrolytic	2000	-40°C to 105°C
PB450Z100S370EA		PROLINE	Standard	45	10	370	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B292F250DI1H1		Genteq	Special	2900		250	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9626		Genteq	Standard	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9595BX	BX	Genteq	Standard	6		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6871		Genteq	Standard	12		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D393F020CF1H1		Genteq	Special	39000		20	1.75	Round	4.125	Electrolytic	1000	-55°C to 85°C
27L7007BX	BX	Genteq	Special	18	8	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23H162F200BF1H1		Genteq	Special	1600		200	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
23A682F100BF1H1		Genteq	Special	6800		100	1.375	Round	4.125	Electrolytic	1000	-40°C to 85°C
23C123F080DC1H1		Genteq	Special	12000		80	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
23D663F016CI1H1		Genteq	Special	66000		16	3	Round	8.625	Electrolytic	1000	-55°C to 85°C
23F361F250BC1H1		Genteq	Special	360		250	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
23B332F200DH1H1		Genteq	Special	3300		200	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB300Y100C370DA		PROLINE	Standard	30	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A902F060BC1H1		Genteq	Special	9000		60	1.375	Round	2.625	Electrolytic	1000	-40°C to 85°C
23A613F060DI1H1		Genteq	Special	61000		60	2	Round	5.625	Electrolytic	1000	-40°C to 85°C
23B282F200CI1H1		Genteq	Special	2800		200	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9841BX	BX	Genteq	Standard	45	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Z075S370CA		PROLINE	Standard	20	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB200E000A440EA		PROLINE	Standard	20		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H172F350CI1H1		Genteq	Special	1700		350	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23B452F250FF1H1		Genteq	Special	4500		250	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
23C703F100FL1H1		Genteq	Special	70000		100	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
97F9002S	S	Genteq	Stock	10		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A433F080DI1H1		Genteq	Special	43000		80	2	Round	5.625	Electrolytic	1000	-40°C to 85°C
23B333F075EE1H1		Genteq	Special	33000		75	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
27L850		Genteq	Standard	11.5	7	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L7003BR	BR	Genteq	Standard	26		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
PB150Z050S440CA		PROLINE	Standard	15	5	440	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5023BX	BX	Genteq	Standard	30		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8055BX	BX	Genteq	Standard	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6956		Genteq	Standard	22.5		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B901F200BE1H1		Genteq	Special	900		200	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6746RC	RC	Genteq	Standard	12		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB030E000P370CA		PROLINE	Standard	3		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C212F250DE1H1		Genteq	Special	2100		250	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
23F422F100DC1H1		Genteq	Special	4200		100	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F6778		Genteq	Standard	45		330	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M142F400DF1H1		Genteq	Special	1400		400	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F9437BX	BX	Genteq	Standard	15	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L570S	S	Genteq	Stock	5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L442BX	BX	Genteq	Standard	28	7	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L907RC	RC	Genteq	Special	55		240	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F103F080BI1H1		Genteq	Special	10000		80	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
27L5180BX	BX	Genteq	Standard	35	10	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J661F300BE1H1		Genteq	Special	660		300	1.375	Round	3.625	Electrolytic	2000	-40°C to 105°C

27L967BX	BX	Genteq	Standard	45	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M402F350FE1H1		Genteq	Special	4000		350	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
23C242F150BF1H1		Genteq	Special	2400		150	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
23J182F250CF1H1		Genteq	Special	1800		250	1.75	Round	4.125	Electrolytic	2000	-40°C to 105°C
27L853		Genteq	Standard	24	10	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L956BX	BX	Genteq	Standard	10	10	370	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6621BX	BX	Genteq	Standard	15		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9616BX	BX	Genteq	Standard	40		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H531F450BI1H1		Genteq	Special	530		450	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9899		Genteq	Standard	35	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250Y050C440DAB X	BX	PROLINE	Standard	25	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B602F100BI1H1		Genteq	Special	6000		100	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B113F100ED1H1		Genteq	Special	11000		100	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F6924BX	BX	Genteq	Standard	13		540	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D273F020CD1H1		Genteq	Special	27000		20	1.75	Round	3.125	Electrolytic	1000	-55°C to 85°C
PB550E000T440EA		PROLINE	Standard	55		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M592F300EH1H1		Genteq	Special	5900		300	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
23B232F150BG1H1		Genteq	Special	2300		150	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
23M642F200EE1H1		Genteq	Special	6400		200	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
23B212F100BC1H1		Genteq	Special	2100		100	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F8066BX	BX	Genteq	Standard	35		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9080		Genteq	Standard	12.5		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J102F200BE1H1		Genteq	Special	1000		200	1.375	Round	3.625	Electrolytic	2000	-40°C to 105°C
23H132F400CI1H1		Genteq	Special	1300		400	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23J113F200FL1H1		Genteq	Special	11000		200	3	Round	8.625	Electrolytic	2000	-40°C to 105°C
PB060E000A370BABX	BX	PROLINE	Standard	6		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D123F035BF1H1		Genteq	Special	12000		35	1.375	Round	4.125	Electrolytic	1000	-55°C to 85°C
23H741F350BG1H1		Genteq	Special	740		350	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
27L55		Genteq	Standard	35	20	280	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6673		Genteq	Special	14		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M431F350BC1H1		Genteq	Special	430		350	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
23B903F050FG1H1		Genteq	Special	90000		50	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
23J222F400FG1H1		Genteq	Special	2200		400	3	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F8061		Genteq	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200E000A440EAS	S	PROLINE	Stock	20		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9022		Genteq	Special	35	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M731F400CD1H1		Genteq	Special	730		400	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
23F172F150DC1H1		Genteq	Special	1700		150	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F6784BX	BX	Genteq	Standard	36		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L862RR	RR	Genteq	Standard	35	24	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB400Y075C440EA		PROLINE	Standard	40	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J142F300DE1H1		Genteq	Special	1400		300	2	Round	3.625	Electrolytic	2000	-40°C to 105°C
23B103F080DC1H1		Genteq	Special	10000		80	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
23H441F450BG1H1		Genteq	Special	440		450	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6935		Genteq	Special	10.5		540	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J431F300BC1H1		Genteq	Special	430		300	1.375	Round	2.625	Electrolytic	2000	-40°C to 105°C
40L6101		Genteq	Stock	1		600	0.67	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
97F6884BR	BR	Genteq	Standard	33	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M123F300FL1H1		Genteq	Special	12000		300	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
23M601F400BF1H1		Genteq	Special	600		400	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
23A842F080BD1H1		Genteq	Special	8400		80	1.375	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F9042		Genteq	Standard	55		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B113F100DG1H1		Genteq	Special	11000		100	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
23H112F400CH1H1		Genteq	Special	1100		400	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C

PB150Z100S440DABX	BX	PROLINE	Standard	15	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B123F060CC1H1		Genteq	Special	12000		60	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
23H522F300E11H1		Genteq	Special	5200		300	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23J472F250EH1H1		Genteq	Special	4700		250	2.5	Round	5.125	Electrolytic	2000	-40°C to 105°C
23M102F300BE1H1		Genteq	Special	1000		300	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
23J811F350CE1H1		Genteq	Special	810		350	1.75	Round	3.625	Electrolytic	2000	-40°C to 105°C
23J421F400DC1H1		Genteq	Special	420		400	2	Round	2.625	Electrolytic	2000	-40°C to 105°C
23C903F075FJ1H1		Genteq	Special	90000		75	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
27L7005		Genteq	Special	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F6882BX	BX	Genteq	Standard	24	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6601BX	BX	Genteq	Standard	10		400	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB075E000P440CABX	BX	PROLINE	Standard	7.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A123F075CC1H1		Genteq	Special	12000		75	1.75	Round	2.625	Electrolytic	1000	-40°C to 85°C
97F6603		Genteq	Special	24		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M122F250DB1H1		Genteq	Special	1200		250	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
23M342F200CF1H1		Genteq	Special	3400		200	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
23B453F080FF1H1		Genteq	Special	45000		80	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
PB200Z075S440DA		PROLINE	Standard	20	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A223F080CF1H1		Genteq	Special	22000		80	1.75	Round	4.125	Electrolytic	1000	-40°C to 85°C
23B122F200BG1H1		Genteq	Special	1200		200	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
27L428BX	BX	Genteq	Standard	24	15	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A222F150DB1H1		Genteq	Special	2200		150	2	Round	2.125	Electrolytic	1000	-40°C to 85°C
23C541F250BC1H1		Genteq	Special	540		250	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
23M232F400FD1H1		Genteq	Special	2300		400	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C132F250DC1H1		Genteq	Special	1300		250	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
27L551		Genteq	Standard	20		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9606BX	BX	Genteq	Standard	25		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F114F050FH1H1		Genteq	Special	110000		50	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
PB300E000C440DAS	S	PROLINE	Stock	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5450BX	BX	Genteq	Special	30	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9897		Genteq	Standard	60	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8037S	S	Genteq	Stock	25		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB550Z050T370DA		PROLINE	Standard	55	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6812BX	BX	Genteq	Standard	17.5		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F812F100DF1H1		Genteq	Special	8100		100	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
23B542F200EH1H1		Genteq	Special	5400		200	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F9047		Genteq	Standard	20	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C123F150FE1H1		Genteq	Special	12000		150	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F6907BX	BX	Genteq	Special	10		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9437		Genteq	Standard	15	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
25L752		Genteq	Special	25	4	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H501F250BB1H1		Genteq	Special	500		250	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
PB175E000A370DA		PROLINE	Standard	17.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6770BX	BX	Genteq	Standard	17.5		330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A213F050BF1H1		Genteq	Special	21000		50	1.375	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F5388		Genteq	Standard	12.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A532F150CG1H1		Genteq	Special	5300		150	1.75	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F5159		Genteq	Standard	40		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Z075S440EABX	BX	PROLINE	Standard	35	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B552F080BD1H1		Genteq	Special	5500		80	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F9045		Genteq	Special	15	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C203F150FI1H1		Genteq	Special	20000		150	3	Round	5.625	Electrolytic	1000	-45°C to 95°C

97F6930BR	BR	Genteq	Standard	10		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5330BX	BX	Genteq	Special	25	4	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB450Z075S370DABX	BX	PROLINE	Standard	45	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9635S	S	Genteq	Stock	30		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B493F060EF1H1		Genteq	Special	49000		60	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
23H362F200CH1H1		Genteq	Special	3600		200	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
23A323F050BI1H1		Genteq	Special	32000		50	1.375	Round	5.625	Electrolytic	1000	-40°C to 85°C
23M162F400DG1H1		Genteq	Special	1600		400	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J202F300CI1H1		Genteq	Special	2000		300	1.75	Round	5.625	Electrolytic	2000	-40°C to 105°C
23B723F060FF1H1		Genteq	Special	72000		60	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
23M672F350FI1H1		Genteq	Special	6700		350	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9642BX	BX	Genteq	Standard	40		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A913F080FH1H1		Genteq	Special	91000		80	3	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F8048BX	BX	Genteq	Standard	80		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1050		Genteq	Standard	25	10	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B563F075EI1H1		Genteq	Special	56000		75	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
23F661F250CC1H1		Genteq	Special	660		250	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
27L7001		Genteq	Standard	10		400	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23C143F150FF1H1		Genteq	Special	14000		150	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F8240		Genteq	Special	1.5		600	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
40L3331		Genteq	Stock	3.3		400	0.69	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
97F9951		Genteq	Standard	40	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6858		Genteq	Standard	10		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H182F450FF1H1		Genteq	Special	1800		450	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
27L7005BX	BX	Genteq	Special	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F9024		Genteq	Special	40	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150E000P440CA		PROLINE	Standard	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F723F080FL1H1		Genteq	Special	72000		80	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
PB650E000T370DA		PROLINE	Standard	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B162F200CE1H1		Genteq	Special	1600		200	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
PB800Z100T440EA		PROLINE	Standard	80	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9741BX	BX	Genteq	Standard	45	5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M312F200DD1H1		Genteq	Special	3100		200	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23M701F350BE1H1		Genteq	Special	700		350	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB450Z075T440DA		PROLINE	Standard	45	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J632F200EI1H1		Genteq	Special	6300		200	2.5	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F9043		Genteq	Standard	60		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B113F060BE1H1		Genteq	Special	11000		60	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
23C463F060DG1H1		Genteq	Special	46000		60	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F6757BX	BX	Genteq	Standard	34		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D612F028BB1H1		Genteq	Special	6100		28	1.375	Round	2.125	Electrolytic	1000	-55°C to 85°C
23M401F400CB1H1		Genteq	Special	400		400	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23C882F100BH1H1		Genteq	Special	8800		100	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
23J252F400FH1H1		Genteq	Special	2500		400	3	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F9972BX	BX	Genteq	Standard	50	10	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5362BX	BX	Genteq	Special	25	7.5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H132F350CG1H1		Genteq	Special	1300		350	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB500Y075D440GABX	BX	PROLINE	Standard	50	7.5	440	2	Oval	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C603F050DH1H1		Genteq	Special	60000		50	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F6759		Genteq	Standard	24		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350E000S370CABX	BX	PROLINE	Standard	35		370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L4221		Genteq	Stock	2.2		400	0.69	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C

27L570BX	BX	Genteq	Standard	5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6921		Genteq	Standard	26		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6522		Genteq	Standard	24		280	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D173F016BD1H1		Genteq	Special	17000		16	1.375	Round	3.125	Electrolytic	1000	-55°C to 85°C
97F6869BX	BX	Genteq	Standard	42		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5054		Genteq	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6708		Genteq	Standard	13		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L727RR	RR	Genteq	Standard	45	19	300	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D663F007CE1H1		Genteq	Special	66000		7.5	1.75	Round	3.625	Electrolytic	1000	-55°C to 85°C
97F6509		Genteq	Standard	38		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D292F055BB1H1		Genteq	Special	2900		55	1.375	Round	2.125	Electrolytic	1000	-55°C to 85°C
97F6680BR	BR	Genteq	Special	24		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6606BX	BX	Genteq	Standard	10		400	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A592F150DF1H1		Genteq	Special	5900		150	2	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9319BX	BX	Genteq	Special	55	7.5	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6684BX	BX	Genteq	Special	12.5		440	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L2152		Genteq	Stock	0.15		1200	0.67	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F5205BX	BX	Genteq	Special	35		440	2.5	Round	3.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
40L6682		Genteq	Stock	0.68		600	0.55	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
23A104F050FE1H1		Genteq	Special	100000		50	3	Round	3.625	Electrolytic	1000	-40°C to 85°C
PB400E000C440DABX	BX	PROLINE	Standard	40		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L1003BX	BX	Genteq	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5670		Genteq	Special	40	7.5	240	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9038BX	BX	Genteq	Standard	17.5		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D532F055CB1H1		Genteq	Special	5300		55	1.75	Round	2.125	Electrolytic	1000	-55°C to 85°C
23F813F050FF1H1		Genteq	Special	81000		50	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
27L1045		Genteq	Standard	60		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C263F100EF1H1		Genteq	Special	26000		100	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
23H132F450EF1H1		Genteq	Special	1300		450	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
41L4100		Genteq	Stock	10		400	1.18	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F8044S	S	Genteq	Stock	60		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M701F400DC1H1		Genteq	Special	700		400	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
27L967		Genteq	Standard	45	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B762F150FD1H1		Genteq	Special	7600		150	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB550Z050T440EA		PROLINE	Standard	55	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB250E000P440DABX	BX	PROLINE	Standard	25		440	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C672F200FE1H1		Genteq	Special	6700		200	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
23B183F050BH1H1		Genteq	Special	18000		50	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
27L470BX	BX	Genteq	Standard	25	10	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C213F080CG1H1		Genteq	Special	21000		80	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
23F232F150DD1H1		Genteq	Special	2300		150	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
23F452F080CB1H1		Genteq	Special	4500		80	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F6534BX	BX	Genteq	Special	28		170	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A911F150BB1H1		Genteq	Special	910		150	1.375	Round	2.125	Electrolytic	1000	-40°C to 85°C
27L514BX	BX	Genteq	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9614BX	BX	Genteq	Standard	40		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6907		Genteq	Special	10		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9630		Genteq	Standard	20		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB800Z075T370EA		PROLINE	Standard	80	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C

PB500Z100S370EABX	BX	PROLINE	Standard	50	10	370	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C173F060BF1H1		Genteq	Special	17000		60	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F6683		Genteq	Special	21		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB040E000A370AA		PROLINE	Standard	4		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6926BX	BX	Genteq	Standard	26		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D593F016CH1H1		Genteq	Special	59000		16	1.75	Round	5.125	Electrolytic	1000	-55°C to 85°C
23F742F100CG1H1		Genteq	Special	7400		100	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
23J401F250BB1H1		Genteq	Special	400		250	1.375	Round	2.125	Electrolytic	2000	-40°C to 105°C
27L907BX	BX	Genteq	Special	55		240	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B113F100CI1H1		Genteq	Special	11000		100	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B123F080BI1H1		Genteq	Special	12000		80	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
23F753F050EH1H1		Genteq	Special	75000		50	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
23F403F075FE1H1		Genteq	Special	40000		75	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
23M112F300BF1H1		Genteq	Special	1100		300	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
27L576		Genteq	Special	20	8	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200E000S440CA		PROLINE	Standard	20		440	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D513F020CH1H1		Genteq	Special	51000		20	1.75	Round	5.125	Electrolytic	1000	-55°C to 85°C
97F6695		Genteq	Special	6.5		480	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6777RC	RC	Genteq	Special	35		330	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB300E000A370EABX	BX	PROLINE	Standard	30		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6925RC	RC	Genteq	Special	48		300	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450E000S370DA		PROLINE	Standard	45		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F522F200EI1H1		Genteq	Special	5200		200	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
23A153F050BD1H1		Genteq	Special	15000		50	1.375	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F8056BX	BX	Genteq	Standard	5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6902		Genteq	Special	55		240	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M301F450BD1H1		Genteq	Special	300		450	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6727BR	BR	Genteq	Standard	32		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6919		Genteq	Standard	16		540	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A682F150CI1H1		Genteq	Special	6800		150	1.75	Round	5.625	Electrolytic	1000	-40°C to 85°C
27L5200		Genteq	Standard	50	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H172F450EH1H1		Genteq	Special	1700		450	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB200Z075S440DABX	BX	PROLINE	Standard	20	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B712F250FJ1H1		Genteq	Special	7100		250	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
97F6773		Genteq	Standard	22.5		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9845BX	BX	Genteq	Standard	40	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C681F250CB1H1		Genteq	Special	680		250	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
97F6778RC	RC	Genteq	Standard	45		330	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B263F060DE1H1		Genteq	Special	26000		60	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
23F502F200FF1H1		Genteq	Special	5000		200	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
42L3152		Genteq	Stock	0.15		2000	0.77	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23B123F075CD1H1		Genteq	Special	12000		75	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F9817		Genteq	Standard	60	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8036		Genteq	Standard	15		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F302F100DB1H1		Genteq	Special	3000		100	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
23B533F050EF1H1		Genteq	Special	53000		50	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
23M122F400DE1H1		Genteq	Special	1200		400	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
23C144F060FI1H1		Genteq	Special	14000 0		60	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB550Z100T440EA		PROLINE	Standard	55	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A114F050EH1H1		Genteq	Special	11000 0		50	2.5	Round	5.125	Electrolytic	1000	-40°C to 85°C
23M172F250BG1H1		Genteq	Special	1700		250	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
23H292F200CF1H1		Genteq	Special	2900		200	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C

25L6755BR	BR	Genteq	Standard	20	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350Y050C370DA		PROLINE	Standard	35	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9054BX	BX	Genteq	Special	30	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F802F150EI1H1		Genteq	Special	8000		150	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F6801		Genteq	Standard	6		280	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B682F150DI1H1		Genteq	Special	6800		150	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9758BX	BX	Genteq	Standard	45	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5814		Genteq	Special	25	5	370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9071BX	BX	Genteq	Special	35		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J771F300BF1H1		Genteq	Special	770		300	1.375	Round	4.125	Electrolytic	2000	-40°C to 105°C
PB800Z050T370EABX	BX	PROLINE	Standard	80	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8076		Genteq	Special	50		480	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B782F200FH1H1		Genteq	Special	7800		200	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
23J112F300BI1H1		Genteq	Special	1100		300	1.375	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F8245BX	BX	Genteq	Standard	5		600	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L947BX	BX	Genteq	Standard	45	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5115		Genteq	Special	35		440	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8056		Genteq	Standard	5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B453F060DI1H1		Genteq	Special	45000		60	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F5481BX	BX	Genteq	Special	25	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB450E000C440EABX	BX	PROLINE	Standard	45		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB200E000A370DABX	BX	PROLINE	Standard	20		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9451BX	BX	Genteq	Standard	20	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F222F250DH1H1		Genteq	Special	2200		250	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
23J162F350DI1H1		Genteq	Special	1600		350	2	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F6771		Genteq	Standard	18		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J981F300CD1H1		Genteq	Special	980		300	1.75	Round	3.125	Electrolytic	2000	-40°C to 105°C
97F6696BX	BX	Genteq	Special	38		300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8049		Genteq	Standard	85		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B203F060CE1H1		Genteq	Special	20000		60	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6762		Genteq	Standard	11		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9998BX	BX	Genteq	Standard	15	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1054S	S	Genteq	Stock	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F603F080FJ1H1		Genteq	Special	60000		80	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
23F672F200FH1H1		Genteq	Special	6700		200	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F8043		Genteq	Standard	55		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5501		Genteq	Special	25	5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F203F075CH1H1		Genteq	Special	20000		75	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
23J212F350EG1H1		Genteq	Special	2100		350	2.5	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F6516BX	BX	Genteq	Standard	22.5		280	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB050E000A370AA		PROLINE	Standard	5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5670BX	BX	Genteq	Special	40	7.5	240	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6812RC	RC	Genteq	Standard	17.5		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450E000C370DA		PROLINE	Standard	45		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A473F080FD1H1		Genteq	Special	47000		80	3	Round	3.125	Electrolytic	1000	-40°C to 85°C
PB300E000C370CA		PROLINE	Standard	30		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M401F450CC1H1		Genteq	Special	400		450	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F6606		Genteq	Standard	10		400	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F6836RC	RC	Genteq	Standard	48		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C173F080CF1H1		Genteq	Special	17000		80	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
27L176		Genteq	Special	7.5		540	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L865BR	BR	Genteq	Standard	15	6	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F772F200FJ1H1		Genteq	Special	7700		200	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
PB550Z075T440EAS	S	PROLINE	Stock	55	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
25L2754		Genteq	Standard	35	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B843F080FL1H1		Genteq	Special	84000		80	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
97F9996		Genteq	Standard	40	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H482F400FL1H1		Genteq	Special	4800		400	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
23D223F035CF1H1		Genteq	Special	22000		35	1.75	Round	4.125	Electrolytic	1000	-55°C to 85°C
PB600E000D440HA		PROLINE	Standard	60		440	2	Oval	4.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M232F400EF1H1		Genteq	Special	2300		400	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F5337		Genteq	Standard	4		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB800Z100T440EABX	BX	PROLINE	Standard	80	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H481F450CD1H1		Genteq	Special	480		450	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
40L3221		Genteq	Stock	2.2		400	0.56	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
27L591BX	BX	Genteq	Standard	35	15	300	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9152		Genteq	Standard	40		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M143F200FH1H1		Genteq	Special	14000		200	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
23F632F100CF1H1		Genteq	Special	6300		100	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
23C303F060CF1H1		Genteq	Special	30000		60	1.75	Round	4.125	Electrolytic	1000	-45°C to 95°C
23C183F100CI1H1		Genteq	Special	18000		100	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6765BX	BX	Genteq	Standard	6		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H122F300BH1H1		Genteq	Special	1200		300	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23H102F350CE1H1		Genteq	Special	1000		350	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
23A164F050FH1H1		Genteq	Special	16000 0		50	3	Round	5.125	Electrolytic	1000	-40°C to 85°C
23A842F150EE1H1		Genteq	Special	8400		150	2.5	Round	3.625	Electrolytic	1000	-40°C to 85°C
23J861F300BG1H1		Genteq	Special	860		300	1.375	Round	4.625	Electrolytic	2000	-40°C to 105°C
23F173F080CH1H1		Genteq	Special	17000		80	1.75	Round	5.125	Electrolytic	1000	-55°C to 105°C
23M182F250CD1H1		Genteq	Special	1800		250	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
42L1201		Genteq	Stock	2		850	1.12	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23B102F250DC1H1		Genteq	Special	1000		250	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
27L402BR	BR	Genteq	Standard	24	8	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B143F080CF1H1		Genteq	Special	14000		80	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23J492F350FL1H1		Genteq	Special	4900		350	3	Round	8.625	Electrolytic	2000	-40°C to 105°C
23F223F075ED1H1		Genteq	Special	22000		75	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F6745BX	BX	Genteq	Standard	21		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J522F300FH1H1		Genteq	Special	5200		300	3	Round	5.125	Electrolytic	2000	-40°C to 105°C
23M212F450FE1H1		Genteq	Special	2100		450	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
23A352F100BC1H1		Genteq	Special	3500		100	1.375	Round	2.625	Electrolytic	1000	-40°C to 85°C
97F6865BX	BX	Genteq	Standard	35		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L3473		Genteq	Stock	0.047		2000	0.57	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23C123F200FJ1H1		Genteq	Special	12000		200	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
97F6518BX	BX	Genteq	Standard	8		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8044		Genteq	Standard	60		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5583		Genteq	Standard	2		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Z050S370CA		PROLINE	Standard	30	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B113F200FL1H1		Genteq	Special	11000		200	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
23A472F100BD1H1		Genteq	Special	4700		100	1.375	Round	3.125	Electrolytic	1000	-40°C to 85°C
23M902F250FG1H1		Genteq	Special	9000		250	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB400Z075S370DABX	BX	PROLINE	Standard	40	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB200E000S440CAB X	BX	PROLINE	Standard	20		440	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9965		Genteq	Standard	15	10	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23C323F080EE1H1		Genteq	Special	32000		80	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F8036S	S	Genteq	Stock	15		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9365		Genteq	Special	25		480	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B373F050ED1H1		Genteq	Special	37000		50	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB300E000C240CA		PROLINE	Standard	30		240	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M302F300ED1H1		Genteq	Special	3000		300	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
23M802F250FF1H1		Genteq	Special	8000		250	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
PB350Y100C370DABX	BX	PROLINE	Standard	35	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9005		Genteq	Standard	20		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F573F080FI1H1		Genteq	Special	57000		80	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C203F080DE1H1		Genteq	Special	20000		80	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
23C593F060DI1H1		Genteq	Special	59000		60	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6934BX	BX	Genteq	Standard	26		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D333F020CE1H1		Genteq	Special	33000		20	1.75	Round	3.625	Electrolytic	1000	-55°C to 85°C
PB150Y075C440CABX	BX	PROLINE	Standard	15	7.5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9041BX	BX	Genteq	Standard	35		440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B343F075DI1H1		Genteq	Special	34000		75	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9678BX	BX	Genteq	Standard	25	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C222F200DD1H1		Genteq	Special	2200		200	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
27L590BR	BR	Genteq	Standard	24	11	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B803F050FF1H1		Genteq	Special	80000		50	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
23F592F080DB1H1		Genteq	Special	5900		80	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
23F352F080BC1H1		Genteq	Special	3500		80	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
23M701F450DD1H1		Genteq	Special	700		450	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
PB175E000P370CA		PROLINE	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9608S	S	Genteq	Stock	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9966		Genteq	Standard	20	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H762F300FI1H1		Genteq	Special	7600		300	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
23D323F016BH1H1		Genteq	Special	32000		16	1.375	Round	5.125	Electrolytic	1000	-55°C to 85°C
23B103F100CH1H1		Genteq	Special	10000		100	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F9451BR	BR	Genteq	Standard	20	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H192F350EE1H1		Genteq	Special	1900		350	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6537BR	BR	Genteq	Standard	24		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6945		Genteq	Standard	24		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F703F050FE1H1		Genteq	Special	70000		50	3	Round	3.625	Electrolytic	1000	-55°C to 105°C
23B313F100FH1H1		Genteq	Special	31000		100	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB200Y050C440CA		PROLINE	Standard	20	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J732F300FL1H1		Genteq	Special	7300		300	3	Round	8.625	Electrolytic	2000	-40°C to 105°C
27L695BX	BX	Genteq	Standard	7.5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B403F060DH1H1		Genteq	Special	40000		60	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
23C212F150BE1H1		Genteq	Special	2100		150	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F9637BX	BX	Genteq	Standard	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5067BX	BX	Genteq	Standard	12.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9201		Genteq	Standard	4		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C153F080CE1H1		Genteq	Special	15000		80	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
23F542F150FD1H1		Genteq	Special	5400		150	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
PB750E000T370EABX	BX	PROLINE	Standard	75		370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F383F080FF1H1		Genteq	Special	38000		80	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F6538BR	BR	Genteq	Standard	35		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A673F060FD1H1		Genteq	Special	67000		60	3	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F9142BX	BX	Genteq	Standard	17.5	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H212F300DF1H1		Genteq	Special	2100		300	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
23C162F250CE1H1		Genteq	Special	1600		250	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C

23A104F060FF1H1		Genteq	Special	10000 0		60	3	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F6602		Genteq	Standard	15		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L600BX	BX	Genteq	Standard	39	13	330	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6930		Genteq	Standard	10		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9828BX	BX	Genteq	Standard	30	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L757BX	BX	Genteq	Special	55		440	2	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B223F050DD1H1		Genteq	Special	22000		50	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
23M272F350EE1H1		Genteq	Special	2700		350	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
27L987		Genteq	Standard	3		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9834		Genteq	Standard	35	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L428		Genteq	Standard	24	15	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L705		Genteq	Standard	42	22	280	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H132F250DC1H1		Genteq	Special	1300		250	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
23C292F200CG1H1		Genteq	Special	2900		200	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
23H172F250BI1H1		Genteq	Special	1700		250	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
23M322F450FH1H1		Genteq	Special	3200		450	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9044BX	BX	Genteq	Special	15	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F213F060DF1H1		Genteq	Special	21000		60	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
PB500E000C370DAS	S	PROLINE	Stock	50		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C572F100DB1H1		Genteq	Special	5700		100	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23C282F200DE1H1		Genteq	Special	2800		200	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
23C504F075FE1H1		Genteq	Special	50000		75	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F5914BX	BX	Genteq	Standard	32.5		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J242F200CG1H1		Genteq	Special	2400		200	1.75	Round	4.625	Electrolytic	2000	-40°C to 105°C
23M401F300BB1H1		Genteq	Special	400		300	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
23B132F150BD1H1		Genteq	Special	1300		150	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
23J671F200BC1H1		Genteq	Special	670		200	1.375	Round	2.625	Electrolytic	2000	-40°C to 105°C
23M692F350FJ1H1		Genteq	Special	6900		350	3	Round	5.875	Electrolytic	2000	-40°C to 85°C
23C143F150EI1H1		Genteq	Special	14000		150	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
23M153F250FL1H1		Genteq	Special	15000		250	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
97F9827BX	BX	Genteq	Standard	25	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB450Z100S370EABX	BX	PROLINE	Standard	45	10	370	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5705		Genteq	Standard	5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D133F055CF1H1		Genteq	Special	13000		55	1.75	Round	4.125	Electrolytic	1000	-55°C to 85°C
97F9805BX	BX	Genteq	Standard	45		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1022		Genteq	Standard	3		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M771F300BD1H1		Genteq	Special	770		300	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9814		Genteq	Standard	20	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F442F100CD1H1		Genteq	Special	4400		100	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
23M202F400EE1H1		Genteq	Special	2000		400	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
23A723F100FL1H1		Genteq	Special	72000		100	3	Round	8.625	Electrolytic	1000	-40°C to 85°C
97F9735BX	BX	Genteq	Standard	35	5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M172F250DC1H1		Genteq	Special	1700		250	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
23F172F150CD1H1		Genteq	Special	1700		150	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F6764BR	BR	Genteq	Standard	5		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C473F080FE1H1		Genteq	Special	47000		80	3	Round	3.625	Electrolytic	1000	-45°C to 95°C
PB250Z050S370CABX	BX	PROLINE	Standard	25	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D183F028BG1H1		Genteq	Special	18000		28	1.375	Round	4.625	Electrolytic	1000	-55°C to 85°C
23B163F100EF1H1		Genteq	Special	16000		100	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
PB450Y050C440EAB X	BX	PROLINE	Standard	45	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H742F200EH1H1		Genteq	Special	7400		200	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
23F481F250BD1H1		Genteq	Special	480		250	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
23H321F450BE1H1		Genteq	Special	320		450	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
PB350E000A370EAS	S	PROLINE	Stock	35		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C

23B383F075FD1H1		Genteq	Special	38000		75	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
23F242F250DI1H1		Genteq	Special	2400		250	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C381F250BB1H1		Genteq	Special	380		250	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
23A103F100BI1H1		Genteq	Special	10000		100	1.375	Round	5.625	Electrolytic	1000	-40°C to 85°C
23F771F200DB1H1		Genteq	Special	770		200	2	Round	2.125	Electrolytic	1000	-55°C to 105°C
PB700Z075T440GA		PROLINE	Standard	70	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L589BR	BR	Genteq	Standard	10	5	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B353F060CI1H1		Genteq	Special	35000		60	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
27L6094BX	BX	Genteq	Special	3		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J242F300DI1H1		Genteq	Special	2400		300	2	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F8218BX	BX	Genteq	Standard	30		240	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C223F060BH1H1		Genteq	Special	22000		60	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F8090		Genteq	Standard	20		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L566S	S	Genteq	Stock	7.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB700Z100T440EA		PROLINE	Standard	70	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6952RC	RC	Genteq	Standard	36		540	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F343F050DF1H1		Genteq	Special	34000		50	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F9318BX	BX	Genteq	Special	55	5	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350E000P240DA		PROLINE	Standard	35		240	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100E000A440CA		PROLINE	Standard	10		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9059BX	BX	Genteq	Special	55	5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J302F250EE1H1		Genteq	Special	3000		250	2.5	Round	3.625	Electrolytic	2000	-40°C to 105°C
23J991F400CI1H1		Genteq	Special	990		400	1.75	Round	5.625	Electrolytic	2000	-40°C to 105°C
23M202F350CH1H1		Genteq	Special	2000		350	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F6857RC	RC	Genteq	Standard	8		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B123F050DB1H1		Genteq	Special	12000		50	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F6871RC	RC	Genteq	Standard	12		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB040E000A440AABX	BX	PROLINE	Standard	4		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F123F075BI1H1		Genteq	Special	12000		75	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
23M342F400EI1H1		Genteq	Special	3400		400	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23C373F080EF1H1		Genteq	Special	37000		80	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F6674BX	BX	Genteq	Special	12		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150E000P440CAS	S	PROLINE	Stock	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6683BR	BR	Genteq	Special	21		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C502F080BC1H1		Genteq	Special	5000		80	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
97F6777BX	BX	Genteq	Special	35		330	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B433F050DH1H1		Genteq	Special	43000		50	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
23F922F150FG1H1		Genteq	Special	9200		150	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F5276BX	BX	Genteq	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6940		Genteq	Standard	35		580	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F154F050FL1H1		Genteq	Special	15000 0		50	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
23H461F350BD1H1		Genteq	Special	460		350	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
23J521F350BF1H1		Genteq	Special	520		350	1.375	Round	4.125	Electrolytic	2000	-40°C to 105°C
23D233F007BC1H1		Genteq	Special	23000		7.5	1.375	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F9698BX	BX	Genteq	Special	25	4	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A144F050FG1H1		Genteq	Special	14000 0		50	3	Round	4.625	Electrolytic	1000	-40°C to 85°C
23C143F060DB1H1		Genteq	Special	14000		60	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23J581F350DC1H1		Genteq	Special	580		350	2	Round	2.625	Electrolytic	2000	-40°C to 105°C
25L6753		Genteq	Standard	35	13	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B483F050DI1H1		Genteq	Special	48000		50	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
PB400Y050C440EA		PROLINE	Standard	40	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B603F080FH1H1		Genteq	Special	60000		80	3	Round	5.125	Electrolytic	3000	-40°C to 85°C

23D253F016CC1H1		Genteq	Special	25000		16	1.75	Round	2.625	Electrolytic	1000	-55°C to 85°C
27L6014		Genteq	Special	6		660	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A833F050FD1H1		Genteq	Special	83000		50	3	Round	3.125	Electrolytic	1000	-40°C to 85°C
23F283F075EE1H1		Genteq	Special	28000		75	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
27L213BX	BX	Genteq	Standard	7.5		400	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J951F400DG1H1		Genteq	Special	950		400	2	Round	4.625	Electrolytic	2000	-40°C to 105°C
41L4301		Genteq	Stock	3		400	0.79	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
27L1020		Genteq	Standard	2		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H392F250DI1H1		Genteq	Special	3900		250	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
27L430BX	BX	Genteq	Standard	18	6	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C503F080EH1H1		Genteq	Special	50000		80	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
23J401F350DB1H1		Genteq	Special	400		350	2	Round	2.125	Electrolytic	2000	-40°C to 105°C
23B853F075FJ1H1		Genteq	Special	85000		75	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
23F133F060BI1H1		Genteq	Special	13000		60	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F5927		Genteq	Standard	70	7.5	440	2.5	Round	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F282F150DE1H1		Genteq	Special	2800		150	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
23B752F150EF1H1		Genteq	Special	7500		150	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
27L566		Genteq	Standard	7.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9477BX	BX	Genteq	Standard	45	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Y050C440CAB X	BX	PROLINE	Standard	20	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B662F100DD1H1		Genteq	Special	6600		100	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
27L366		Genteq	Standard	40		600	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6886		Genteq	Standard	27	8	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9060BX	BX	Genteq	Special	55	7.5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C383F100EI1H1		Genteq	Special	38000		100	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB150E000A370CAS	S	PROLINE	Stock	15		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6727RC	RC	Genteq	Standard	32		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A353F100EH1H1		Genteq	Special	35000		100	2.5	Round	5.125	Electrolytic	1000	-40°C to 85°C
23C382F200DG1H1		Genteq	Special	3800		200	2	Round	4.625	Electrolytic	1000	-45°C to 95°C
23B283F050DE1H1		Genteq	Special	28000		50	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
23C662F150CI1H1		Genteq	Special	6600		150	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
23M242F450FF1H1		Genteq	Special	2400		450	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
23J441F350BE1H1		Genteq	Special	440		350	1.375	Round	3.625	Electrolytic	2000	-40°C to 105°C
23A193F150FH1H1		Genteq	Special	19000		150	3	Round	5.125	Electrolytic	1000	-40°C to 85°C
23B242F200DF1H1		Genteq	Special	2400		200	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F6960		Genteq	Standard	8	2	400	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L562BX	BX	Genteq	Special	45	19	330	1.75	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1001BX	BX	Genteq	Standard	45		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6675		Genteq	Special	16		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1002BX	BX	Genteq	Standard	20		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
40L3101		Genteq	Stock	1		400	0.39	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
23B643F075FG1H1		Genteq	Special	64000		75	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
23A132F150BC1H1		Genteq	Special	1300		150	1.375	Round	2.625	Electrolytic	1000	-40°C to 85°C
23F193F100FF1H1		Genteq	Special	19000		100	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F5320		Genteq	Standard	50		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F272F250EF1H1		Genteq	Special	2700		250	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F9062		Genteq	Standard	60	5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Z050S440DABX	BX	PROLINE	Standard	30	5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C653F060FD1H1		Genteq	Special	65000		60	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F9850		Genteq	Standard	50	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B173F150FJ1H1		Genteq	Special	17000		150	3	Round	5.875	Electrolytic	3000	-40°C to 85°C
23B203F050BI1H1		Genteq	Special	20000		50	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F8053BX	BX	Genteq	Standard	120		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H921F400CF1H1		Genteq	Special	920		400	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C

23B282F200ED1H1		Genteq	Special	2800		200	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB060E000A440BABX	BX	PROLINE	Standard	6		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A113F100DD1H1		Genteq	Special	11000		100	2	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F6601		Genteq	Standard	10		400	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F483F075EI1H1		Genteq	Special	48000		75	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
23C363F050CG1H1		Genteq	Special	36000		50	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
27L1053BX	BX	Genteq	Standard	7.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L3562		Genteq	Stock	0.56		2000	1.14	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
23C143F080BI1H1		Genteq	Special	14000		80	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
23F252F080BB1H1		Genteq	Special	2500		80	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F6921BX	BX	Genteq	Standard	26		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B852F250FL1H1		Genteq	Special	8500		250	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
PB200Z050S370CABX	BX	PROLINE	Standard	20	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB600E000C370EA		PROLINE	Standard	60		370	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B193F080CH1H1		Genteq	Special	19000		80	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB550E000P370EABX	BX	PROLINE	Standard	55		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M272F300CH1H1		Genteq	Special	2700		300	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F6918BR	BR	Genteq	Special	28		480	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J701F400DE1H1		Genteq	Special	700		400	2	Round	3.625	Electrolytic	2000	-40°C to 105°C
27L7000BX	BX	Genteq	Standard	48		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23B242F150CD1H1		Genteq	Special	2400		150	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F8050		Genteq	Standard	90		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H222F450FG1H1		Genteq	Special	2200		450	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6716BX	BX	Genteq	Standard	20		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB050E000A370AAS	S	PROLINE	Stock	5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8058S	S	Genteq	Stock	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B163F050BG1H1		Genteq	Special	16000		50	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F9881BX	BX	Genteq	Standard	35	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6601BR	BR	Genteq	Standard	10		400	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9997		Genteq	Standard	15	5	440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5056		Genteq	Standard	40		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L880S	S	Genteq	Stock	45	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9121BX	BX	Genteq	Standard	15		370	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L729BX	BX	Genteq	Special	20	4	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9627BX	BX	Genteq	Special	15		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8293		Genteq	Standard	48		330	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L20		Genteq	Standard	30	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5436		Genteq	Standard	6		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6881		Genteq	Standard	42	14	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L2332		Genteq	Stock	0.33		1200	0.77	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23M452F450FL1H1		Genteq	Special	4500		450	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
23F132F150CC1H1		Genteq	Special	1300		150	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F9022BX	BX	Genteq	Special	35	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6761RC	RC	Genteq	Standard	17.5		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B502F100DC1H1		Genteq	Special	5000		100	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
23F962F050CB1H1		Genteq	Special	9600		50	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
23J392F300FF1H1		Genteq	Special	3900		300	3	Round	4.125	Electrolytic	2000	-40°C to 105°C
PB250Z100S440DA		PROLINE	Standard	25	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6884BX	BX	Genteq	Standard	33	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5475		Genteq	Special	20	4	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23C163F080DD1H1		Genteq	Special	16000		80	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
27L401		Genteq	Standard	20	8	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6603RC	RC	Genteq	Special	24		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6779BX	BX	Genteq	Standard	18		330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB020E000P370CABX	BX	PROLINE	Standard	2		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6661BX	BX	Genteq	Standard	14		400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9381		Genteq	Standard	35		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6934BR	BR	Genteq	Standard	26		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J781F400CG1H1		Genteq	Special	780		400	1.75	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F9365BX	BX	Genteq	Special	25		480	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9005BX	BX	Genteq	Standard	20		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
24DB250B330PA		Genteq	Standard	25		330	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
23A223F100DH1H1		Genteq	Special	22000		100	2	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F6864BX	BX	Genteq	Standard	24		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B313F060CH1H1		Genteq	Special	31000		60	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
23B623F050EG1H1		Genteq	Special	62000		50	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
27L6082BX	BX	Genteq	Special	20		660	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
25L756		Genteq	Standard	60	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5567BX	BX	Genteq	Special	35	10	370	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F473F075FF1H1		Genteq	Special	47000		75	3	Round	4.125	Electrolytic	1000	-55°C to 105°C
27L571		Genteq	Standard	4		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6698BR	BR	Genteq	Standard	13		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C472F250EG1H1		Genteq	Special	4700		250	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
23J492F200EG1H1		Genteq	Special	4900		200	2.5	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F5283		Genteq	Special	30		370	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L4501		Genteq	Stock	5		400	0.85	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F6680		Genteq	Special	24		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J771F350DD1H1		Genteq	Special	770		350	2	Round	3.125	Electrolytic	2000	-40°C to 105°C
PB125E000A440DAS	S	PROLINE	Stock	12.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D283F028CF1H1		Genteq	Special	28000		28	1.75	Round	4.125	Electrolytic	1000	-55°C to 85°C
97F9859BX	BX	Genteq	Standard	45	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L68		Genteq	Standard	30	18	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB400Y100D440EA		PROLINE	Standard	40	10	440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B163F150FI1H1		Genteq	Special	16000		150	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F6929BX	BX	Genteq	Standard	12		400	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A193F080CE1H1		Genteq	Special	19000		80	1.75	Round	3.625	Electrolytic	1000	-40°C to 85°C
23C113F080BG1H1		Genteq	Special	11000		80	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
PB350Z100T440DA		PROLINE	Standard	35	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5705BX	BX	Genteq	Standard	5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F113F075BH1H1		Genteq	Special	11000		75	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
27L757		Genteq	Special	55		440	2	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1022BX	BX	Genteq	Standard	3		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6602BR	BR	Genteq	Standard	15		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J291F350BC1H1		Genteq	Special	290		350	1.375	Round	2.625	Electrolytic	2000	-40°C to 105°C
23J691F400CF1H1		Genteq	Special	690		400	1.75	Round	4.125	Electrolytic	2000	-40°C to 105°C
23F213F080DH1H1		Genteq	Special	21000		80	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
23C303F080DH1H1		Genteq	Special	30000		80	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
23B213F075CG1H1		Genteq	Special	21000		75	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
PB030E000A370AA		PROLINE	Standard	3		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C

PB800Z050T370EA		PROLINE	Standard	80	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M901F450CG1H1		Genteq	Special	900		450	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB500Y100D440GABX	BX	PROLINE	Standard	50	10	440	2	Oval	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L6101		Genteq	Stock	1		600	0.61	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23A652F100CC1H1		Genteq	Special	6500		100	1.75	Round	2.625	Electrolytic	1000	-40°C to 85°C
97F9366BX	BX	Genteq	Standard	35		240	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F811F250BG1H1		Genteq	Special	810		250	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F9642		Genteq	Standard	40		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B153F075BI1H1		Genteq	Special	15000		75	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B532F080CB1H1		Genteq	Special	5300		80	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F9082		Genteq	Standard	20		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L724BX	BX	Genteq	Standard	24	11	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
24DB350B370PA		Genteq	Standard	35		370	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
PB650E000T370DABX	BX	PROLINE	Standard	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A423F060CH1H1		Genteq	Special	42000		60	1.75	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F8071BX	BX	Genteq	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9848		Genteq	Standard	35	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J322F250DI1H1		Genteq	Special	3200		250	2	Round	5.625	Electrolytic	2000	-40°C to 105°C
27L444RR	RR	Genteq	Special	37	11	300	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5251		Genteq	Standard	70		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6946		Genteq	Standard	21		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C443F100FG1H1		Genteq	Special	44000		100	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
PB550Z050T370DABX	BX	PROLINE	Standard	55	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D852F028BC1H1		Genteq	Special	8500		28	1.375	Round	2.625	Electrolytic	1000	-55°C to 85°C
23C114F050FG1H1		Genteq	Special	110000		50	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
23J132F350CI1H1		Genteq	Special	1300		350	1.75	Round	5.625	Electrolytic	2000	-40°C to 105°C
23D153F020CB1H1		Genteq	Special	15000		20	1.75	Round	2.125	Electrolytic	1000	-55°C to 85°C
23H272F350EG1H1		Genteq	Special	2700		350	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB500E000P240EABX	BX	PROLINE	Standard	50		240	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L542		Genteq	Standard	10.5	8	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB500Z075S370EA		PROLINE	Standard	50	7.5	370	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB150Z050S440CABX	BX	PROLINE	Standard	15	5	440	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
25L6755BX	BX	Genteq	Standard	20	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M332F250DF1H1		Genteq	Special	3300		250	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8064S	S	Genteq	Stock	25		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1024S	S	Genteq	Stock	5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5567		Genteq	Special	35	10	370	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6670BX	BX	Genteq	Special	38.5		370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H142F400DH1H1		Genteq	Special	1400		400	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB060E000A440BAS	S	PROLINE	Stock	6		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L4682		Genteq	Stock	0.68		400	0.39	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F6539BX	BX	Genteq	Standard	14		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J102F350CG1H1		Genteq	Special	1000		350	1.75	Round	4.625	Electrolytic	2000	-40°C to 105°C
23F233F075DG1H1		Genteq	Special	23000		75	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F6924		Genteq	Standard	13		540	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M701F300CB1H1		Genteq	Special	700		300	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23D153F035CD1H1		Genteq	Special	15000		35	1.75	Round	3.125	Electrolytic	1000	-55°C to 85°C
23D732F055BF1H1		Genteq	Special	7300		55	1.375	Round	4.125	Electrolytic	1000	-55°C to 85°C
23F142F150BF1H1		Genteq	Special	1400		150	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
PB250E000P440DAS	S	PROLINE	Stock	25		440	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C

PB400Y100D440EAB X	BX	PROLINE	Standard	40	10	440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100Y100C440CAB X	BX	PROLINE	Standard	10	10	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6200		Genteq	Special	9.4		290	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200Z100S440DA		PROLINE	Standard	20	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H432F250FD1H1		Genteq	Special	4300		250	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C832F100CD1H1		Genteq	Special	8300		100	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
23C543F080FF1H1		Genteq	Special	54000		80	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
PB040E000A440AAS	S	PROLINE	Stock	4		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6526RC	RC	Genteq	Standard	10		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B533F080FG1H1		Genteq	Special	53000		80	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
23H142F300DD1H1		Genteq	Special	1400		300	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23F321F200BB1H1		Genteq	Special	320		200	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
23H201F400BB1H1		Genteq	Special	200		400	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
42L1101		Genteq	Stock	1		850	0.81	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
PB500E000T440DABX	BX	PROLINE	Standard	50		440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9885		Genteq	Standard	50	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B213F080ED1H1		Genteq	Special	21000		80	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
23M372F450FJ1H1		Genteq	Special	3700		450	3	Round	5.875	Electrolytic	2000	-40°C to 85°C
97F9737		Genteq	Standard	35	7.5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6535		Genteq	Standard	24		400	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L7003RC	RC	Genteq	Standard	26		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
PB400Z100S440EABX	BX	PROLINE	Standard	40	10	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L989		Genteq	Special	30		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB030E000A440AABX	BX	PROLINE	Standard	3		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C503F100FH1H1		Genteq	Special	50000		100	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
PB350Z050T440CA		PROLINE	Standard	35	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F492F150DI1H1		Genteq	Special	4900		150	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F9021BX	BX	Genteq	Special	35	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C403F075EF1H1		Genteq	Special	40000		75	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F8048		Genteq	Standard	80		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8240BX	BX	Genteq	Special	1.5		600	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Y075C440EAB X	BX	PROLINE	Standard	35	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB500Y050C370EA		PROLINE	Standard	50	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L444		Genteq	Special	37	11	300	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C891F250DB1H1		Genteq	Special	890		250	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23F152F250CG1H1		Genteq	Special	1500		250	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
23M162F450EF1H1		Genteq	Special	1600		450	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
41L6201		Genteq	Stock	2		600	0.73	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
PB075E000A370BA		PROLINE	Standard	7.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L322BX	BX	Genteq	Special	80		440	2.5	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L868		Genteq	Special	80	10	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J612F200FF1H1		Genteq	Special	6100		200	3	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F5483		Genteq	Special	35	4	370	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB450E000C370DAB X	BX	PROLINE	Standard	45		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C122F250BG1H1		Genteq	Special	1200		250	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
23J122F300CE1H1		Genteq	Special	1200		300	1.75	Round	3.625	Electrolytic	2000	-40°C to 105°C
PB020E000A440AA		PROLINE	Standard	2		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C123F060BD1H1		Genteq	Special	12000		60	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F9987		Genteq	Standard	50	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M312F250CG1H1		Genteq	Special	3100		250	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C

PB350Y100C370DA		PROLINE	Standard	35	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB350Y075C370DA		PROLINE	Standard	35	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C233F100DI1H1		Genteq	Special	23000		100	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
23F592F080BE1H1		Genteq	Special	5900		80	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
23F843F050EI1H1		Genteq	Special	84000		50	2.5	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F6505		Genteq	Standard	17.5		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5482		Genteq	Special	30	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M252F350DH1H1		Genteq	Special	2500		350	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB300Z075S440DA		PROLINE	Standard	30	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L6016BX	BX	Genteq	Special	8		660	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L758BX	BX	Genteq	Special	50		440	2	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A833F050EF1H1		Genteq	Special	83000		50	2.5	Round	4.125	Electrolytic	1000	-40°C to 85°C
27L569BX	BX	Genteq	Special	50	5	440	2.5	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6926RC	RC	Genteq	Standard	26		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H292F200DE1H1		Genteq	Special	2900		200	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F8243		Genteq	Special	3		600	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M102F300DB1H1		Genteq	Special	1000		300	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F9751BX	BX	Genteq	Special	20	4	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F602F060CB1H1		Genteq	Special	6000		60	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
PB500E000C370DABX	BX	PROLINE	Standard	50		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9030BX	BX	Genteq	Special	50	10	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C592F150CH1H1		Genteq	Special	5900		150	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
23B902F075CC1H1		Genteq	Special	9000		75	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
23C253F075CH1H1		Genteq	Special	25000		75	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
23H172F200BG1H1		Genteq	Special	1700		200	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
23C303F100EG1H1		Genteq	Special	30000		100	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C
27L5201		Genteq	Standard	50	10	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M352F250CH1H1		Genteq	Special	3500		250	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
23M562F250FD1H1		Genteq	Special	5600		250	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
PB600Z100T440EA		PROLINE	Standard	60	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C772F100BG1H1		Genteq	Special	7700		100	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
23C432F200DH1H1		Genteq	Special	4300		200	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
PB450Y050C370DA		PROLINE	Standard	45	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8248		Genteq	Standard	8		600	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C643F080FG1H1		Genteq	Special	64000		80	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
23A263F080CG1H1		Genteq	Special	26000		80	1.75	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F9898BX	BX	Genteq	Standard	60	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400Y075C370DA		PROLINE	Standard	40	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B393F080FE1H1		Genteq	Special	39000		80	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6885BR	BR	Genteq	Standard	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F932F200FL1H1		Genteq	Special	9300		200	3	Round	8.625	Electrolytic	1000	-55°C to 105°C
23B272F250EE1H1		Genteq	Special	2700		250	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
PB350E000S440DA		PROLINE	Standard	35		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9007BX	BX	Genteq	Standard	35		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A242F150CC1H1		Genteq	Special	2400		150	1.75	Round	2.625	Electrolytic	1000	-40°C to 85°C
23B143F100DI1H1		Genteq	Special	14000		100	2	Round	5.625	Electrolytic	3000	-40°C to 85°C
23H841F350CD1H1		Genteq	Special	840		350	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
23H122F350DE1H1		Genteq	Special	1200		350	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6676		Genteq	Special	3		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6774BR	BR	Genteq	Standard	24		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M901F400BI1H1		Genteq	Special	900		400	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F8255BX	BX	Genteq	Standard	30		600	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H123F200FI1H1		Genteq	Special	12000		200	3	Round	5.625	Electrolytic	2000	-40°C to 85°C

23F143F075DD1H1		Genteq	Special	14000		75	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
PB350Y075C370DABX	BX	PROLINE	Standard	35	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5050BX	BX	Genteq	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C392F150DD1H1		Genteq	Special	3900		150	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
PB350Z050S440EABX	BX	PROLINE	Standard	35	5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A363F075DG1H1		Genteq	Special	36000		75	2	Round	4.625	Electrolytic	1000	-40°C to 85°C
PB250Y100C370CABX	BX	PROLINE	Standard	25	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D153F028CC1H1		Genteq	Special	15000		28	1.75	Round	2.625	Electrolytic	1000	-55°C to 85°C
PB500Y050D440GABX	BX	PROLINE	Standard	50	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5239BX	BX	Genteq	Standard	55		480	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H182F300DE1H1		Genteq	Special	1800		300	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
23F632F150EG1H1		Genteq	Special	6300		150	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
23M113F200EI1H1		Genteq	Special	11000		200	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F461F250CB1H1		Genteq	Special	460		250	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F9090		Genteq	Standard	40		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
40L3682		Genteq	Stock	0.68		400	0.3	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
97F6760BX	BX	Genteq	Standard	12		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L92BX	BX	Genteq	Special	80	7.5	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J971F300BH1H1		Genteq	Special	970		300	1.375	Round	5.125	Electrolytic	2000	-40°C to 105°C
23J422F200EF1H1		Genteq	Special	4200		200	2.5	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F6535BR	BR	Genteq	Standard	24		400	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C373F100FF1H1		Genteq	Special	37000		100	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
23H202F300CG1H1		Genteq	Special	2000		300	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
23F342F100BF1H1		Genteq	Special	3400		100	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F8052		Genteq	Standard	100		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B193F080DF1H1		Genteq	Special	19000		80	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F9630BX	BX	Genteq	Standard	20		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C213F150FJ1H1		Genteq	Special	21000		150	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
23M492F400FI1H1		Genteq	Special	4900		400	3	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6774BX	BX	Genteq	Standard	24		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5116BX	BX	Genteq	Standard	40		440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8312BX	BX	Genteq	Standard	90		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9856		Genteq	Standard	40	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6783BX	BX	Genteq	Special	25		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L430		Genteq	Standard	18	6	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B132F250CE1H1		Genteq	Special	1300		250	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6766BR	BR	Genteq	Standard	7		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M652F300EI1H1		Genteq	Special	6500		300	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6951BR	BR	Genteq	Standard	22.5		540	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A163F075CD1H1		Genteq	Special	16000		75	1.75	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F9730BX	BX	Genteq	Standard	25	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300E000P440DABX	BX	PROLINE	Standard	30		440	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B373F050CI1H1		Genteq	Special	37000		50	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9641		Genteq	Standard	40		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F293F100FI1H1		Genteq	Special	29000		100	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
97F6744BX	BX	Genteq	Special	12.5		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6767BX	BX	Genteq	Standard	10		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8218		Genteq	Standard	30		240	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M751F250BC1H1		Genteq	Special	750		250	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F9063BX	BX	Genteq	Standard	60	7.5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB700E000T370EA		PROLINE	Standard	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C

PB300Z100S440DABX	BX	PROLINE	Standard	30	10	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J202F250CG1H1		Genteq	Special	2000		250	1.75	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F6945BR	BR	Genteq	Standard	24		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB300Y075C370DA		PROLINE	Standard	30	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A592F100DB1H1		Genteq	Special	5900		100	2	Round	2.125	Electrolytic	1000	-40°C to 85°C
23F293F075DI1H1		Genteq	Special	29000		75	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
23H391F400DB1H1		Genteq	Special	390		400	2	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F9979BX	BX	Genteq	Standard	25	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C123F080CD1H1		Genteq	Special	12000		80	1.75	Round	3.125	Electrolytic	1000	-45°C to 95°C
23B472F060BB1H1		Genteq	Special	4700		60	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
23J151F400BB1H1		Genteq	Special	150		400	1.375	Round	2.125	Electrolytic	2000	-40°C to 105°C
97F9859		Genteq	Standard	45	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6696		Genteq	Special	38		300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6804		Genteq	Special	10		280	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6931		Genteq	Standard	20		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C143F100CG1H1		Genteq	Special	14000		100	1.75	Round	4.625	Electrolytic	1000	-45°C to 95°C
PB500Z100T440EA		PROLINE	Standard	50	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C652F150ED1H1		Genteq	Special	6500		150	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
23J152F200CD1H1		Genteq	Special	1500		200	1.75	Round	3.125	Electrolytic	2000	-40°C to 105°C
23B262F150BH1H1		Genteq	Special	2600		150	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB550Z100T370DABX	BX	PROLINE	Standard	55	10	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F353F080EH1H1		Genteq	Special	35000		80	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F9615		Genteq	Standard	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6530		Genteq	Standard	40		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F323F060DI1H1		Genteq	Special	32000		60	2	Round	5.625	Electrolytic	1000	-55°C to 105°C
23H582F250EH1H1		Genteq	Special	5800		250	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB600E000D440HABX	BX	PROLINE	Standard	60		440	2	Oval	4.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B203F075DE1H1		Genteq	Special	20000		75	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6865RC	RC	Genteq	Standard	35		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9673BX	BX	Genteq	Standard	20	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8049BX	BX	Genteq	Standard	85		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7009BX	BX	Genteq	Special	24		400	1.25	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F6882BR	BR	Genteq	Standard	24	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C832F080DB1H1		Genteq	Special	8300		80	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
PB300Y075C440DA		PROLINE	Standard	30	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB600Z100T370EA		PROLINE	Standard	60	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B163F060DC1H1		Genteq	Special	16000		60	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F6857BR	BR	Genteq	Standard	8		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6886BX	BX	Genteq	Standard	27	8	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9007		Genteq	Standard	35		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B662F060BC1H1		Genteq	Special	6600		60	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F6765		Genteq	Standard	6		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H182F350DH1H1		Genteq	Special	1800		350	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
23F124F050FI1H1		Genteq	Special	12000	0	50	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
27L6093		Genteq	Special	2.5		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H242F200CE1H1		Genteq	Special	2400		200	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F8254		Genteq	Standard	25		600	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6762BX	BX	Genteq	Standard	11		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L865BX	BX	Genteq	Standard	15	6	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5781BX	BX	Genteq	Standard	50	7.5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C

24DB400B370PA		Genteq	Standard	40		370	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
23M292F350DI1H1		Genteq	Special	2900		350	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
23F353F060FD1H1		Genteq	Special	35000		60	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F6947BX	BX	Genteq	Special	52		330	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B163F060CD1H1		Genteq	Special	16000		60	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB550E000T440EABX	BX	PROLINE	Standard	55		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9608		Genteq	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J172F200DD1H1		Genteq	Special	1700		200	2	Round	3.125	Electrolytic	2000	-40°C to 105°C
23M472F350EI1H1		Genteq	Special	4700		350	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F6804BX	BX	Genteq	Special	10		280	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6602BX	BX	Genteq	Standard	15		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5368BX	BX	Genteq	Special	35	5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350Y100C440EABX	BX	PROLINE	Standard	35	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D283F016BG1H1		Genteq	Special	28000		16	1.375	Round	4.625	Electrolytic	1000	-55°C to 85°C
PB700Z100T440EABX	BX	PROLINE	Standard	70	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H112F450EE1H1		Genteq	Special	1100		450	2.5	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F9053		Genteq	Special	30	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B172F250CG1H1		Genteq	Special	1700		250	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
23B233F100EI1H1		Genteq	Special	23000		100	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
27L947		Genteq	Standard	45	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9264		Genteq	Standard	20		410	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H981F450CI1H1		Genteq	Special	980		450	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23C253F050BI1H1		Genteq	Special	25000		50	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
23C333F075DH1H1		Genteq	Special	33000		75	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
PB150Z075S370CABX	BX	PROLINE	Standard	15	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9628		Genteq	Standard	17.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6768BX	BX	Genteq	Standard	14		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J841F200BD1H1		Genteq	Special	840		200	1.375	Round	3.125	Electrolytic	2000	-40°C to 105°C
23H262F300CI1H1		Genteq	Special	2600		300	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23M162F400CI1H1		Genteq	Special	1600		400	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
41L2150		Genteq	Stock	15		250	0.96	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
PB650E000T440EABX	BX	PROLINE	Standard	65		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9001BX	BX	Genteq	Standard	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F133F100FD1H1		Genteq	Special	13000		100	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
23D413F028CI1H1		Genteq	Special	41000		28	3	Round	8.625	Electrolytic	1000	-55°C to 85°C
23A183F050BE1H1		Genteq	Special	18000		50	1.375	Round	3.625	Electrolytic	1000	-40°C to 85°C
23A692F150DG1H1		Genteq	Special	6900		150	2	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F6950BX	BX	Genteq	Standard	12	12	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H112F200BD1H1		Genteq	Special	1100		200	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9251BX	BX	Genteq	Standard	25	3.2	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8049S	S	Genteq	Stock	85		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB500E000S370DABX	BX	PROLINE	Standard	50		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8254BX	BX	Genteq	Standard	25		600	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5362		Genteq	Special	25	7.5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B402F100BF1H1		Genteq	Special	4000		100	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
PB450Y100C440EABX	BX	PROLINE	Standard	45	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8294		Genteq	Standard	60		330	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F792F075CC1H1		Genteq	Special	7900		75	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F6702BX	BX	Genteq	Special	7		330	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H381F450CC1H1		Genteq	Special	380		450	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23A483F060DG1H1		Genteq	Special	48000		60	2	Round	4.625	Electrolytic	1000	-40°C to 85°C

PB450Z075T440DABX	BX	PROLINE	Standard	45	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L322		Genteq	Special	80		440	2.5	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A163F075DC1H1		Genteq	Special	16000		75	2	Round	2.625	Electrolytic	1000	-40°C to 85°C
97F9053BX	BX	Genteq	Special	30	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B433F060EE1H1		Genteq	Special	43000		60	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6925		Genteq	Special	48		300	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J132F400EF1H1		Genteq	Special	1300		400	2.5	Round	4.125	Electrolytic	2000	-40°C to 105°C
23J362F400FL1H1		Genteq	Special	3600		400	3	Round	8.625	Electrolytic	2000	-40°C to 105°C
23J271F400CB1H1		Genteq	Special	270		400	1.75	Round	2.125	Electrolytic	2000	-40°C to 105°C
PB300Y075C440DABX	BX	PROLINE	Standard	30	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J602F250FG1H1		Genteq	Special	6000		250	3	Round	4.625	Electrolytic	2000	-40°C to 105°C
27L1001		Genteq	Standard	45		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5437BX	BX	Genteq	Standard	3		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C692F075CB1H1		Genteq	Special	6900		75	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
23H502F200DI1H1		Genteq	Special	5000		200	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
23M222F250BI1H1		Genteq	Special	2200		250	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
23C891F250BE1H1		Genteq	Special	890		250	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
40L3501		Genteq	Stock	5		400	0.69	Oval	1.75	Dry-Axial Leaded	100000	-55°C to 105°C
23C123F200FI1H1		Genteq	Special	12000		200	3	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6522BX	BX	Genteq	Standard	24		280	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150Y050C440CA		PROLINE	Standard	15	5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9836BX	BX	Genteq	Special	30	4	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C283F075ED1H1		Genteq	Special	28000		75	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
PB450E000P370EABX	BX	PROLINE	Standard	45		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6770		Genteq	Standard	17.5		330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9636BX	BX	Genteq	Standard	30		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8050S	S	Genteq	Stock	90		240	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300E000C240CABX	BX	PROLINE	Standard	30		240	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6537		Genteq	Standard	24		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6694		Genteq	Special	20		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB300E000P370DABX	BX	PROLINE	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C133F075DC1H1		Genteq	Special	13000		75	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
23A802F100BG1H1		Genteq	Special	8000		100	1.375	Round	4.625	Electrolytic	1000	-40°C to 85°C
23M272F400EG1H1		Genteq	Special	2700		400	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
23A463F050CG1H1		Genteq	Special	46000		50	1.75	Round	4.625	Electrolytic	1000	-40°C to 85°C
23B133F150FG1H1		Genteq	Special	13000		150	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F6727		Genteq	Standard	32		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L176BR	BR	Genteq	Special	7.5		540	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C203F060DC1H1		Genteq	Special	20000		60	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
23A313F100EG1H1		Genteq	Special	31000		100	2.5	Round	4.625	Electrolytic	1000	-40°C to 85°C
PB550E000T370DA		PROLINE	Standard	55		370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B412F150CG1H1		Genteq	Special	4100		150	1.75	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F8005BX	BX	Genteq	Special	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M102F450DF1H1		Genteq	Special	1000		450	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F6519		Genteq	Standard	16		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L543BX	BX	Genteq	Standard	9.5	6.5	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L7008		Genteq	Special	11	6	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F6683BX	BX	Genteq	Special	21		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B262F250DH1H1		Genteq	Special	2600		250	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F9973BX	BX	Genteq	Standard	55	7.5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F854F250DC1H1		Genteq	Special	850		250	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
23B421F250BC1H1		Genteq	Special	420		250	1.375	Round	2.625	Electrolytic	3000	-40°C to 85°C

97F6885BX	BX	Genteq	Standard	36	12	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6758		Genteq	Standard	15		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB250E000P440DA		PROLINE	Standard	25		440	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F542F150EF1H1		Genteq	Special	5400		150	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
23H791F450DF1H1		Genteq	Special	790		450	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
23C542F075BC1H1		Genteq	Special	5400		75	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
23C213F050DB1H1		Genteq	Special	21000		50	2	Round	2.125	Electrolytic	1000	-45°C to 95°C
23H132F200BE1H1		Genteq	Special	1300		200	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
23H122F300CD1H1		Genteq	Special	1200		300	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
41L4101		Genteq	Stock	1		400	0.47	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F8071		Genteq	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L862		Genteq	Standard	35	24	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6766S	S	Genteq	Stock	7		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A283F080DF1H1		Genteq	Special	28000		80	2	Round	4.125	Electrolytic	1000	-40°C to 85°C
PB400E000S370DAB X	BX	PROLINE	Standard	40		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H701F250BC1H1		Genteq	Special	700		250	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
23J102F250BF1H1		Genteq	Special	1000		250	1.375	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F6878		Genteq	Standard	20	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B652F075CB1H1		Genteq	Special	6500		75	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F6779		Genteq	Standard	18		330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M252F200BH1H1		Genteq	Special	2500		200	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23H681F450CF1H1		Genteq	Special	680		450	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
23A133F075BF1H1		Genteq	Special	13000		75	1.375	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9993		Genteq	Standard	25	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C163F075CE1H1		Genteq	Special	16000		75	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F8251		Genteq	Standard	15		600	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C184F060FL1H1		Genteq	Special	18000 0		60	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
23D203F028CD1H1		Genteq	Special	20000		28	1.75	Round	3.125	Electrolytic	1000	-55°C to 85°C
23F372F150ED1H1		Genteq	Special	3700		150	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
23F461F200BC1H1		Genteq	Special	460		200	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F6643BX	BX	Genteq	Special	30		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6673BX	BX	Genteq	Special	14		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6884		Genteq	Standard	33	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8008BX	BX	Genteq	Special	50		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150E000P370CA		PROLINE	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C233F080CH1H1		Genteq	Special	23000		80	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
27L442RR	RR	Genteq	Standard	28	7	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1044		Genteq	Standard	55		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C223F100EE1H1		Genteq	Special	22000		100	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
23J781F250DB1H1		Genteq	Special	780		250	2	Round	2.125	Electrolytic	2000	-40°C to 105°C
PB300Y050C440DAB X	BX	PROLINE	Standard	30	5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5114		Genteq	Special	35		370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9025		Genteq	Special	40	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7003		Genteq	Standard	26		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23J242F350EH1H1		Genteq	Special	2400		350	2.5	Round	5.125	Electrolytic	2000	-40°C to 105°C
23C162F200BG1H1		Genteq	Special	1600		200	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
23F552F075CB1H1		Genteq	Special	5500		75	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F6684		Genteq	Special	12.5		440	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9039		Genteq	Standard	20		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L401BX	BX	Genteq	Standard	20	8	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB125E000P440CAB X	BX	PROLINE	Standard	12.5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J362F200EE1H1		Genteq	Special	3600		200	2.5	Round	3.625	Electrolytic	2000	-40°C to 105°C

23B352F200EE1H1		Genteq	Special	3500		200	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
23F263F050CF1H1		Genteq	Special	26000		50	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F8069BX	BX	Genteq	Standard	50		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J481F200BB1H1		Genteq	Special	480		200	1.375	Round	2.125	Electrolytic	2000	-40°C to 105°C
23C663F050FD1H1		Genteq	Special	66000		50	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
27L432		Genteq	Standard	22	7	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C343F100BC1H1		Genteq	Special	3400		100	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
23A172F150BD1H1		Genteq	Special	1700		150	1.375	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F5401		Genteq	Special	45	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L6681		Genteq	Stock	6.8		600	1.12	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
PB250Z100S370CA		PROLINE	Standard	25	10	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F123F150FJ1H1		Genteq	Special	12000		150	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
97F8039		Genteq	Standard	35		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L647BX	BX	Genteq	Standard	50	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6768		Genteq	Standard	14		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
25L2005BX	BX	Genteq	Special	35		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C104F050FF1H1		Genteq	Special	10000 0		50	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9002BX	BX	Genteq	Standard	10		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB125E000A370CAS	S	PROLINE	Stock	12.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9627		Genteq	Special	15		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8242		Genteq	Special	2.5		600	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB020E000P370CA		PROLINE	Standard	2		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23D173F055CH1H1		Genteq	Special	17000		55	1.75	Round	5.125	Electrolytic	1000	-55°C to 85°C
23A133F150EH1H1		Genteq	Special	13000		150	2.5	Round	5.125	Electrolytic	1000	-40°C to 85°C
23H512F300FF1H1		Genteq	Special	5100		300	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F6881BX	BX	Genteq	Standard	42	14	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450Z050T440DA		PROLINE	Standard	45	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6866		Genteq	Standard	40		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8246BX	BX	Genteq	Standard	6		600	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C642F080CB1H1		Genteq	Special	6400		80	1.75	Round	2.125	Electrolytic	1000	-45°C to 95°C
42L4473		Genteq	Stock	0.047		3000	0.73	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23A673F060EF1H1		Genteq	Special	67000		60	2.5	Round	4.125	Electrolytic	1000	-40°C to 85°C
27L667BX	BX	Genteq	Standard	42	22	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L590RR	RR	Genteq	Standard	24	11	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H302F350EH1H1		Genteq	Special	3000		350	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
23C242F100BB1H1		Genteq	Special	2400		100	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
PB050E000P440CA		PROLINE	Standard	5		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L791		Genteq	Standard	8		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A413F075DH1H1		Genteq	Special	41000		75	2	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F9084BX	BX	Genteq	Standard	55		440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8041BX	BX	Genteq	Standard	45		240	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A263F150FL1H1		Genteq	Special	26000		150	3	Round	8.625	Electrolytic	1000	-40°C to 85°C
97F5457BX	BX	Genteq	Special	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F353F060EF1H1		Genteq	Special	35000		60	2.5	Round	4.125	Electrolytic	1000	-55°C to 105°C
97F8253BX	BX	Genteq	Standard	20		600	1.5	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H192F450EI1H1		Genteq	Special	1900		450	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
PB300Y100C440EA		PROLINE	Standard	30	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9844		Genteq	Standard	45	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C663F050EF1H1		Genteq	Special	66000		50	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F8040BX	BX	Genteq	Standard	40		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23H261F350BB1H1		Genteq	Special	260		350	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F6755RC	RC	Genteq	Standard	26		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB020E000A370AA		PROLINE	Standard	2		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6883		Genteq	Standard	36	20	280	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F532F050BB1H1		Genteq	Special	5300		50	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
23B902F050BD1H1		Genteq	Special	9000		50	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB400E000P440EA		PROLINE	Standard	40		440	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L443RR	RR	Genteq	Standard	17	7	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H861F450CH1H1		Genteq	Special	860		450	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F6947		Genteq	Special	52		330	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9626S	S	Genteq	Stock	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L633BX	BX	Genteq	Standard	70	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H122F250BF1H1		Genteq	Special	1200		250	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
23B222F250CI1H1		Genteq	Special	2200		250	1.75	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F6753BX	BX	Genteq	Special	7		330	1.5	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J312F200CI1H1		Genteq	Special	3100		200	1.75	Round	5.625	Electrolytic	2000	-40°C to 105°C
27L6012BX	BX	Genteq	Special	4		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L7001BR	BR	Genteq	Standard	10		400	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
23M112F350BH1H1		Genteq	Special	1100		350	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23H211F450BC1H1		Genteq	Special	210		450	1.375	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F5103		Genteq	Special	30		440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D433F007BF1H1		Genteq	Special	43000		7.5	1.375	Round	4.125	Electrolytic	1000	-55°C to 85°C
97F9816BX	BX	Genteq	Standard	60	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8053		Genteq	Standard	120		240	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9837BX	BX	Genteq	Special	35	4	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A113F075BE1H1		Genteq	Special	11000		75	1.375	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F6868RC	RC	Genteq	Standard	26		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L3222		Genteq	Stock	0.22		2000	0.93	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F9012S	S	Genteq	Stock	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L576BX	BX	Genteq	Special	20	8	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6746BX	BX	Genteq	Standard	12		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6950		Genteq	Standard	12	12	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B433F100FL1H1		Genteq	Special	43000		100	3	Round	8.625	Electrolytic	3000	-40°C to 85°C
97F9987BX	BX	Genteq	Standard	50	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6855BR	BR	Genteq	Standard	22.5		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D213F016BE1H1		Genteq	Special	21000		16	1.375	Round	3.625	Electrolytic	1000	-55°C to 85°C
23H552F200EF1H1		Genteq	Special	5500		200	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8064		Genteq	Standard	25		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C103F075CC1H1		Genteq	Special	10000		75	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
PB400E000S370DA		PROLINE	Standard	40		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A203F050CC1H1		Genteq	Special	20000		50	1.75	Round	2.625	Electrolytic	1000	-40°C to 85°C
23A643F075FE1H1		Genteq	Special	64000		75	3	Round	3.625	Electrolytic	1000	-40°C to 85°C
23H472F300EH1H1		Genteq	Special	4700		300	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB450E000C370DAS	S	PROLINE	Stock	45		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C283F050DC1H1		Genteq	Special	28000		50	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
23H232F350FD1H1		Genteq	Special	2300		350	3	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6902BX	BX	Genteq	Special	55		240	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C882F050BC1H1		Genteq	Special	8800		50	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
97F9319		Genteq	Special	55	7.5	440	2	Oval	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6952BR	BR	Genteq	Standard	36		540	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C632F100CC1H1		Genteq	Special	6300		100	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C

23D203F028BH1H1		Genteq	Special	20000		28	1.375	Round	5.125	Electrolytic	1000	-55°C to 85°C
23C712F075BD1H1		Genteq	Special	7100		75	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F6755BX	BX	Genteq	Standard	26		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B532F250FG1H1		Genteq	Special	5300		250	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
PB1502050S370CABX	BX	PROLINE	Standard	15	5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L402		Genteq	Standard	24	8	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A153F100CG1H1		Genteq	Special	15000		100	1.75	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F5266BX	BX	Genteq	Special	45		370	2.5	Round	3.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F462F060BC1H1		Genteq	Special	4600		60	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
PB5502075T370DABX	BX	PROLINE	Standard	55	7.5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100E000P440CA		PROLINE	Standard	10		440	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H322F200CG1H1		Genteq	Special	3200		200	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J302F200DG1H1		Genteq	Special	3000		200	2	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F8313		Genteq	Special	46		600	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L540BX	BX	Genteq	Standard	16.5	11.5	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6931BR	BR	Genteq	Standard	20		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L388		Genteq	Special	60		440	2	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B233F075DF1H1		Genteq	Special	23000		75	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F9638S	S	Genteq	Stock	35		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB050E000A440BA		PROLINE	Standard	5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C233F080DF1H1		Genteq	Special	23000		80	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
23F953F050FG1H1		Genteq	Special	95000		50	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
23H312F300DI1H1		Genteq	Special	3100		300	2	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9844BX	BX	Genteq	Standard	45	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H122F350CF1H1		Genteq	Special	1200		350	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8044BX	BX	Genteq	Standard	60		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Y050C370DABX	BX	PROLINE	Standard	30	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9992BX	BX	Genteq	Standard	15	7.5	440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M742F200EF1H1		Genteq	Special	7400		200	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
27L414BX	BX	Genteq	Standard	70	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F212F150BI1H1		Genteq	Special	2100		150	1.375	Round	5.625	Electrolytic	1000	-55°C to 105°C
PB020E000A370AABX	BX	PROLINE	Standard	2		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9491		Genteq	Standard	30		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600E000T440EA		PROLINE	Standard	60		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L1008		Genteq	Standard	60	10	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L635		Genteq	Special	90		440	2.5	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L727		Genteq	Standard	45	19	300	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M552F300FE1H1		Genteq	Special	5500		300	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6839BX	BX	Genteq	Special	43.5		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H152F250BH1H1		Genteq	Special	1500		250	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23H222F250DE1H1		Genteq	Special	2200		250	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
23B502F050BB1H1		Genteq	Special	5000		50	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
23C173F050BF1H1		Genteq	Special	17000		50	1.375	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9051BX	BX	Genteq	Special	25	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9837		Genteq	Special	35	4	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L635BX	BX	Genteq	Special	90		440	2.5	Round	5.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L907		Genteq	Special	55		240	1.75	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A252F100BB1H1		Genteq	Special	2500		100	1.375	Round	2.125	Electrolytic	1000	-40°C to 85°C
23C282F150BG1H1		Genteq	Special	2800		150	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
23F313F080EG1H1		Genteq	Special	31000		80	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C

97F6771BX	BX	Genteq	Standard	18		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F263F075DH1H1		Genteq	Special	26000		75	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
23M551F350BD1H1		Genteq	Special	550		350	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
27L6015		Genteq	Special	7		660	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6956BX	BX	Genteq	Standard	22.5		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H262F400EI1H1		Genteq	Special	2600		400	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
23B173F050DC1H1		Genteq	Special	17000		50	2	Round	2.625	Electrolytic	3000	-40°C to 85°C
23B172F150BE1H1		Genteq	Special	1700		150	1.375	Round	3.625	Electrolytic	3000	-40°C to 85°C
23F832F075BF1H1		Genteq	Special	8300		75	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
23A104F060EI1H1		Genteq	Special	10000 0		60	2.5	Round	5.625	Electrolytic	1000	-40°C to 85°C
27L872		Genteq	Standard	60	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9834S	S	Genteq	Stock	35	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6751BX	BX	Genteq	Special	9.25		330	1.25	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9981		Genteq	Standard	30	5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F663F050EG1H1		Genteq	Special	66000		50	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
23B152F250CF1H1		Genteq	Special	1500		250	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23C123F075BG1H1		Genteq	Special	12000		75	1.375	Round	4.625	Electrolytic	1000	-45°C to 95°C
23C413F050CH1H1		Genteq	Special	41000		50	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F5729BX	BX	Genteq	Standard	50	5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A233F060BH1H1		Genteq	Special	23000		60	1.375	Round	5.125	Electrolytic	1000	-40°C to 85°C
23B143F100EE1H1		Genteq	Special	14000		100	2.5	Round	3.625	Electrolytic	3000	-40°C to 85°C
23F183F060DE1H1		Genteq	Special	18000		60	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
23F132F100BB1H1		Genteq	Special	1300		100	1.375	Round	2.125	Electrolytic	1000	-55°C to 105°C
97F5481		Genteq	Special	25	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B561F250BD1H1		Genteq	Special	460		250	1.375	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F9858		Genteq	Standard	50	7.5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L2301		Genteq	Stock	3		250	0.53	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F6526BR	BR	Genteq	Standard	10		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F134F050FJ1H1		Genteq	Special	13000 0		50	3	Round	5.875	Electrolytic	1000	-55°C to 105°C
23C373F080FD1H1		Genteq	Special	37000		80	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
23H952F300FL1H1		Genteq	Special	9500		300	3	Round	8.625	Electrolytic	2000	-40°C to 85°C
27L1044BX	BX	Genteq	Standard	55		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A353F075ED1H1		Genteq	Special	35000		75	2.5	Round	3.125	Electrolytic	1000	-40°C to 85°C
PB250Z075S440DABX	BX	PROLINE	Standard	25	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L1051		Genteq	Special	50	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9991		Genteq	Standard	20	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9626BX	BX	Genteq	Standard	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5339		Genteq	Standard	5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L590		Genteq	Standard	24	11	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F192F250DG1H1		Genteq	Special	1900		250	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
23A172F150CB1H1		Genteq	Special	1700		150	1.75	Round	2.125	Electrolytic	1000	-40°C to 85°C
97F6505BX	BX	Genteq	Standard	17.5		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H112F200CB1H1		Genteq	Special	1100		200	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F5161		Genteq	Standard	15		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8056S	S	Genteq	Stock	5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B843F060FG1H1		Genteq	Special	84000		60	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
23A124F050EI1H1		Genteq	Special	12000 0		50	2.5	Round	5.625	Electrolytic	1000	-40°C to 85°C
27L432BX	BX	Genteq	Standard	22	7	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6678BX	BX	Genteq	Special	4.5		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6940BR	BR	Genteq	Standard	35		580	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6644BX	BX	Genteq	Special	45		300	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 90°C

23B682F250FI1H1		Genteq	Special	6800		250	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
23C812F150EE1H1		Genteq	Special	8100		150	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
42L3332		Genteq	Stock	0.33		2000	1.12	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
27L590BX	BX	Genteq	Standard	24	11	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6690		Genteq	Special	36	12	260	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M113F200FF1H1		Genteq	Special	11000		200	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
23A203F080DD1H1		Genteq	Special	20000		80	2	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F9678		Genteq	Standard	25	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F113F060DC1H1		Genteq	Special	11000		60	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
23B312F150DD1H1		Genteq	Special	3100		150	2	Round	3.125	Electrolytic	3000	-40°C to 85°C
PB400Y050C440EAB X	BX	PROLINE	Standard	40	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB500E000C370DA		PROLINE	Standard	50		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB450Z100T440DA		PROLINE	Standard	45	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H182F300CF1H1		Genteq	Special	1800		300	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F9203		Genteq	Standard	6		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5707BX	BX	Genteq	Special	7.5		370	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B902F150FE1H1		Genteq	Special	9000		150	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
23M192F250BH1H1		Genteq	Special	1900		250	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9012BX	BX	Genteq	Standard	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C113F100DD1H1		Genteq	Special	11000		100	2	Round	3.125	Electrolytic	1000	-45°C to 95°C
23B413F080EH1H1		Genteq	Special	41000		80	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F9640		Genteq	Standard	35		440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C183F100ED1H1		Genteq	Special	18000		100	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
23F113F060CD1H1		Genteq	Special	11000		60	1.75	Round	3.125	Electrolytic	1000	-55°C to 105°C
27L556		Genteq	Standard	70	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6746		Genteq	Standard	12		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B452F150DF1H1		Genteq	Special	4500		150	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
23M681F450CE1H1		Genteq	Special	680		450	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
27L7001RC	RC	Genteq	Standard	10		400	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
27L540		Genteq	Standard	16.5	11.5	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F243F060ED1H1		Genteq	Special	24000		60	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
23M142F350DD1H1		Genteq	Special	1400		350	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F5116		Genteq	Standard	40		440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B852F060CB1H1		Genteq	Special	8500		60	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
23H152F350ED1H1		Genteq	Special	1500		350	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9815S	S	Genteq	Stock	55	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5011		Genteq	Standard	10		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L378		Genteq	Standard	45	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5608BX	BX	Genteq	Special	35	7.5	370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C403F050DE1H1		Genteq	Special	40000		50	2	Round	3.625	Electrolytic	1000	-45°C to 95°C
PB350Y050C440EA		PROLINE	Standard	35	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A803F080FG1H1		Genteq	Special	80000		80	3	Round	4.625	Electrolytic	1000	-40°C to 85°C
27L1024BX	BX	Genteq	Standard	5		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6854		Genteq	Standard	34		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M992F200EH1H1		Genteq	Special	9900		200	2.5	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9979		Genteq	Standard	25	7.5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
40L6472		Genteq	Stock	0.47		600	0.46	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C
23F961F150BD1H1		Genteq	Special	960		150	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
23M221F400BB1H1		Genteq	Special	220		400	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
23A203F060BG1H1		Genteq	Special	20000		60	1.375	Round	4.625	Electrolytic	1000	-40°C to 85°C
97F8040		Genteq	Standard	40		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200Z075S370CABX	BX	PROLINE	Standard	20	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C

97F8243BX	BX	Genteq	Special	3		600	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6749BX	BX	Genteq	Standard	13.5		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB350Z050S440EA		PROLINE	Standard	35	5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9632S	S	Genteq	Stock	25		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600E000D440HAS	S	PROLINE	Stock	60		440	2	Oval	4.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
24DB450B370PA		Genteq	Standard	45		370	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
23F122F200BH1H1		Genteq	Special	1200		200	1.375	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F6622		Genteq	Standard	24		400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8045BX	BX	Genteq	Standard	65		240	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A153F075BG1H1		Genteq	Special	15000		75	1.375	Round	4.625	Electrolytic	1000	-40°C to 85°C
23A114F080FJ1H1		Genteq	Special	11000 0		80	3	Round	5.875	Electrolytic	1000	-40°C to 85°C
23C163F150FG1H1		Genteq	Special	16000		150	3	Round	4.625	Electrolytic	1000	-45°C to 95°C
97F8250BX	BX	Genteq	Standard	12		600	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F112F200DC1H1		Genteq	Special	1100		200	2	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F5520		Genteq	Special	45	5	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8020		Genteq	Special	54		440	2.5	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D293F035CH1H1		Genteq	Special	29000		35	1.75	Round	5.125	Electrolytic	1000	-55°C to 85°C
97F5337BX	BX	Genteq	Standard	4		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8070S	S	Genteq	Stock	55		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9609		Genteq	Standard	30		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5121BX	BX	Genteq	Special	15		440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6872BX	BX	Genteq	Standard	48		280	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J112F400EE1H1		Genteq	Special	1100		400	2.5	Round	3.625	Electrolytic	2000	-40°C to 105°C
25L2754BX	BX	Genteq	Standard	35	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M512F300EG1H1		Genteq	Special	5100		300	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB300E000C240CAS	S	PROLINE	Stock	30		240	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB550E000S370DAB X	BX	PROLINE	Standard	55		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9621		Genteq	Standard	50		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6860		Genteq	Standard	15		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L647		Genteq	Standard	50	10	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D563F020CI1H1		Genteq	Special	56000		20	3	Round	8.625	Electrolytic	1000	-55°C to 85°C
23C712F200EH1H1		Genteq	Special	7100		200	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
23J282F400FI1H1		Genteq	Special	2800		400	3	Round	5.625	Electrolytic	2000	-40°C to 105°C
PB350Y100C440EA		PROLINE	Standard	35	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB700E000T440EA		PROLINE	Standard	70		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB250E000A440EAS	S	PROLINE	Stock	25		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J512F250FF1H1		Genteq	Special	5100		250	3	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F9845		Genteq	Standard	40	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9045BX	BX	Genteq	Special	15	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B212F200DE1H1		Genteq	Special	2100		200	2	Round	3.625	Electrolytic	3000	-40°C to 85°C
PB500Z075T440EA		PROLINE	Standard	50	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F722F075BE1H1		Genteq	Special	7200		75	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
23C332F200CH1H1		Genteq	Special	3300		200	1.75	Round	5.125	Electrolytic	1000	-45°C to 95°C
23H122F250CC1H1		Genteq	Special	1200		250	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23F263F100FH1H1		Genteq	Special	26000		100	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
23H102F250BE1H1		Genteq	Special	1000		250	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
23A682F075BC1H1		Genteq	Special	6800		75	1.375	Round	2.625	Electrolytic	1000	-40°C to 85°C
23F771F200BE1H1		Genteq	Special	770		200	1.375	Round	3.625	Electrolytic	1000	-55°C to 105°C
23A482F075BB1H1		Genteq	Special	4800		75	1.375	Round	2.125	Electrolytic	1000	-40°C to 85°C

23A154F060FJ1H1		Genteq	Special	150000		60	3	Round	5.875	Electrolytic	1000	-40°C to 85°C
23J531F350CC1H1		Genteq	Special	530		350	1.75	Round	2.625	Electrolytic	2000	-40°C to 105°C
23C453F060CI1H1		Genteq	Special	45000		60	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6946BR	BR	Genteq	Standard	21		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9644BX	BX	Genteq	Standard	45		440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C263F150FL1H1		Genteq	Special	26000		150	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
23C603F075EI1H1		Genteq	Special	60000		75	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
PB700E000T370EABX	BX	PROLINE	Standard	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB100E000A370CABX	BX	PROLINE	Standard	10		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F232F250EE1H1		Genteq	Special	2300		250	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
23M371F450BE1H1		Genteq	Special	370		450	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
27L5201BX	BX	Genteq	Standard	50	10	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9204BX	BX	Genteq	Standard	7.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L889BX	BX	Genteq	Standard	45	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB125E000A370CA		PROLINE	Standard	12.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB400Z050T440CABX	BX	PROLINE	Standard	40	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5461BX	BX	Genteq	Special	15		370	1.75	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300Z075S370DA		PROLINE	Standard	30	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6805		Genteq	Standard	10		280	1.5	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L1030BX	BX	Genteq	Standard	2.5		370	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M852F300FH1H1		Genteq	Special	8500		300	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
23D373F028CH1H1		Genteq	Special	37000		28	1.75	Round	5.125	Electrolytic	1000	-55°C to 85°C
PB300E000C440DA		PROLINE	Standard	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J112F250DC1H1		Genteq	Special	1100		250	2	Round	2.625	Electrolytic	2000	-40°C to 105°C
97F5170BX	BX	Genteq	Special	20		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
42L2102		Genteq	Stock	0.1		1200	0.55	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23F472F080BD1H1		Genteq	Special	4700		80	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F9616		Genteq	Standard	40		370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J912F200FI1H1		Genteq	Special	9100		200	3	Round	5.625	Electrolytic	2000	-40°C to 105°C
97F6606RC	RC	Genteq	Standard	10		400	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L989BX	BX	Genteq	Special	30		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB550E000D440EABX	BX	PROLINE	Standard	55		440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9951BX	BX	Genteq	Standard	40	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6745		Genteq	Standard	21		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9366		Genteq	Standard	35		240	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L566BX	BX	Genteq	Standard	7.5		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B313F075DH1H1		Genteq	Special	31000		75	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
41L7301		Genteq	Stock	3		700	1.12	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23C104F080FL1H1		Genteq	Special	100000		80	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
23B792F080BF1H1		Genteq	Special	7900		80	1.375	Round	4.125	Electrolytic	3000	-40°C to 85°C
23H941F450DG1H1		Genteq	Special	940		450	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23D193F055CI1H1		Genteq	Special	19000		55	3	Round	8.625	Electrolytic	1000	-55°C to 85°C
PB350E000S440DABX	BX	PROLINE	Standard	35		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9884S	S	Genteq	Stock	45		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6839		Genteq	Special	43.5		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J481F400BH1H1		Genteq	Special	480		400	1.375	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F6711BX	BX	Genteq	Special	16		330	1.5	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F433F075EH1H1		Genteq	Special	43000		75	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
23F193F080CI1H1		Genteq	Special	19000		80	1.75	Round	5.625	Electrolytic	1000	-55°C to 105°C
23B472F100BG1H1		Genteq	Special	4700		100	1.375	Round	4.625	Electrolytic	3000	-40°C to 85°C

23A123F100CF1H1		Genteq	Special	12000		100	1.75	Round	4.125	Electrolytic	1000	-40°C to 85°C
97F9874BX	BX	Genteq	Standard	55	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9732		Genteq	Standard	25	7.5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6709BX	BX	Genteq	Special	14		330	1.5	Oval	3.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C403F075FD1H1		Genteq	Special	40000		75	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
27L946BX	BX	Genteq	Standard	40	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L961BX	BX	Genteq	Standard	25		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B104F050FH1H1		Genteq	Special	100000		50	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
23B132F200CD1H1		Genteq	Special	1300		200	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F6823BX	BX	Genteq	Standard	28		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C322F250DH1H1		Genteq	Special	3200		250	2	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F6727BX	BX	Genteq	Standard	32		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L705BX	BX	Genteq	Standard	42	22	280	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150Y100C370CA		PROLINE	Standard	15	10	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB300Y050C370DA		PROLINE	Standard	30	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6935BX	BX	Genteq	Special	10.5		540	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB450E000S440DA		PROLINE	Standard	45		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB450E000S440DABX	BX	PROLINE	Standard	45		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB300E000A370EA		PROLINE	Standard	30		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L480		Genteq	Special	20	6	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D842F035BD1H1		Genteq	Special	8400		35	1.375	Round	3.125	Electrolytic	1000	-55°C to 85°C
23B372F250EG1H1		Genteq	Special	3700		250	2.5	Round	4.625	Electrolytic	3000	-40°C to 85°C
23A143F100DE1H1		Genteq	Special	14000		100	2	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F9170		Genteq	Special	35		440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L591		Genteq	Standard	35	15	300	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8313BX	BX	Genteq	Special	46		600	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H602F300FG1H1		Genteq	Special	6000		300	3	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F9391BX	BX	Genteq	Special	80		370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9696BX	BX	Genteq	Standard	20	7.5	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5704		Genteq	Standard	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B182F150CC1H1		Genteq	Special	1800		150	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
23A153F150EI1H1		Genteq	Special	15000		150	2.5	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F6846		Genteq	Standard	29		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C572F100BE1H1		Genteq	Special	5700		100	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F6890		Genteq	Standard	18	10	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J252F250DG1H1		Genteq	Special	2500		250	2	Round	4.625	Electrolytic	2000	-40°C to 105°C
23J172F200BI1H1		Genteq	Special	1700		200	1.375	Round	5.625	Electrolytic	2000	-40°C to 105°C
23A134F080FL1H1		Genteq	Special	130000		80	3	Round	8.625	Electrolytic	1000	-40°C to 85°C
PB450Y075C370DABX	BX	PROLINE	Standard	45	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9625BX	BX	Genteq	Standard	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L797RC	RC	Genteq	Standard	15	7.5	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200Y100C370DA		PROLINE	Standard	20	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6517RC	RC	Genteq	Standard	15		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B352F150CF1H1		Genteq	Special	3500		150	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F6871BR	BR	Genteq	Standard	12		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9017BX	BX	Genteq	Special	20	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C114F060FG1H1		Genteq	Special	110000		60	3	Round	4.625	Electrolytic	1000	-45°C to 95°C

97F8005		Genteq	Special	30		440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5475BX	BX	Genteq	Special	20	4	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9632		Genteq	Standard	25		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5491		Genteq	Special	30	4	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J112F350DF1H1		Genteq	Special	1100		350	2	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F9069BX	BX	Genteq	Special	25		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F233F050CE1H1		Genteq	Special	23000		50	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
97F9613		Genteq	Standard	35		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B252F200CH1H1		Genteq	Special	2500		200	1.75	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F6698RC	RC	Genteq	Standard	13		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5066BX	BX	Genteq	Standard	10		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9669BX	BX	Genteq	Standard	40		440	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L6301		Genteq	Stock	3		600	0.89	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
27L542BX	BX	Genteq	Standard	10.5	8	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9203BX	BX	Genteq	Standard	6		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J232F250CH1H1		Genteq	Special	2300		250	1.75	Round	5.125	Electrolytic	2000	-40°C to 105°C
23A333F080DG1H1		Genteq	Special	33000		80	2	Round	4.625	Electrolytic	1000	-40°C to 85°C
23F962F100DG1H1		Genteq	Special	9600		100	2	Round	4.625	Electrolytic	1000	-55°C to 105°C
PB450Z050T440DAS	S	PROLINE	Stock	45	5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H561F400DC1H1		Genteq	Special	560		400	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F9840BX	BX	Genteq	Standard	40	5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9779BX	BX	Genteq	Standard	40	7.5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B402F200FD1H1		Genteq	Special	4000		200	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
23M112F400CF1H1		Genteq	Special	1100		400	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F9038		Genteq	Standard	17.5		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A333F100FE1H1		Genteq	Special	33000		100	3	Round	3.625	Electrolytic	1000	-40°C to 85°C
27L366BX	BX	Genteq	Standard	40		600	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1027		Genteq	Standard	10		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L7682		Genteq	Stock	0.68		700	0.67	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23H351F400BD1H1		Genteq	Special	350		400	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
23C711F200BC1H1		Genteq	Special	710		200	1.375	Round	2.625	Electrolytic	1000	-45°C to 95°C
97F6510BX	BX	Genteq	Special	50		260	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H132F350DF1H1		Genteq	Special	1300		350	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8073S	S	Genteq	Stock	70		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9242BX	BX	Genteq	Special	20		440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6698BX	BX	Genteq	Standard	13		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6505RC	RC	Genteq	Standard	17.5		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C532F200EF1H1		Genteq	Special	5300		200	2.5	Round	4.125	Electrolytic	1000	-45°C to 95°C
23A453F100FG1H1		Genteq	Special	45000		100	3	Round	4.625	Electrolytic	1000	-40°C to 85°C
PB200Y075C370CAB X	BX	PROLINE	Standard	20	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A632F060BB1H1		Genteq	Special	6300		60	1.375	Round	2.125	Electrolytic	1000	-40°C to 85°C
23J311F300BB1H1		Genteq	Special	310		300	1.375	Round	2.125	Electrolytic	2000	-40°C to 105°C
23B303F060DF1H1		Genteq	Special	30000		60	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F6940BX	BX	Genteq	Standard	35		580	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A403F060DF1H1		Genteq	Special	40000		60	2	Round	4.125	Electrolytic	1000	-40°C to 85°C
PB550E000D440EAS	S	PROLINE	Stock	55		440	2	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB450Z100T440DABX	BX	PROLINE	Standard	45	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J421F400BG1H1		Genteq	Special	420		400	1.375	Round	4.625	Electrolytic	2000	-40°C to 105°C
23F753F060FI1H1		Genteq	Special	75000		60	3	Round	5.625	Electrolytic	1000	-55°C to 105°C
27L862BR	BR	Genteq	Standard	35	24	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6537RC	RC	Genteq	Standard	24		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F6872RC	RC	Genteq	Standard	48		280	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A114F075FJ1H1		Genteq	Special	110000		75	3	Round	5.875	Electrolytic	1000	-40°C to 85°C
23F252F150CF1H1		Genteq	Special	2500		150	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
27L637		Genteq	Special	80	5	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F212F200DF1H1		Genteq	Special	2100		200	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
23D982F016BB1H1		Genteq	Special	9800		16	1.375	Round	2.125	Electrolytic	1000	-55°C to 85°C
97F6921RC	RC	Genteq	Standard	26		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L827RC	RC	Genteq	Standard	18	10	330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H721F350DC1H1		Genteq	Special	720		350	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
97F6768BR	BR	Genteq	Standard	14		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A842F100DC1H1		Genteq	Special	8400		100	2	Round	2.625	Electrolytic	1000	-40°C to 85°C
PB075E000A440CA		PROLINE	Standard	7.5		440	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B102F200CC1H1		Genteq	Special	1000		200	1.75	Round	2.625	Electrolytic	3000	-40°C to 85°C
97F9115		Genteq	Special	45		370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6812		Genteq	Standard	17.5		280	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H322F250CI1H1		Genteq	Special	3200		250	1.75	Round	5.625	Electrolytic	2000	-40°C to 85°C
23B272F100CB1H1		Genteq	Special	2700		100	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F9689BX	BX	Genteq	Standard	40	5	370	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C382F150CE1H1		Genteq	Special	3800		150	1.75	Round	3.625	Electrolytic	1000	-45°C to 95°C
97F6863		Genteq	Special	22.5		280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M312F300DG1H1		Genteq	Special	3100		300	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F8063BX	BX	Genteq	Standard	20		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9004BX	BX	Genteq	Standard	15		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M182F200CC1H1		Genteq	Special	1800		200	1.75	Round	2.625	Electrolytic	2000	-40°C to 85°C
23H721F400BI1H1		Genteq	Special	720		400	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
41L2101		Genteq	Stock	1		250	0.43	Round	0.75	Dry-Axial Leaded	100000	-40°C to 85°C
23B222F250ED1H1		Genteq	Special	2200		250	2.5	Round	3.125	Electrolytic	3000	-40°C to 85°C
23B133F100DH1H1		Genteq	Special	13000		100	2	Round	5.125	Electrolytic	3000	-40°C to 85°C
23F162F200CF1H1		Genteq	Special	1600		200	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
PB600E000C370EABX	BX	PROLINE	Standard	60		370	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8038BX	BX	Genteq	Standard	30		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9884		Genteq	Standard	45		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H442F300FE1H1		Genteq	Special	4400		300	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F9978		Genteq	Standard	25	5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J962F250FL1H1		Genteq	Special	9600		250	3	Round	8.625	Electrolytic	2000	-40°C to 105°C
97F6887BX	BX	Genteq	Standard	38	17	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB600E000T370DA		PROLINE	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L7007		Genteq	Special	18	8	330	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 100°C
97F8039S	S	Genteq	Stock	35		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M132F200CB1H1		Genteq	Special	1300		200	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23D143F035BG1H1		Genteq	Special	14000		35	1.375	Round	4.625	Electrolytic	1000	-55°C to 85°C
97F9451RR	RR	Genteq	Standard	20	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5564		Genteq	Standard	8		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6801BX	BX	Genteq	Standard	6		280	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB600E000P370EABX	BX	PROLINE	Standard	60		370	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F442F150DH1H1		Genteq	Special	4400		150	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
23J192F400FF1H1		Genteq	Special	1900		400	3	Round	4.125	Electrolytic	2000	-40°C to 105°C
42L3223		Genteq	Stock	0.022		2000	0.41	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23C153F075BI1H1		Genteq	Special	15000		75	1.375	Round	5.625	Electrolytic	1000	-45°C to 95°C
23H661F350BF1H1		Genteq	Special	660		350	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8054		Genteq	Standard	3		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L414		Genteq	Standard	70	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C

23H282F250CH1H1		Genteq	Special	2800		250	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9871BX	BX	Genteq	Standard	20		440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9810		Genteq	Standard	15	5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F302F200EE1H1		Genteq	Special	3000		200	2.5	Round	3.625	Electrolytic	1000	-55°C to 105°C
PB100E000A370CAS	S	PROLINE	Stock	10		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M282F400FE1H1		Genteq	Special	2800		400	3	Round	3.625	Electrolytic	2000	-40°C to 85°C
23M401F400BD1H1		Genteq	Special	400		400	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F9978BX	BX	Genteq	Standard	25	5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D123F020BC1H1		Genteq	Special	12000		20	1.375	Round	2.625	Electrolytic	1000	-55°C to 85°C
97F6855		Genteq	Standard	22.5		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L791BX	BX	Genteq	Standard	8		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C463F050CI1H1		Genteq	Special	46000		50	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
23M262F300DF1H1		Genteq	Special	2600		300	2	Round	4.125	Electrolytic	2000	-40°C to 85°C
PB300E000P440DAS	S	PROLINE	Stock	30		440	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C362F250DI1H1		Genteq	Special	3600		250	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
23C184F050FL1H1		Genteq	Special	18000 0		50	3	Round	8.625	Electrolytic	1000	-45°C to 95°C
23M232F250DD1H1		Genteq	Special	2300		250	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
23A113F050BC1H1		Genteq	Special	11000		50	1.375	Round	2.625	Electrolytic	1000	-40°C to 85°C
PB500Z050T370DA		PROLINE	Standard	50	5	370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C102F250CC1H1		Genteq	Special	1000		250	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
23H271F450CB1H1		Genteq	Special	270		450	1.75	Round	2.125	Electrolytic	2000	-40°C to 85°C
23B253F050CF1H1		Genteq	Special	25000		50	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23B292F080BB1H1		Genteq	Special	2900		80	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
23F273F080FD1H1		Genteq	Special	27000		80	3	Round	3.125	Electrolytic	1000	-55°C to 105°C
97F9010S	S	Genteq	Stock	55		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D523F016CG1H1		Genteq	Special	52000		16	1.75	Round	4.625	Electrolytic	1000	-55°C to 85°C
97F6676BX	BX	Genteq	Special	3		480	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9897BX	BX	Genteq	Standard	60	5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J162F400FE1H1		Genteq	Special	1600		400	3	Round	3.625	Electrolytic	2000	-40°C to 105°C
23C402F250FD1H1		Genteq	Special	4000		250	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F6643BR	BR	Genteq	Special	30		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A273F050CD1H1		Genteq	Special	27000		50	1.75	Round	3.125	Electrolytic	1000	-40°C to 85°C
23J261F400BD1H1		Genteq	Special	260		400	1.375	Round	3.125	Electrolytic	2000	-40°C to 105°C
23F113F080CE1H1		Genteq	Special	11000		80	1.75	Round	3.625	Electrolytic	1000	-55°C to 105°C
23B733F075FH1H1		Genteq	Special	73000		75	3	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB500E000P240EA		PROLINE	Standard	50		240	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B872F200FI1H1		Genteq	Special	8700		200	3	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F5063BX	BX	Genteq	Special	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8256		Genteq	Standard	35		600	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9040BX	BX	Genteq	Standard	25		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A782F050BB1H1		Genteq	Special	7800		50	1.375	Round	2.125	Electrolytic	1000	-40°C to 85°C
97F5710		Genteq	Special	10		370	1.25	Oval	2.62	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D114F007CI1H1		Genteq	Special	11000 0		7.5	3	Round	8.625	Electrolytic	1000	-55°C to 85°C
23H682F300FH1H1		Genteq	Special	6800		300	3	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F6836BR	BR	Genteq	Standard	48		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
27L204BX	BX	Genteq	Standard	35	10	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9042BX	BX	Genteq	Standard	55		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB300E000P440DA		PROLINE	Standard	30		440	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A583F060EE1H1		Genteq	Special	58000		60	2.5	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F5913		Genteq	Standard	30		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J391F400CC1H1		Genteq	Special	390		400	1.75	Round	2.625	Electrolytic	2000	-40°C to 105°C
23F103F150FH1H1		Genteq	Special	10000		150	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
27L476		Genteq	Standard	33	15	330	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C

97F9614S	S	Genteq	Stock	40		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B233F060CF1H1		Genteq	Special	23000		60	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23F103F060BG1H1		Genteq	Special	10000		60	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
23D173F035BI1H1		Genteq	Special	17000		35	1.375	Round	5.625	Electrolytic	1000	-55°C to 85°C
24DB450B250PA		Genteq	Standard	45		250	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
23A683F075EH1H1		Genteq	Special	68000		75	2.5	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F9832BX	BX	Genteq	Standard	45	10	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9683		Genteq	Standard	30	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C532F250EH1H1		Genteq	Special	5300		250	2.5	Round	5.125	Electrolytic	1000	-45°C to 95°C
23F611F200BD1H1		Genteq	Special	610		200	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
23F402F200EG1H1		Genteq	Special	4000		200	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F9830		Genteq	Standard	35	10	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F722F150EH1H1		Genteq	Special	7200		150	2.5	Round	5.125	Electrolytic	1000	-55°C to 105°C
23C843F080FJ1H1		Genteq	Special	84000		80	3	Round	5.875	Electrolytic	1000	-45°C to 95°C
97F6857BX	BX	Genteq	Standard	8		280	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5056BX	BX	Genteq	Standard	40		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9885BX	BX	Genteq	Standard	50	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A872F075CB1H1		Genteq	Special	8700		75	1.75	Round	2.125	Electrolytic	1000	-40°C to 85°C
97F9752		Genteq	Standard	25	4	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J211F350BB1H1		Genteq	Special	210		350	1.375	Round	2.125	Electrolytic	2000	-40°C to 105°C
23F752F050BC1H1		Genteq	Special	7500		50	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
97F9004		Genteq	Standard	15		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L7471		Genteq	Stock	4.7		700	1.18	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
23C103F200FH1H1		Genteq	Special	10000		200	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
23M232F300DE1H1		Genteq	Special	2300		300	2	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6535RC	RC	Genteq	Standard	24		400	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9043BX	BX	Genteq	Standard	60		440	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9968BX	BX	Genteq	Standard	30	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6921BR	BR	Genteq	Standard	26		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9046		Genteq	Special	15	10	440	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6703BX	BX	Genteq	Standard	8		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150E000A440EA		PROLINE	Standard	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L68BX	BX	Genteq	Standard	30	18	400	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5573BX	BX	Genteq	Special	10		370	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6778BX	BX	Genteq	Standard	45		330	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9848S	S	Genteq	Stock	35	5	440	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C343F080DI1H1		Genteq	Special	34000		80	2	Round	5.625	Electrolytic	1000	-45°C to 95°C
23A753F050DI1H1		Genteq	Special	75000		50	2	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F9028BX	BX	Genteq	Special	50	5	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB200E000S370CA		PROLINE	Standard	20		370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H202F400EG1H1		Genteq	Special	2000		400	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
23J422F200FD1H1		Genteq	Special	4200		200	3	Round	3.125	Electrolytic	2000	-40°C to 105°C
97F6656BX	BX	Genteq	Standard	7.5		400	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B352F100DB1H1		Genteq	Special	3500		100	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F9027		Genteq	Special	45	5	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9996BX	BX	Genteq	Standard	40	7.5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L2681		Genteq	Stock	6.8		250	0.79	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23J321F400BE1H1		Genteq	Special	320		400	1.375	Round	3.625	Electrolytic	2000	-40°C to 105°C
23J591F400CE1H1		Genteq	Special	590		400	1.75	Round	3.625	Electrolytic	2000	-40°C to 105°C
27L176RC	RC	Genteq	Special	7.5		540	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C773F050EG1H1		Genteq	Special	77000		50	2.5	Round	4.625	Electrolytic	1000	-45°C to 95°C

23B842F075DB1H1		Genteq	Special	8400		75	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
97F8055		Genteq	Standard	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6923BX	BX	Genteq	Special	32		540	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB550Z075T440EA		PROLINE	Standard	55	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L572BX	BX	Genteq	Standard	12.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A593F080FE1H1		Genteq	Special	59000		80	3	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F9008		Genteq	Standard	45		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L573RR	RR	Genteq	Standard	40	15	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M172F300B1H1		Genteq	Special	1700		300	1.375	Round	5.625	Electrolytic	2000	-40°C to 85°C
97F9202BX	BX	Genteq	Standard	5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB030E000A440AA		PROLINE	Standard	3		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J352F350FH1H1		Genteq	Special	3500		350	3	Round	5.125	Electrolytic	2000	-40°C to 105°C
23C143F075BH1H1		Genteq	Special	14000		75	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
PB250Y075C370CAB X	BX	PROLINE	Standard	25	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M801F450CF1H1		Genteq	Special	800		450	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F8059		Genteq	Standard	10		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6715BX	BX	Genteq	Standard	19		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9086BX	BX	Genteq	Special	30		440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9028		Genteq	Special	50	5	370	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M102F400DD1H1		Genteq	Special	1000		400	2	Round	3.125	Electrolytic	2000	-40°C to 85°C
PB060E000A440BA		PROLINE	Standard	6		440	1.25	Oval	2.12	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B553F075FF1H1		Genteq	Special	55000		75	3	Round	4.125	Electrolytic	3000	-40°C to 85°C
23A203F075CE1H1		Genteq	Special	20000		75	1.75	Round	3.625	Electrolytic	1000	-40°C to 85°C
97F6530RC	RC	Genteq	Standard	40		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6695BX	BX	Genteq	Special	6.5		480	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C104F050E11H1		Genteq	Special	10000 0		50	2.5	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F6515		Genteq	Standard	10		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J222F300DH1H1		Genteq	Special	2200		300	2	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F5463BX	BX	Genteq	Standard	20		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9603BX	BX	Genteq	Standard	20		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9802BX	BX	Genteq	Standard	50		370	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J532F200FE1H1		Genteq	Special	5300		200	3	Round	3.625	Electrolytic	2000	-40°C to 105°C
23B133F080CE1H1		Genteq	Special	13000		80	1.75	Round	3.625	Electrolytic	3000	-40°C to 85°C
23B323F050DF1H1		Genteq	Special	32000		50	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F5239		Genteq	Standard	55		480	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H371F450BF1H1		Genteq	Special	370		450	1.375	Round	4.125	Electrolytic	2000	-40°C to 85°C
23C572F150DF1H1		Genteq	Special	5700		150	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F5816		Genteq	Special	25	7.5	370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C711F250BD1H1		Genteq	Special	710		250	1.375	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F6758BX	BX	Genteq	Standard	15		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F153F060DD1H1		Genteq	Special	15000		60	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
23M701F200BB1H1		Genteq	Special	700		200	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
23H202F200CD1H1		Genteq	Special	2000		200	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
27L470		Genteq	Standard	25	10	300	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5161BX	BX	Genteq	Standard	15		370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB150E000A440EABX	BX	PROLINE	Standard	15		440	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6641		Genteq	Special	52		170	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L4333		Genteq	Stock	0.033		3000	0.79	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
23F113F100DH1H1		Genteq	Special	11000		100	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
23F163F060CF1H1		Genteq	Special	16000		60	1.75	Round	4.125	Electrolytic	1000	-55°C to 105°C
40L3151		Genteq	Stock	1.5		400	0.48	Oval	1.25	Dry-Axial Leaded	100000	-55°C to 105°C

97F6746BR	BR	Genteq	Standard	12		330	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H162F350DG1H1		Genteq	Special	1600		350	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
23F721F150BC1H1		Genteq	Special	720		150	1.375	Round	2.625	Electrolytic	1000	-55°C to 105°C
23J142F250BI1H1		Genteq	Special	1400		250	1.375	Round	5.625	Electrolytic	2000	-40°C to 105°C
25L501BX	BX	Genteq	Standard	40		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M132F350CE1H1		Genteq	Special	1300		350	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
23C573F050EE1H1		Genteq	Special	57000		50	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
41L2300		Genteq	Stock	30		250	1.16	Round	2.17	Dry-Axial Leaded	100000	-40°C to 85°C
PB800Z075T440EABX	BX	PROLINE	Standard	80	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C263F080CI1H1		Genteq	Special	26000		80	1.75	Round	5.625	Electrolytic	1000	-45°C to 95°C
97F8058		Genteq	Standard	7.5		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F841F200CC1H1		Genteq	Special	840		200	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
23C132F200CC1H1		Genteq	Special	1300		200	1.75	Round	2.625	Electrolytic	1000	-45°C to 95°C
23H431F400BE1H1		Genteq	Special	430		400	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F8078		Genteq	Special	8		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A233F100EE1H1		Genteq	Special	23000		100	2.5	Round	3.625	Electrolytic	1000	-40°C to 85°C
PB750E000T370EA		PROLINE	Standard	75		370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B682F200FG1H1		Genteq	Special	6800		200	3	Round	4.625	Electrolytic	3000	-40°C to 85°C
23F453F050DH1H1		Genteq	Special	45000		50	2	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F8070BX	BX	Genteq	Standard	55		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9631		Genteq	Standard	20		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F112F250DD1H1		Genteq	Special	1100		250	2	Round	3.125	Electrolytic	1000	-55°C to 105°C
41L2251		Genteq	Stock	2.5		250	0.47	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
PB700Z075T370EA		PROLINE	Standard	70	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F143F080DE1H1		Genteq	Special	14000		80	2	Round	3.625	Electrolytic	1000	-55°C to 105°C
27L727BR	BR	Genteq	Standard	45	19	300	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A862F100CD1H1		Genteq	Special	8600		100	1.75	Round	3.125	Electrolytic	1000	-40°C to 85°C
27L480BX	BX	Genteq	Special	20	6	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9200		Genteq	Special	3		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B793F050EI1H1		Genteq	Special	79000		50	2.5	Round	5.625	Electrolytic	3000	-40°C to 85°C
23B541F250CB1H1		Genteq	Special	540		250	1.75	Round	2.125	Electrolytic	3000	-40°C to 85°C
23J192F400EI1H1		Genteq	Special	1900		400	2.5	Round	5.625	Electrolytic	2000	-40°C to 105°C
PB400E000C370DAS	S	PROLINE	Stock	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB600E000S370DA		PROLINE	Standard	60		370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23C322F200DF1H1		Genteq	Special	3200		200	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9200BX	BX	Genteq	Special	3		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6659		Genteq	Standard	12		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8071S	S	Genteq	Stock	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6854BX	BX	Genteq	Standard	34		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8036BX	BX	Genteq	Standard	15		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B152F100BB1H1		Genteq	Special	1500		100	1.375	Round	2.125	Electrolytic	3000	-40°C to 85°C
23C612F060BB1H1		Genteq	Special	6100		60	1.375	Round	2.125	Electrolytic	1000	-45°C to 95°C
23M901F400CE1H1		Genteq	Special	900		400	1.75	Round	3.625	Electrolytic	2000	-40°C to 85°C
97F6855BX	BX	Genteq	Standard	22.5		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150Z100S370CA		PROLINE	Standard	15	10	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6682BX	BX	Genteq	Special	31.5		420	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6533BR	BR	Genteq	Standard	30		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5043		Genteq	Special	10		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9026		Genteq	Special	40	10	370	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600E000T440EABX	BX	PROLINE	Standard	60		440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L443BX	BX	Genteq	Standard	17	7	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F342F200FD1H1		Genteq	Special	3400		200	3	Round	3.125	Electrolytic	1000	-55°C to 105°C

97F6733BX	BX	Genteq	Special	40		330	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23A173F100CH1H1		Genteq	Special	17000		100	1.75	Round	5.125	Electrolytic	1000	-40°C to 85°C
97F9071		Genteq	Special	35		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9849S	S	Genteq	Stock	40	5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
25L261		Genteq	Standard	80	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6767		Genteq	Standard	10		330	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M552F250EF1H1		Genteq	Special	5500		250	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
23H222F350EF1H1		Genteq	Special	2200		350	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
27L522		Genteq	Standard	80	7.5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C242F250DF1H1		Genteq	Special	2400		250	2	Round	4.125	Electrolytic	1000	-45°C to 95°C
97F9855		Genteq	Standard	40	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6952		Genteq	Standard	36		540	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6692BX	BX	Genteq	Special	8.5		480	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6539		Genteq	Standard	14		400	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M232F200BG1H1		Genteq	Special	2300		200	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB2502075S370CA		PROLINE	Standard	25	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9011		Genteq	Standard	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9811BX	BX	Genteq	Standard	15	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6761		Genteq	Standard	17.5		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5388S	S	Genteq	Stock	12.5		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F313F050CG1H1		Genteq	Special	31000		50	1.75	Round	4.625	Electrolytic	1000	-55°C to 105°C
97F8039BX	BX	Genteq	Standard	35		240	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9843BX	BX	Genteq	Standard	40	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J591F350BG1H1		Genteq	Special	590		350	1.375	Round	4.625	Electrolytic	2000	-40°C to 105°C
97F9039BX	BX	Genteq	Standard	20		440	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D783F007CF1H1		Genteq	Special	78000		7.5	1.75	Round	4.125	Electrolytic	1000	-55°C to 85°C
27L1050BX	BX	Genteq	Standard	25	10	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M301F350BB1H1		Genteq	Special	300		350	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
23C563F060EE1H1		Genteq	Special	56000		60	2.5	Round	3.625	Electrolytic	1000	-45°C to 95°C
PB350E000A370EA		PROLINE	Standard	35		370	1.25	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A213F150FI1H1		Genteq	Special	21000		150	3	Round	5.625	Electrolytic	1000	-40°C to 85°C
97F6755BR	BR	Genteq	Standard	26		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H203F200BH1H1		Genteq	Special	2000		200	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
23H342F350EI1H1		Genteq	Special	3400		350	2.5	Round	5.625	Electrolytic	2000	-40°C to 85°C
PB5002050T440HA		PROLINE	Standard	50	5	440	2.5	Round	4.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5781		Genteq	Standard	50	7.5	440	2	Oval	5.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B312F250FD1H1		Genteq	Special	3100		250	3	Round	3.125	Electrolytic	3000	-40°C to 85°C
23M142F300BG1H1		Genteq	Special	1400		300	1.375	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6871BX	BX	Genteq	Standard	12		280	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9037		Genteq	Standard	15		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L729RR	RR	Genteq	Special	20	4	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23J462F300FG1H1		Genteq	Special	4600		300	3	Round	4.625	Electrolytic	2000	-40°C to 105°C
23M142F400CH1H1		Genteq	Special	1400		400	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F9683BX	BX	Genteq	Standard	30	7.5	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D113F055BI1H1		Genteq	Special	11000		55	1.375	Round	5.625	Electrolytic	1000	-55°C to 85°C
23F383F075EG1H1		Genteq	Special	38000		75	2.5	Round	4.625	Electrolytic	1000	-55°C to 105°C
23M801F400BH1H1		Genteq	Special	800		400	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
PB300E000S370CA		PROLINE	Standard	30		370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F9826BX	BX	Genteq	Standard	25	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H152F350CH1H1		Genteq	Special	1500		350	1.75	Round	5.125	Electrolytic	2000	-40°C to 85°C

97F5114BX	BX	Genteq	Special	35		370	2	Round	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9462		Genteq	Standard	40	10	370	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C143F060BE1H1		Genteq	Special	14000		60	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
23B213F100EH1H1		Genteq	Special	21000		100	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
97F6927		Genteq	Special	11.5	3	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200Z050S440CA		PROLINE	Standard	20	5	440	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
PB300Y100C440EABX	BX	PROLINE	Standard	30	10	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F673F060FH1H1		Genteq	Special	67000		60	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
97F8078BX	BX	Genteq	Special	8		440	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6093BX	BX	Genteq	Special	2.5		660	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23A154F060FI1H1		Genteq	Special	150000		60	3	Round	5.625	Electrolytic	1000	-40°C to 85°C
27L63BX	BX	Genteq	Standard	80		370	2.5	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C892F075BE1H1		Genteq	Special	8900		75	1.375	Round	3.625	Electrolytic	1000	-45°C to 95°C
23F232F100CB1H1		Genteq	Special	2300		100	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
23D842F055BG1H1		Genteq	Special	8400		55	1.375	Round	4.625	Electrolytic	1000	-55°C to 85°C
27L589RR	RR	Genteq	Standard	10	5	400	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9121		Genteq	Standard	15		370	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F5459BX	BX	Genteq	Standard	12.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23B663F060EH1H1		Genteq	Special	66000		60	2.5	Round	5.125	Electrolytic	3000	-40°C to 85°C
PB300E000S440DABX	BX	PROLINE	Standard	30		440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A263F050DC1H1		Genteq	Special	26000		50	2	Round	2.625	Electrolytic	1000	-40°C to 85°C
23F143F050BF1H1		Genteq	Special	14000		50	1.375	Round	4.125	Electrolytic	1000	-55°C to 105°C
23B292F150BI1H1		Genteq	Special	2900		150	1.375	Round	5.625	Electrolytic	3000	-40°C to 85°C
97F9739BX	BX	Genteq	Standard	40	5	440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB250Y075C370CA		PROLINE	Standard	25	7.5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6686		Genteq	Special	11.5		480	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6703RC	RC	Genteq	Standard	8		330	1.25	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6933		Genteq	Standard	18		540	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6712BX	BX	Genteq	Special	17.5		330	1.5	Oval	3.5	Oil-Filled (UL Approved)	60000	-40°C to 90°C
42L4103		Genteq	Stock	0.01		3000	0.47	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C
97F9978S	S	Genteq	Stock	25	5	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB600E000T370DABX	BX	PROLINE	Standard	60		370	2.5	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F802F080BG1H1		Genteq	Special	8000		80	1.375	Round	4.625	Electrolytic	1000	-55°C to 105°C
23J112F300DD1H1		Genteq	Special	1100		300	2	Round	3.125	Electrolytic	2000	-40°C to 105°C
97F9123BX	BX	Genteq	Special	17.5		370	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9494BX	BX	Genteq	Standard	35	7.5	440	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6933BX	BX	Genteq	Standard	18		540	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C302F150DC1H1		Genteq	Special	3000		150	2	Round	2.625	Electrolytic	1000	-45°C to 95°C
97F6850		Genteq	Standard	45		280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F193F075DF1H1		Genteq	Special	19000		75	2	Round	4.125	Electrolytic	1000	-55°C to 105°C
23F553F075FG1H1		Genteq	Special	55000		75	3	Round	4.625	Electrolytic	1000	-55°C to 105°C
27L1003RR	RR	Genteq	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6788BR	BR	Genteq	Standard	2.5		330	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9871		Genteq	Standard	20		440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB040E000A440AA		PROLINE	Standard	4		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	10000	-40°C to 70°C
41L4681		Genteq	Stock	6.8		400	0.98	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
97F6922BX	BX	Genteq	Special	8		525	1.5	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB300Z050S440DA		PROLINE	Standard	30	5	440	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F921F150CB1H1		Genteq	Special	920		150	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C

23H112F300DC1H1		Genteq	Special	1100		300	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
PB400Z075S370DA		PROLINE	Standard	40	7.5	370	2	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23A183F100ED1H1		Genteq	Special	18000		100	2.5	Round	3.125	Electrolytic	1000	-40°C to 85°C
97F6945BX	BX	Genteq	Standard	24		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C582F250FF1H1		Genteq	Special	5800		250	3	Round	4.125	Electrolytic	1000	-45°C to 95°C
25L502BX	BX	Genteq	Standard	35		440	1.75	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23J152F200BH1H1		Genteq	Special	1500		200	1.375	Round	5.125	Electrolytic	2000	-40°C to 105°C
97F6622RC	RC	Genteq	Standard	24		400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23D113F028BD1H1		Genteq	Special	11000		28	1.375	Round	3.125	Electrolytic	1000	-55°C to 85°C
PB550Z075T440EABX	BX	PROLINE	Standard	55	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23J561F300CB1H1		Genteq	Special	560		300	1.75	Round	2.125	Electrolytic	2000	-40°C to 105°C
PB400E000P440EABX	BX	PROLINE	Standard	40		440	1.75	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23F522F250FH1H1		Genteq	Special	5200		250	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
23M402F250DG1H1		Genteq	Special	4000		250	2	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F6622BR	BR	Genteq	Standard	24		400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9006BX	BX	Genteq	Standard	25		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9600BX	BX	Genteq	Standard	17.5		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6930RC	RC	Genteq	Standard	10		580	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB700Z100T370EA		PROLINE	Standard	70	10	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23H401F300BB1H1		Genteq	Special	400		300	1.375	Round	2.125	Electrolytic	2000	-40°C to 85°C
97F9207BX	BX	Genteq	Standard	25		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6680RC	RC	Genteq	Special	24		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB150Y050C370CABX	BX	PROLINE	Standard	15	5	370	1.75	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L444BR	BR	Genteq	Special	37	11	300	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB200E000P370CA		PROLINE	Standard	20		370	1.75	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6506		Genteq	Standard	14		330	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9052BX	BX	Genteq	Special	30	5	440	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6073		Genteq	Special	15		660	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB100E000A370CA		PROLINE	Standard	10		370	1.25	Oval	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F5483BX	BX	Genteq	Special	35	4	370	1.75	Oval	4.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L729BR	BR	Genteq	Special	20	4	400	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C263F100FD1H1		Genteq	Special	26000		100	3	Round	3.125	Electrolytic	1000	-45°C to 95°C
PB800Z075T440EA		PROLINE	Standard	80	7.5	440	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F8065		Genteq	Standard	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H352F250DH1H1		Genteq	Special	3500		250	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
23M352F300DH1H1		Genteq	Special	3500		300	2	Round	5.125	Electrolytic	2000	-40°C to 85°C
27L709		Genteq	Standard	26		400	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9444BX	BX	Genteq	Standard	15		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9061BX	BX	Genteq	Standard	55	10	440	2	Oval	6.25	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23F513F080FH1H1		Genteq	Special	51000		80	3	Round	5.125	Electrolytic	1000	-55°C to 105°C
23C133F080BH1H1		Genteq	Special	13000		80	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
23B532F150DG1H1		Genteq	Special	5300		150	2	Round	4.625	Electrolytic	3000	-40°C to 85°C
97F8084		Genteq	Standard	60		440	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9832		Genteq	Standard	45	10	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6774RC	RC	Genteq	Standard	24		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F8065S	S	Genteq	Stock	30		370	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
41L2200		Genteq	Stock	20		250	1.1	Round	1.65	Dry-Axial Leaded	100000	-40°C to 85°C
23H242F300ED1H1		Genteq	Special	2400		300	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
42L1472		Genteq	Stock	0.47		850	0.67	Round	1.22	Dry-Axial Leaded	100000	-40°C to 85°C

23B542F100BH1H1		Genteq	Special	5400		100	1.375	Round	5.125	Electrolytic	3000	-40°C to 85°C
23H411F450DC1H1		Genteq	Special	410		450	2	Round	2.625	Electrolytic	2000	-40°C to 85°C
40L3471		Genteq	Stock	4.7		400	0.64	Oval	1.75	Dry-Axial Leaded	100000	-55°C to 105°C
23M452F350FF1H1		Genteq	Special	4500		350	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
25L6755RR	RR	Genteq	Standard	20	8	280	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F622F060BD1H1		Genteq	Special	6200		60	1.375	Round	3.125	Electrolytic	1000	-55°C to 105°C
23M372F350EG1H1		Genteq	Special	3700		350	2.5	Round	4.625	Electrolytic	2000	-40°C to 85°C
PB500Y075D440GA		PROLINE	Standard	50	7.5	440	2	Oval	5.25	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M172F350CG1H1		Genteq	Special	1700		350	1.75	Round	4.625	Electrolytic	2000	-40°C to 85°C
97F8246		Genteq	Standard	6		600	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F7050		Genteq	Special	120		240	2	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D563F007BH1H1		Genteq	Special	56000		7.5	1.375	Round	5.125	Electrolytic	1000	-55°C to 85°C
PB400Z075S440EA		PROLINE	Standard	40	7.5	440	2	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
97F6533RC	RC	Genteq	Standard	30		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5501BX	BX	Genteq	Special	25	5	440	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23C182F200BH1H1		Genteq	Special	1800		200	1.375	Round	5.125	Electrolytic	1000	-45°C to 95°C
23F242F200ED1H1		Genteq	Special	2400		200	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
23F652F080CC1H1		Genteq	Special	6500		80	1.75	Round	2.625	Electrolytic	1000	-55°C to 105°C
PB150Z075S370CA		PROLINE	Standard	15	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
27L382BX	BX	Genteq	Standard	8.5	3.5	280	1.75	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 90°C
24DB250B370PA		Genteq	Standard	25		370	1.75	Round	3.189	Dry (UL Construction Only)	60000	-40°C to 70°C
27L1021		Genteq	Standard	2		440	1.25	Oval	1.56	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23D313F020BI1H1		Genteq	Special	31000		20	1.375	Round	5.625	Electrolytic	1000	-55°C to 85°C
23J381F400BF1H1		Genteq	Special	380		400	1.375	Round	4.125	Electrolytic	2000	-40°C to 105°C
97F6761BX	BX	Genteq	Standard	17.5		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F591F200CB1H1		Genteq	Special	590		200	1.75	Round	2.125	Electrolytic	1000	-55°C to 105°C
23B512F100CD1H1		Genteq	Special	5100		100	1.75	Round	3.125	Electrolytic	3000	-40°C to 85°C
97F6603BR	BR	Genteq	Special	24		400	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
PB700Z050T370EABX	BX	PROLINE	Standard	70	5	370	2.5	Round	4.75	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M102F350CD1H1		Genteq	Special	1000		350	1.75	Round	3.125	Electrolytic	2000	-40°C to 85°C
27L724RR	RR	Genteq	Standard	24	11	280	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9743BX	BX	Genteq	Standard	17.5		370	1.25	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23M142F200BD1H1		Genteq	Special	1400		200	1.375	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F6755		Genteq	Standard	26		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6867		Genteq	Standard	52		280	2	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23C134F060FH1H1		Genteq	Special	13000 0		60	3	Round	5.125	Electrolytic	1000	-45°C to 95°C
97F6931BX	BX	Genteq	Standard	20		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B383F075EF1H1		Genteq	Special	38000		75	2.5	Round	4.125	Electrolytic	3000	-40°C to 85°C
23C463F050ED1H1		Genteq	Special	46000		50	2.5	Round	3.125	Electrolytic	1000	-45°C to 95°C
97F5121		Genteq	Special	15		440	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
25L752BX	BX	Genteq	Special	25	4	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6931RC	RC	Genteq	Standard	20		580	1.75	Oval	4.75	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23M322F400FF1H1		Genteq	Special	3200		400	3	Round	4.125	Electrolytic	2000	-40°C to 85°C
23H641F400BH1H1		Genteq	Special	640		400	1.375	Round	5.125	Electrolytic	2000	-40°C to 85°C
97F6925BX	BX	Genteq	Special	48		300	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6869		Genteq	Standard	42		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9826		Genteq	Standard	25	7.5	370	2	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6623		Genteq	Standard	24		400	2	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H382F200ED1H1		Genteq	Special	3800		200	2.5	Round	3.125	Electrolytic	2000	-40°C to 85°C
97F8054S	S	Genteq	Stock	3		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C

27L20BX	BX	Genteq	Standard	30	5	440	2.5	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
23H432F250EF1H1		Genteq	Special	4300		250	2.5	Round	4.125	Electrolytic	2000	-40°C to 85°C
97F9009BX	BX	Genteq	Standard	50		370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB400E000C370DA		PROLINE	Standard	40		370	1.75	Oval	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23B701F250DB1H1		Genteq	Special	700		250	2	Round	2.125	Electrolytic	3000	-40°C to 85°C
23A473F080EF1H1		Genteq	Special	47000		80	2.5	Round	4.125	Electrolytic	1000	-40°C to 85°C
27L990BX	BX	Genteq	Special	35		240	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L6017BX	BX	Genteq	Special	10		660	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6920		Genteq	Standard	16		540	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F9895BX	BX	Genteq	Standard	45	5	370	2	Round	4.75	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6855RC	RC	Genteq	Standard	22.5		280	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F5304		Genteq	Special	15		440	1.75	Oval	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F8072BX	BX	Genteq	Standard	65		370	2.5	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F6543		Genteq	Special	28		280	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6537BX	BX	Genteq	Standard	24		330	1.75	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23F192F250ED1H1		Genteq	Special	1900		250	2.5	Round	3.125	Electrolytic	1000	-55°C to 105°C
23B192F250DF1H1		Genteq	Special	1900		250	2	Round	4.125	Electrolytic	3000	-40°C to 85°C
97F8055S	S	Genteq	Stock	4		370	1.25	Oval	2.12	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9983		Genteq	Standard	30	10	440	2	Round	3.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
97F9606S	S	Genteq	Stock	25		370	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
27L1003		Genteq	Standard	20		440	1.75	Round	2.88	Oil-Filled (UL Approved)	60000	-40°C to 70°C
PB350E000P370DA		PROLINE	Standard	35		370	1.75	Round	3.88	Oil-Filled (UL Approved)	10000	-40°C to 70°C
23M262F250CF1H1		Genteq	Special	2600		250	1.75	Round	4.125	Electrolytic	2000	-40°C to 85°C
23D213F020BF1H1		Genteq	Special	21000		20	1.375	Round	4.125	Electrolytic	1000	-55°C to 85°C
23B623F060FE1H1		Genteq	Special	62000		60	3	Round	3.625	Electrolytic	3000	-40°C to 85°C
97F6694BX	BX	Genteq	Special	20		480	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23H561F350BE1H1		Genteq	Special	560		350	1.375	Round	3.625	Electrolytic	2000	-40°C to 85°C
23J132F200DC1H1		Genteq	Special	1300		200	2	Round	2.625	Electrolytic	2000	-40°C to 105°C
97F6782		Genteq	Special	18.5		330	1.5	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
97F6757		Genteq	Standard	34		330	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C
23B183F075CF1H1		Genteq	Special	18000		75	1.75	Round	4.125	Electrolytic	3000	-40°C to 85°C
23J122F250CD1H1		Genteq	Special	1200		250	1.75	Round	3.125	Electrolytic	2000	-40°C to 105°C
97F6655BX	BX	Genteq	Standard	50		260	1.75	Oval	3.88	Oil-Filled (UL Approved)	60000	-40°C to 90°C