



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE .500
- 2 FOR USE WITH THE 206-375 TOOL. FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO THE STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SPECIALIST.
- 3 SHIP WITH: STOP 126747, DEFLECTOR 126748-1 AND (2) .030 SHIMS 128290 REFERENCE PB563 FOR PROPER USE.
- 4 128624 ASSEMBLY CONSISTS OF 128514 COLLET AND 128488 DRAWBAR.
- 5 128336-08 ASSEMBLY CONSISTS OF 127078 ANVIL HOLDER AND 127207-06 ANVIL INSERT

REV	DESCRIPTION	DET	DATE
D	REWROTE NOTES; ADDED .453 CENTER TO EDGE DIMENSION		11/24/09
E	128514 WAS 128624. ADDED 128488	JJC	08/03/12

128488	1	DRAWBAR	9
126748-1	1	UNITIZED DEFLECTOR	8
128514	1	COLLET	7
126745	1	GUARD	6
120095	1	DEFLECTOR	5
122912	1	BARBED RETAINER	4
128075	1	UNITIZED CHUCK JAW	3
126746	1	TOP GUARD	2
128336-08	1	ANVIL ASSEMBLY	1
PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH			
ITAR:		HUCK INTERNATIONAL, INC., I.S.D. 1 CORPORATE DR, P.O. BOX 2270 KINGSTON, NEW YORK 12401	
ECCN: EAR99		NOSE ASSEMBLY -08 UAB BR LONG	
SCH B#: 8467.99.0190		DET: MJK	DATE: 11/10/06
HTS: 8467.99.0190		CK:	SCALE: 2:1
B		99-3766-1	