

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0355650300](#)
Status: **Active**
Description: 2.29mm (0.090") Housing

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-35565-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
Series [35565](#)
Application Power
Product Name N/A

Physical

Breakaway No
Circuits (maximum) 3
Color - Resin Natural
Flammability 94HB
Gender Female
Glow-Wire Compliant No
Keying to Mating Part None
Lock to Mating Part None
Material - Resin Polyester Alloy
Number of Rows 2
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 4.20mm (.165")
Polarized to Mating Part No
Ports 1
Stackable No
Temperature Range - Operating -40°C to +120°C

Material Info

Reference - Drawing Numbers

Product Specification PS-35565-001
Sales Drawing SD-35565-001

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[35565Series](#)

Use With
[35454](#) MagKrimp™ Pin Cluster Block
Connector Terminal

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

35565-0300