



REV. DE



PT-01--24-01--22



SEE NOTE 15

PACKAGING VIEW LEAD STYLE SD -22

TABLE 2: SOCKET SPECIFICATION

LEAD STYLE	SERIES					
	-1	F _I G	SL	SDL	'B'	PIN LENGTH
	SS HSS SD					NO OF FINGER CLIPS
-1A	SC-1W1-XX-2 (SL & SDL N/R)	1	N/A	.038 [.97]	.553 [14.05]	4
-1B	SC-1W1-XX-1 (SL & SDL N/R)	1	N/A	.038 [.97]	.703 [17.86]	4
-1C	SC-1W1-XX-3 (SL & SDL N/R)	1	N/A	.038 [.97]	.453 [11.51]	4
-2	SC-1P1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.300 [7.62]	4
-3	SC-1S1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.203 [5.16]	4
-5	SC-2P1-XX (SS & HSS ONLY)	3	N/A	.038 [.97]	.703 [17.86]	4
-5A	SC-2P1-XX (SL & SDL N/R)	1	N/A	N/A	.703 [17.86]	4
-7	SC-1P3-XX (SL & SDL N/R)	1	N/A	N/A	.600 [15.24]	4
-8	SC-2P3-XX (SL & SDL N/R)	1	N/A	N/A	.542 [13.77]	4
-10	N/A	2	SC-3P1-XX	.038 [.97]	.230 [5.84]	4
-11	N/A	2	SC-4P1-XX	.028 [.71]	.240 [6.10]	4
-12	N/A	2	SC-5P1-XX	.028 [.71]	.190 [4.83]	4
-13	SC-2P7-XX (SS ONLY)	2	N/A	.039 [.99]	.310 [7.87]	4
-14	SC-1M1-XX (N/A)	1	N/A	N/A	.205 [5.21]	4
-15	SC-1M2-XX (N/A)	1	N/A	.028 [.71]	.167 [4.24]	4
-17	SC-7P1-XX (N/A)	1	N/A	N/A	.443 [11.25]	4
-18	SC-6P1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.353 [8.97]	4
-19	N/A	2	SC-8P1-XX	.016 [.41]	.165 [4.19]	4
-20	SC-9P1-XX (N/A)	2	N/A	.028 [.71]	.190 [4.83]	4
-21A	EZ-1W1-XX-2 (SL & SDL N/R)	1	N/A	N/A	.553 [14.05]	6
-21B	EZ-1W1-XX-1 (SL & SDL N/R)	1	N/A	N/A	.703 [17.86]	6
-21C	EZ-1W1-XX-3 (SL & SDL N/R)	1	N/A	N/A	.453 [11.51]	6
-22	EZ-1P1-XX (SL & SDL N/R)	1	N/A	.038 [.96]	.300 [7.62]	6
-23	EZ-1S1-XX (SL & SDL N/R)	1	N/A	N/A	.203 [5.16]	6
-28	EZ-2P3-XX (SL & SDL N/R)	1	N/A	N/A	.542 [13.77]	6
-29	EZ-2P2-XX (SL & SDL N/R)	1	N/A	N/A	.703 [17.86]	6
-30	EZ-3P1-XX (SL & SDL ONLY)	2	N/A	.038 [.97]	.230 [5.84]	6
-31	EZ-4P1-XX (SL & SDL ONLY)	2	N/A	.028 [.71]	.240 [6.10]	6
-32	EZ-5P1-XX (SL & SDL ONLY)	2	N/A	.028 [.71]	.190 [4.83]	6
-34	EZ-1M1-XX (N/A)	1	N/A	N/A	.205 [5.21]	6
-37	EZ-7P1-XX (N/A)	1	N/A	N/A	.443 [11.25]	6
-38	EZ-6P1-XX (SL & SDL N/R)	1	N/A	.038 [.97]	.353 [8.97]	6
-39	EZ-8P1-XX (SL & SDL ONLY)	2	N/A	.016 [.41]	.165 [4.19]	6
-40	EZ-9P1-XX (N/A)	2	N/A	.028 [.71]	.190 [4.83]	6
-41	SC-6P1-XX (N/A)	9	N/A	.005 [.13]	.353 [8.97]	4

SEE NOTE 13
SEE NOTE 14NOT AVAILABLE
IN -TT PLATING

SEE NOTE 13 & 14







DELETED
FIGURE 7FIGURE 8
OPTION -N
(FOR -SD STYLE, SEE NOTE 9 SHT.1)
(FOR HSS AND SS STYLES, SEE NOTES 3 & 4)
'B' DIMENSION FOR OPTION -N = NON FLUSHFIGURE 1
(FOR -N OPTION, SEE NOTE 9 SHT.1)FIGURE 2
(SEE NOTE 9 SHT.1)

FIGURE 3

OPTION -L: REPLACE BOTH END
POS. (BOTH ROWS) AS SHOWN
FIGURE 4
(SEE NOTE 9 SHT.1)

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSMITTED IN
ANY FORM OR BY ANY MEANS, ELECTRONIC
OR MECHANICAL, INCLUDING PHOTOCOPYING,
RECORDING, OR BY ANY INFORMATION
SYSTEMS WITHOUT THE WRITTEN
CONSENT OF SAMTEC INC.

MFG/ASST
XSX-1XX-XX-XX-X-X-MKT-SHT2

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47151-1147
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
MARK CHILTON 11-28-88XSX-1XX-XX-XX-X-X
SHEET 2 OF 2

DIMENSIONS ARE IN INCHES UNLESS OTHERWISE NOTED

TOLERANCES ARE:

ONE PLACE DECIMALS ±.1[2.5] THREE PLACE DECIMALS ±.005 [.13]
TWO PLACE DECIMALS ±.01[.25] FOUR PLACE DECIMALS ±.002[.05]

ANGLES
± 2°

TITLE:

ASSEMBLY
SOCKET STRIP

DWG NO:

XSX-1XX-XX-XX-X-X
SHEET 2 OF 2