




FCIconnect.com

Copyright FCI

PRODUCT NO.
SEE TABLE



NOTES:

1. MADE IN ACCORDANCE WITH PRODUCT SPECIFICATION BUS-12-001 AND PURCHASE SPECIFICATION BUS-10-001.
2. COLOR GRAY WITH RED TRACER ON EDGE OF FIRST POSITION.
3. UL-LISTED STYLE 2651, CSA CERTIFIED. (LATEST REVISION)

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		QUICKIE
ltr	ecn	no	dr	date	tolerances unless otherwise specified	 INCH/MM	title
F	-	JWB	11/7/90		angles		#28 AWG STRANDED DOUBLE SCALLOPE
G	V22247	MSC	6/5/92		linear		PVC ROUND CONDUCTOR CABLE
H	V82042	RGD	11/2/98	0'±2'			
J	M06-0282	MHT	7/26/06	dr	J.W.BLAIR	11/7/90	scale 1:1
				enr	M.SMYK	11/7/90	
				chr	M.SMYK	11/7/90	
				appd	M.SMYK	11/7/90	
sheet	revision	J	J				dwg no
index	sheet	1	2				76825
							sheet 1 of 2 size
							A3
							type
							Product Customer Drawing

form: A3

PRODUCT NO.
76825-XXX

76825-XXX

NO. OF CONDUCTORS
(MIN. 6, MAX 64)
LENGTH

TOLERANCE FOR DIMS		
NO. OF CONDUCTORS	DIM. A±	DIM. B±
9 THRU 15	.007/.18	.010/.25
16 THRU 37	.009/.23	.015/.38
38 THRU 64	.011/.28	.015/.38

X	MIN. LENGTH FT/M
0	100/30.48
1	100/30.48
3	300/91.44
4	300/91.44

mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified					title			
J					angles	linear	.XX±.01/.3	INCH/MM		#28 AWG STRANDED DOUBLE SCALLOPE			
					0'±2'		.XXX±.005/.13	scale 1:1		PVC ROUND CONDUCTOR CANBLE			
					dr	J.W.BLAIR	11/7/90			dwg no		sheet 2 of 2 size	
				enr	M.SMYK	11/7/90	76825			A3			
				chr	M.SMYK	11/7/90							
				appd	M.SMYK	11/7/90							
sheet index		revision sheet											

form: A3