


**PAN-FLEX™
.050" Flat Cable**



***CR = 100ft Rolls**
THR = 300ft Rolls
 (Available on 10, 14, 20, 26,
 34 and 50 circuit sizes)

Conductors	Part Numbers	Per Reel
	Only 1st Conductor is Color-marked	
6	050F28V6 CR*	(100 FT)
10	050F28V10 CR*	
14	050F28V14 CR*	
16	050F28V16 CR*	
20	050F28V20 CR*	
26	050F28V26 CR*	
32	050F28V32 CR*	
34	050F28V34 CR*	
40	050F28V40 CR*	
50	050F28V50 CR*	
60	050F28V60 CR*	
64	050F28V64 CR*	

Conductor	CU Tinned
Insulation	PVC Gray
Conductor Resistance	$\leq 230 \Omega/\text{km}$
Insulation Resistance	$\geq 90 \times 10^6 \Omega/\text{km}$
Capacitance	56 pF/m
Voltage Rating	300 V ^{eff}
Temperature Rating	-20 °C/ + 105 °C