




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
V		REV PER ECO 17-000132	5-5-17	CT	DM

1. CONTACTS INCLUDED IN ASSEMBLY.
- △ MATL: STEEL, PER ASTM-A-109.
 - △ FINISH: CADMIUM PER QQ-P-416.
 - △ MATL: BRASS PER ASTM-B-36.
 - △ FINISH: PLATED ZINC .00020 MIN THK PER ASTM-B-633. YELLOW CHROMATE FINISH.
 - △ CONTACT
 - BODY MAT'L: BERYLLIUM COPPER PER ASTM-B-197.
 - BODY FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER NICKEL, .000050 MIN THK PER QQ-N-290.
 - HOOD MAT'L: STAINLESS STEEL PER ASTM-A-240.
 - HOOD FINISH: PASSIVATED PER QQ-P-35
 - △ FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER FLASH
 - △ FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.
 - △ CONTACT
 - BODY MAT'L: BERYLLIUM COPPER PER ASTM-B-197.
 - BODY FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.
 - HOOD MAT'L: COPPER ALLOY PER QQ-B-613.
 - FINISH: PLATED GOLD, .000050 MIN THK PER MIL-G-45204 OVER COPPER, .000100 MIN THK PER MIL-C-14550.

△ △	△ △	△	R10002677-0109	211013-6
△ △	△ △	△	2A091-004W-001	211013-5
△ △	△ △	△	-	211013-4
△ △	△ △	△	(1J02-109)	211013-2
△ △	△ △	△	-	211013-1
EYELET	SHELLS	CONTACT	CUSTOMER P/N	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11-3-98	TE Connectivity	
DIMENSIONS: INCHES		CHK J.NORTON 11-17-98		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J.NORTON 11-17-98	NAME CONNECTOR SAVER,AMPLIMITE 62 POSN.,SIZE 4,SERIES 90	
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 [0.13] 4 PLC ± - ANGLES ± -	PRODUCT SPEC APPLICATION SPEC	RESTRICTED TO	
MATERIAL	-	WEIGHT 0	SIZE A1	CAGE CODE 00779
CUSTOMER DRAWING		DRAWING NO 211013	SCALE 4:1	
		SHEET 1	OF 1	
		REV V		