


SPECIFICATION



ORDER NUMBER 279328

BATTERY TYPE 2/V60H

SYSTEM RECHARGEABLE NIMH

NOMINAL VOLTAGE 2.4 V

TYPICAL CAPACITY 0.2CA 70mAh

TYPICAL CAPACITY 1.0CA 40mAh

WEIGHT APPROX. 8 g

CHARGE CURRENT/TIME 6mA/14-16h

ACCELERATED CHARGE RATE/TIME 30mA/3h 20 C AFTER FULL DISCHARGE

TRICKLE CHARGE RECOMMENDED 0.03CA (1.8mA)

MAX. CONT. OVERCHARGE 6.0 mAh AT 20 C

SERVICE LIFE CYCLIC 1000 CYCLES (IEC 509)

SERVICE LIFE TRICKLE CHARGE CONT UP TO 6 YEARS AT 20 C
UP TO 3 YEARS AT 45 C

<u>TEMPERATURE RANGE</u>	<u>RECOMMENDED</u>	<u>PERMISSABLE</u>
CHARGE	+10 TO +35 C	0 TO +60 C
DISCHARGE	0 TO +45 C	-20 TO +65 C
STORAGE	-40 TO +45 C	-40 TO +65 C