




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
IS	-		51	First issue	03MAY2010	MS
			52	Sampling	12MAY2010	MS
			53	Second sampling	11JUN2010	MS
			A	Go to production	04NOV2010	MS




SECTION A-A

RECOMMENDED
PANEL CUT OUT



- 1 General tolerances acc.to ISO 2768-mH
- 2 Knurl according to DIN 82 RAA 0.5
- 3 Coupling torque 5N max.
- 4) Bulk-packagin

619445-1	2	CROWN	BeCu	min. 0.2 µm Au over Ni
	1	Outer Con.	Brass	min. 5 µm Ag
TE PN	Item	Description	Material	Plating



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN M.Scheggia CHK M.Grazioli APVD -	03MAY2010 03MAY2010 -	Tyco Electronics Lugano - Switzerland	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME STRAIGHT SOCKET PIN SIZE 6mm 125 A	
MATERIAL -		FINISH -		RESTRICTED TO -	
-		-		SCALE 5:1	
-		-		SHEET 1 OF 1	
-		-		REV A	