

Metric & Imperial Spacers

Threaded Female Spacers

- Available in a variety of standard body lengths.
- Brass spacers: base material is free-machining brass, with nickel plating.
- Plastic material: Nylon 66 UL94V-2.



THREADED SPACERS



R25-100
Brass, Hexagonal
M2.5, 5.0mm A/F



R30-100
Brass, Hexagonal
M3, 5.0mm A/F



R30-101
Brass, Hexagonal
M3, 5.5mm A/F



R30-161
Plastic, Hexagonal
M3, 5.5mm A/F



R30-500
Brass, Circular
M3, Ø4.76mm O/D



R40-100
Brass, Hexagonal
M4, 7.0mm A/F





R44-100
Brass, Hexagonal
4-40 UNC, 5.0mm A/F

HOW TO ORDER

RXX - XXX XX XX

SERIES CODE
See pictures above

LENGTH (mm)	
04 to 16, 18, 20, 25	Other
06 to 16, 18, 20, 25	R30-161, R40-100
06, 09, 10, 12, 13, 15, 16, 19, 22, 23, 25, 30, 35, 45, 50	R44-100

MATERIAL/FINISH	
00	Plastic 
02	Brass/Nickel 

All dimensions in mm.