

Signal tower Ø 54 mm
BR 50



IP 54

Protection system

IP 65

Option

UL

+ 50 °C

- 25 °C

Operating temperature

- modular design with sturdy housing for all indoor and outdoor applications in tough conditions
- wherever machine status needs to be displayed and warning signals given
- high protection system IP 54 (optionally IP 65)
- flexible building kit system guarantees easy handling
- up to 5 modules with 6 lens colours can be combined as desired by simply plugging together, even retrospectively
- mechanical and electronic components are uncoupled, resulting in a more stable structure that is less sensitive to vibration
- many different variations are possible, can be fixed by means of tubular stand, tube or direct mounting
- made of environmentally-friendly materials as per DIN ISO 14000
- monitored module for greater safety; the light bulb has two separate LED strands. If one strand fails, the alarm contact is activated and the second strand continues to light




Technical data		BR 50 (standard modules)						
Modules		continuous light		blinking light 1.5 Hz		flashing light	sounder	
Colours		clear, yellow, amber, red, green, blue						
Segment stages (total)		max. 5 (order and colour can be selected individually)						
Angle of radiation		360°						
Light source		bulb A15d ¹	LED ¹	bulb A15d ¹	LED ¹			
Rated power	per stage	7 W	depending on voltage	7 W	depending on voltage			
	per stage if 5 stages	5 W		5 W				
Flash energy	230 V / 115 V AC					0.6 Joules		
	24 V AC/DC					24 V: 1 Joules		
Flash frequency						approx. 1 Hz		
Sound pressure level								85 dB (A)
Tones								7
Rated current consumption (50/60 Hz)	230 V AC	35 mA	15 mA	35 mA	–	10.5 mA	15 mA	
	115 V AC	64 mA	15 mA	–	–	20 mA	15 mA	
	operating range	- 15% ... + 10%				- 10% ... + 15%	- 15% ... + 10%	
Rated current consumption	24 V	DC: 300 mA	DC: 30 mA	DC: 250 mA	DC: 30 mA	AC/DC: 100 mA	12 mA	
	operating range	- 15% ... + 20%		10 V – 30 V		AC: 10 V – 27 V DC: 10 V – 35 V	- 15% ... + 20%	
Operating temperature	with bulb	- 25 °C ... + 50 °C		- 25 °C ... + 50 °C			- 10 °C ... + 45 °C	
	with LED	- 30 °C ... + 60 °C						
Relative humidity		90%						
Protection system according to EN 60529		IP 54					IP 43	
Duty cycle		100%						
Service life of light sources		approx. 1,500 h	approx. 50,000 h	approx. 1,500 h	approx. 50,000 h	light emission still 70% after 8,000,000 flashes		
Material	base	acrylonitrile butadiene styrene (ABS)						
	lens	polycarbonate (PC)						
	tube	stainless steel						
Tube thread		30 mm, M16 x 1.5						
Mounting		vertical or horizontal						
Mounting information		the sounder module or the monitored module is always the uppermost module; a maximum of 1 monitored module may be used per signal tower						
Weight	module	80 g		90 g		90 g	230 g	
	base	mounting stand: approx. 220 g / tube mounting: approx. 200 g / direct mounting: approx. 180 g						

¹ Please order light source separately


Technical data	monitored continuous light module	BR 50 AS-i Bus slave	
Modules		AS-i	AS-i-AB
Module types	monitored continuous light	LED module, sounder module, continuous light module, blinking light module	
Colours	yellow, red		
Segment stages (total)	max. 3	max. 4	max. 3
Angle of radiation	360°		
Light source	2 x 8 LED (not exchangeable)		
AS-i profile		S-8.F.E	S-8.A.E
AS-i specification		AS-i 3. / EN 50295	
Programming		DC-Jack, Ø 1.3 mm	
max. slave/master		31	62
Alarm output	max. 230 V / 80 mA, R _{ONmax} = 35 Ω (closed at error-free operation)		
Rated voltage	24 V DC		
Rated current consumption	approx. 35 mA	< 0.25 A	
Operating range	- 15% ... + 20%	26.5 V – 31.6 V	
Operating temperature	- 30 °C ... + 60 °C		
Relative humidity	90%		
Protection system according to EN 60529	IP 54		
Duty cycle	100%		
LService life of light sources	50,000 hrs @ 24 °C, 40% R.H.		
Material	base	acrylonitrile butadiene styrene (ABS)	
	lens	polycarbonate (PC)	
Montage	vertical or horizontal		
Mounting information	the monitored module is always the uppermost module; a maximum of 1 monitored module may be used per signal tower	the AS-i / AS-i-AB module is always used as the lowest module	
Weight	90 g		

Connection configuration / connection diagrams for monitored module



Base module + 1 st stage monitored		Base module + 1 st stage not monitored, 2 nd stage monitored		Base module + 1 st /2 nd stage not monitored, 3 rd stage monitored	
-/N	supply voltage (-), common connection for all stages	-/N	supply voltage (-), common connection for all stages	-/N	supply voltage (-), common connection for all stages
1+/L	supply voltage (+), activation of monitored module	1+/L	supply voltage (+), activation of 1 st stage	1+/L	supply voltage (+), activation of 1 st stage
2+/L	potential-free alarm output contact 1	2+/L	supply voltage (+), activation of 2 nd stage (monitored)	2+/L	supply voltage (+), activation of 2 nd stage
3+/L	potential-free alarm output contact 2	3+/L	potential-free alarm output contact 1	3+/L	supply voltage (+), activation of 3 rd stage (monitored)
4+/L	n.c.	4+/L	potential-free alarm output contact 2	4+/L	potential-free alarm output contact 1
5+/L	n.c.	5+/L	n.c.	5+/L	potential-free alarm output contact 2



Dimensions



	L1 tube mounting	L1 mounting stand
Tube length 100	78	88
Tube length 250	228	238
Tube length 400	378	388
	L2	
1-stage	107	
2-stage	170	
3-stage	233	
4-stage	296	
5-stage	359	



Bayonet connection allows fast, simple mounting



Configuration alternatives



Ordering details				
Article numbers		BR 50 modules		
Version	Rated voltage	230 V AC	115 V AC	24 V DC
Basis- und Abschlussmodul	BR50-BC	282 50 01 0 000		
Continuous light module	clear BR50-CL-CL	282 50 04 0 010		
	yellow BR50-CL-YE	282 50 04 0 030		
	amber BR50-CL-AM	282 50 04 0 040		
	red BR50-CL-RE	282 50 04 0 050		
	green BR50-CL-GR	282 50 04 0 060		
	blue BR50-CL-BL	282 50 04 0 070		
Blinking light module	clear BR50-BL-CL	282 50 05 1 010	282 50 05 1 610	282 50 05 8 010
	yellow BR50-BL-YE	282 50 05 1 030	282 50 05 1 630	282 50 05 8 030
	amber BR50-BL-AM	282 50 05 1 040	282 50 05 1 640	282 50 05 8 040
	red BR50-BL-RE	282 50 05 1 050	282 50 05 1 650	282 50 05 8 050
	green BR50-BL-GR	282 50 05 1 060	282 50 05 1 660	282 50 05 8 060
	blue BR50-BL-BL	282 50 05 1 070	282 50 05 1 670	282 50 05 8 070
Flashing light module	clear BR50-FL-CL	282 50 07 1 010	282 50 07 1 610	282 50 07 8 010
	yellow BR50-FL-YE	282 50 07 1 030	282 50 07 1 630	282 50 07 8 030
	amber BR50-FL-AM	282 50 07 1 040	282 50 07 1 640	282 50 07 8 040
	red BR50-FL-RE	282 50 07 1 050	282 50 07 1 650	282 50 07 8 050
	green BR50-FL-GR	282 50 07 1 060	282 50 07 1 660	282 50 07 8 060
	blue BR50-FL-BL	282 50 07 1 070	282 50 07 1 670	282 50 07 8 070
LED module, monitored	yellow BR50-LED-M-YE	–	–	282 50 06 8 030
	red BR50-LED-M-RE	–	–	282 50 06 8 050
Sounder module	BR50-SM	282 50 08 1 000	282 50 08 1 600	282 50 08 8 000
AS-i module	BR50-AS-i	282 50 14 8 300		
AS-i-AB module	BR50-AS-i-AB	282 50 17 8 300		
Information module	BR50-IM	282 50 27 0 000		
Tubular stand with plinth	100 mm BR50-S100	282 50 15 0 010		
	250 mm BR50-S250	282 50 15 0 020		
	400 mm BR50-S400	282 50 15 0 040		
Tube with thread and bracket (excl. seal and cable)	100 mm BR50-T100	282 50 16 0 010		
	250 mm BR50-T250	282 50 16 0 020		
	400 mm BR50-T400	282 50 16 0 040		

Light bulbs for constant light and blinking light modules must be ordered separately

Options / accessories



Article number:
282 50 25 0 000



for mounting stand
Article number:
282 50 20 0 000



for direct mounting
Article number:
282 50 21 0 000



Article number:
282 50 22 0 000
282 50 23 0 000



Light source



See pages 190/191 for further information