

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION					
© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION.				ALL INTERNATIONAL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
					D	REVISED PER ECR-09-027352	18FEB10	JR	TM

1

43.89 MAX
[1.728]

AMP 12-10*

18.29
[.720]

13.16±0.20
[.518±.008]
FOR 1/2 STUD

INSULATION

BODY

AMP

WIRE RANGE

12-10 AWG
STRANDED

1

STAMP AMP 12-10* APPROX AS SHOWN

2

WIRE INSULATION DIA 6.10 [.240] MAX

3

TONGUE MATERIAL THK 1.02±0.05 [.040±.002]

4

SUPERSEDED BY 8-55861-3

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 125° C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S S GOULDEN 6/93		Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608								
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 600V MAX (BUILDING WIRING) 1000V MAX (FIXTURES & SIGNS)		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:					CHK R HERSEY 6/93				
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 1.04-2.62² [2050-5180] STRANDED				0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -					APVD B BARE 6/93				
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL BODY: ETP COPPER INSULATION: POLYOLEFIN COLOR: YELLOW		FINISH EDP TIN PLATED					PRODUCT SPEC -				
								APPLICATION SPEC 408-4022		NAME TERMINAL, RING TONGUE, SEALABLE HEAT SHRINKABLE							
								WEIGHT -		SIZE A3		CAGE CODE 00779		DRAWING NO C-55861		RESTRICTED TO -	
								CUSTOMER DRAWING		SCALE NTS		SHEET 1 OF 1		REV D			