





JKL LAMP NUMBER	VOLTS RATED	WATTS	INITIAL MSCP	INITIAL LUMENS	AVERAGE LIFE HRS.	FILAMENT TYPE
6S6-12V	12	6	3.58	45.0	1,500	C-2V
6S6-30V	30	6	3.98	50.0	1,500	C-2V
6S6-120V	120	6	3.18	40.0	1,500	C-7A
6S6-145V	145	6	3.18	40.0	1,500	C-7A
6S6-155V	155	6	3.18	40.0	1,500	C-7A
10S6-230V	230	10	5.97	75.0	1,500	C-1
10S6-250V	250	10	5.97	75.0	1,500	C-1

METRIC



THIRD ANGLE
PROJECTION

DIMENSIONS ARE
IN MILLIMETERS

TOLERANCE UNLESS
OTHERWISE SPECIFIED

1 PL +/- 0.2

2 PL +/- 0.20

ANGLE +/- 0

DRAWN BY

L. WENGSTROM

APPVD BY DATE

Q.C. 3/1/01

JKL

COMPONENTS CORPORATION

TITLE

S-6 MINIATURE CANDELABRA
SCREW BASE LAMP

SIZE

A

FSCM NO.

55335

DRAWING

NO.

SCREW BASE CANDELABRA S-6

SCALE

NONE

RELEASED

DATE

3/1/01

REVISION

DATE

REV.

NO.

SHEET

1 OF 1

- CAD DRAWING -

MANUAL REVISIONS NOT PERMITTED

REV. NO.	DESCRIPTION/ECO NUMBER	APPVD DATE
RELEASED		3/1/01