

Distributed by:



**[www.Jameco.com](http://www.Jameco.com) ♦ 1-800-831-4242**

The content and copyrights of the attached  
material are the property of its owner.

# DC FAN

JAMICON®

60X60X25 (A) mm

- **Frame** : Plastic Material UL 94V-0
- **Impeller** : Plastic Material UL 94V-0
- **Speed Range** :  $\pm 10\%$



## SPECIFICATIONS

| Model      | Rated Voltage (V) | Operating Voltage (V) | Air Flow (CFM) | Static Pressure (mmH <sub>2</sub> O) | Speed (R.P.M) | Rated Current (Amp) | Input Power (Watt) | Noise (dBA) | Weight (g) |
|------------|-------------------|-----------------------|----------------|--------------------------------------|---------------|---------------------|--------------------|-------------|------------|
| JF0625x1TR | 12                | 10.2 ~ 13.8           | 29.69          | 10.73                                | 6000          | 0.41                | 4.92               | 42.5        | 65.0       |
| JF0625x1UR |                   |                       | 26.96          | 9.06                                 | 5500          | 0.35                | 4.20               | 39.2        |            |
| JF0625x1SR |                   |                       | 24.27          | 7.42                                 | 5000          | 0.29                | 3.48               | 35.7        |            |
| JF0625x1H  |                   |                       | 21.44          | 6.03                                 | 4500          | 0.23                | 2.76               | 34.1        |            |
| JF0625x1M  |                   |                       | 19.00          | 4.69                                 | 4000          | 0.20                | 2.40               | 31.6        |            |
| JF0625x1L  |                   |                       | 16.76          | 3.68                                 | 3500          | 0.17                | 2.04               | 27.3        |            |
| JF0625x1E  |                   |                       | 14.24          | 2.74                                 | 3000          | 0.13                | 1.56               | 21.8        |            |
| JF0625x1V  |                   |                       | 11.72          | 1.93                                 | 2500          | 0.08                | 0.96               | 20.2        |            |
| JF0625x2TR | 24                | 20.4 ~ 27.6           | 29.69          | 10.73                                | 6000          | 0.25                | 6.00               | 42.5        |            |
| JF0625x2UR |                   |                       | 26.96          | 9.06                                 | 5500          | 0.22                | 5.28               | 39.2        |            |
| JF0625x2SR |                   |                       | 24.27          | 7.42                                 | 5000          | 0.19                | 4.56               | 35.7        |            |
| JF0625x2H  |                   |                       | 21.44          | 6.03                                 | 4500          | 0.17                | 4.08               | 34.1        |            |
| JF0625x2M  |                   |                       | 19.00          | 4.69                                 | 4000          | 0.13                | 3.12               | 31.6        |            |
| JF0625x2L  |                   |                       | 16.76          | 3.68                                 | 3500          | 0.11                | 2.64               | 27.3        |            |
| JF0625x2E  |                   |                       | 14.24          | 2.74                                 | 3000          | 0.09                | 2.16               | 21.8        |            |
| JF0625x2V  |                   |                       | 11.72          | 1.93                                 | 2500          | 0.07                | 1.68               | 20.2        |            |
| JF0625x4T  | 48                | 40.8 ~ 55.2           | 29.69          | 10.73                                | 6000          | 0.16                | 7.68               | 42.5        |            |
| JF0625x4U  |                   |                       | 26.96          | 9.06                                 | 5500          | 0.14                | 6.72               | 39.2        |            |
| JF0625x4S  |                   |                       | 24.27          | 7.42                                 | 5000          | 0.12                | 5.76               | 35.7        |            |
| JF0625x4H  |                   |                       | 21.44          | 6.03                                 | 4500          | 0.10                | 4.80               | 34.1        |            |
| JF0625x4M  |                   |                       | 19.00          | 4.69                                 | 4000          | 0.08                | 3.84               | 31.6        |            |
| JF0625x4L  |                   |                       | 16.76          | 3.68                                 | 3500          | 0.06                | 2.88               | 27.3        |            |
| JF0625x4E  |                   |                       | 14.24          | 2.74                                 | 3000          | 0.05                | 2.40               | 21.8        |            |

P.S.: The 7<sup>th</sup> character of the model codes could be "S", "C" or "B"; "S": Sleeve bearing, "C": Ball + Sleeve bearing, "B": Two ball bearing  
Specifications subject to change without notice

