

Overview

The 920 Series is a relampable midget flanged base lampholder. The mating lens cap accepts a T-1 3/4 midget flanged base incandescent lamp, held in the lens assembly by means of a friction fit which insures good contact and prevents the lamp from falling out when the lens is removed. A Littelite Lens Cap Assembly must be used with the holder to hold the lamp in proper relationship to the socket contact. Also available with RFI/EMI shielded lens to eliminate the possible transmission or reception of RF signals.

Approvals

UL Recognized and CSA Certified. For MIL Spec Lampholders, contact the factory.

Specification

Housing: Aluminum. Black anodized finish standard. Clear anodized or yellow iridescent chromate finish optional.

Internal Tooth Lockwasher & Hex Nut: Steel. Zinc-plated with yellow iridescent chromate finish.

Terminals: Brass. Tin-plated with elongated slot (3/64" x 3/32"). Tapered to accept a quick-connect receptacle.

Socket: Brass. Nickel-plated.


Lens: Heat resistant, high strength polycarbonate.

Lens Marking: Flat rotatable lenses may be stamped. Contact factory.

Lens Barrel: Brass. Nickel-plated.

Retainer: Aluminum. Black or clear anodized finish.

920 Series Maximum Rating: 1.12 Watts, 28 Volts.



ORDERING INFORMATION:					EXAMPLE: 9 2 0 4 0 1 X 31 0 RN								
					Black Anodized Finish			Stovepipe Lens		No Retainer		Red Non-Diffusing Lens	
Series Number	Lampholders				Lens Cap Assembly								
	Termination	Features	Finish	Resistor	Lens Style		Retainer	Lens Color					
920	4 Solder Cup	0 None	1 Black Anodized - Standard 2 Clear (Silver) Anodized 3 Yellow Iridescent Chromate	X None Required	31 ⁴ Stovepipe		0 ³ No Retainer	Nondiffusing					
					32 ^{1,4} Flat Rotatable			AN Amber					
					33 ⁴ Cylindrical			BN Blue					
					34 ⁵ Convex			CN Colorless					
					38 ⁶ Convex			GN Green					
					30 Stovepipe - RFI/EMI Shielded		1 Black Anodized Finish Standard	RN Red					
								WN White					
								YN Yellow					
								Translucent					
								AT Amber					
							2 Clear (Silver) Anodized Finish	BT Blue					
								GT Green					
								RT Red					
								WT White					
								YT Yellow					
							2 Clear (Silver) Anodized Finish	Diffusing					
								AD Amber					
								BD Blue					
								CD Colorless					
								GD Green					
							RD Red						
							YD Yellow						