

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301110023

Status:

Active

Overview:

Stringlights

Description:

Pro-Yellow Stringlight, 150W, 14/2 AWM with 2.43m Lead, 10 Sockets with Guards, Overall Length 30.48m (100.0')



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130111
NEMA Configuration	N/A
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Pro-Yellow
Type	String Lights
UPC	78678853637
Physical	
Cord Length - Primary	2.43m (8.0')
Cord Length - Secondary	0.61m (2.0')
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Polypropylene
Height	N/A
Length	30.48m (100.0')
Material - Guard	Polypropylene
Mounting Style	Stringer
Net Weight	4.105/kg
Packaging Type	Carton
Socket Construction	Assembled
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	14/2
Lamp Type	A21
Lamp Wattage - Maximum	150W
Lumens	1500
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	202SRL

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130111 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION