

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0026291111](#)
Status: **Obsolete**
Overview: [kk](#)
Description: 3.96mm (.156") Pitch KK® PC Board Connector, Bottom Entry, Nylon Connector, Gold (Au) Selective, 11 Circuits

Documents:
[Drawing \(PDF\)](#)

General

Product Family	PCB Receptacles
Series	3215
Application	Board-to-Board, Power
Overview	kk
Product Name	KK®

Physical

Circuits (Loaded)	11
Circuits (maximum)	11
Durability (mating cycles max)	25
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Number of Rows	1
Orientation	Bottom Entry
PC Tail Length	4.06mm (.160")
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	3.96mm (.156")
Pitch - Termination Interface	3.96mm (.156")
Polarized to Mating Part	No
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0°C to +75°C
Termination Interface: Style	Through Hole

Electrical


Current - Maximum per Contact	5A
Voltage - Maximum	250V

Material Info

Old Part Number	3215HR11G2B
-----------------	-------------

Reference - Drawing Numbers

Product Specification	PS-99020-0087
Sales Drawing	SDAE-3215-**N**-**



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[3215Series](#)