

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39517-2916

Status:


Active

Overview:

Eurostyle™ Terminal Blocks

Description:

3.81mm Pitch Eurostyle™ Vertical Plug, with Retention Screws and Reverse Imprinting, Rear Wire Entry, Gold (Au) Plated, 16 Circuits



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Specification PS-39500-001 \(PDF\)](#)

| General        |                                         |
|----------------|-----------------------------------------|
| Product Family | Terminal Blocks                         |
| Series         | 39517                                   |
| Application    | N/A                                     |
| Comments       | Rear Wire Entry with Reverse Imprinting |
| Component Type | Plug                                    |
| Overview       | Eurostyle™ Terminal Blocks              |
| Product Name   | ESE, Eurostyle™Pluggable                |
| Type           | Euro Block                              |
| UPC            | 822350454414                            |

| Physical                      |                                |
|-------------------------------|--------------------------------|
| Circuits (Loaded)             | 16                             |
| Entry Angle                   | Horizontal                     |
| Lock to Mating Part           | Yes                            |
| Number of Rows                | 1                              |
| Orientation                   | Vertical                       |
| Panel Mount                   | No                             |
| Pitch - Mating Interface      | 3.81mm                         |
| Pitch - Termination Interface | 3.81mm                         |
| Polarized to Mating Part      | Yes                            |
| Stackable                     | No                             |
| Temperature Range - Operating | -40°C to +105°C                |
| Wire Size AWG                 | 16, 18, 20, 22, 24, 26, 28, 30 |
| Wire Size mm²                 | 0.05 - 1.31                    |

| Electrical                    |      |
|-------------------------------|------|
| Current - Maximum per Contact | 8A   |
| Voltage - Maximum             | 300V |

Material Info

| Reference - Drawing Numbers |              |
|-----------------------------|--------------|
| Product Specification       | PS-39500-001 |
| Sales Drawing               | SD-39517-002 |

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

39517Series

Mates With

Most 3.81mm Pitch Industry Standard PCB Headers, 39515 Vertical PCB Header with Threaded Retention Inserts, 39516 Horizontal PCB Header with Threaded Retention Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[39517-2916](#)