

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [15268-0486](#)
Status: **Active**
Overview: [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Description: 1.25mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 40 Circuits, 0.152m Cable Length, 0.27mm Cable Thickness, Tin (Sn) Plating

Documents:
[Drawing \(PDF\)](#)
[Product Specification PS-15268-001 \(PDF\)](#)
[Packaging Specification PK-15268-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Cable
Series [15268](#)
Comments Contacts on opposite sides, Type D
Crimp Quality Equipment Yes
Overview [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)
Product Name Premo-Flex™ FFC Jumper
UPC 884982431447

Physical
Cable Length 0.152m
Circuits (Loaded) 40
Circuits (maximum) 40
Packaging Type Bag
Pitch - Termination Interface 1.25mm
Temperature Range - Operating -40°C to +105°C
Wire Size AWG N/A
Wire/Cable Type Flat Flex Cable

Electrical
Current - Maximum per Contact 1.4A
Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers
Packaging Specification PK-15268-001
Product Specification PS-15268-001
Sales Drawing SD-15268-001



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[15268Series](#)

Use With
Molex FFC – FPC connector.
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION