



Sample photo

Order symbol: PCM 175/125 T
Product nbr: 6016922
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074052261
El. number:
 Finland 3435220
 Denmark 8212027530
 Sweden 2535440

Including: Base with metric knock-outs and TPE gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and wing heads for cover screws.

Dimensions:			
mm:	180	180	125
inch:	7.1	7.1	4.9
Materials:			
Material:	PC		
Base colour:	RAL 7035		
Cover colour:	Smoked grey		
Cover screws material:	Polyamide		
Cover screws colour:	Black		
Gasket material:	TPE		
Temperatures:			
Short term:	-40 ... 120 °C		
Continuous:	-40 ... 80 °C		
Short term:	-40 ... 250 °F		
Continuous:	-40 ... 175 °F		
Accessories:			
MIV 175	Mounting plate		
MIN 15	DIN-15 Mounting rail		
MIV 15	DIN-35 Mounting rail		
FP A 175/180	Front plate		
HFP 180	Front plate hinge series		
Rating:			
Ingress Protection (EN 60529): IP 66/67			
Impact Resistance (EN 50102): IK 08			
Electrical insulation: Totally insulated			
Halogen free (DIN/VDE 0472, Part 815): Yes			
UV resistance: UL 508			
Flammability Rating (UL 746 C 5): UL 94 5V			
Glow Wire Test (IEC 695-2-1) °C: 960			
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13			
Certificates:			
Germanischer Lloyd (GL)			
Underwriters Laboratories			
Det Norske Veritas			
Fimko			
Europe EN 50298 1998			
UL Canada			
Gost R			

