



2.5mm Mono Phone Plug

171-3304

KOBI CONN

2.5mm Mono Phone Plug

171-3304



Dimensions: In.

(except where noted)

SPECIFICATIONS	
Type:	2.5mm Mono Phone
Temperature Rating:	70°C
Breakdown Voltage:	500VAC for 1 Minute
Insulation Resistance:	100MΩ @ 500VDC
Contact Resistance:	50mΩ max.
Life Time:	10,000 Cycles min.
Contacts, Terminal:	Nickel Plated Brass
Pin:	Nickel Plated Steel
Insulator:	Acrylonitrile Butadiene Styrene (ABS)
Cap:	Polypropylene

Date Last Revised: 4-18-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-300541

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[171-3304](#)