

THIS DRAWING IS UNPUBLISHED.



RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS						
J		-		P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
				0	作成	RELEASED	FJ00-0158-98	30 JAN 98	ES	7





NOTE,

- 1 APPLICABLE P.C.BOARD THICKNESS: 1.6mm
- 2 RECOMMENDED MOUNTING SCREW: 4mmDIA, 6mmLENGTH
TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE : 4kgcm MAX)
- 3 THE MATING PLUG HSG P/N ; 353112,1123632

注 :

- 1 適用プリント基板厚: 1.6mm
- 2 推奨取付ネジ: JIS B1115, B1122 タッピンネジ, ナベ2種
呼び径4, 長さ6mm (締付トルク 4kgcm以下)
- 3 嵌合相手型番 ; 353112, 1123632



推奨プリント基板取付け寸法 (公差 ±0.1)

(MOUNTING DIMENSIONS FOR P.C.BOARD: TOLERANCE ±0.1)

ピッチ公差は累積しないこと (NON ACCUMULATE PITCH TOLERANCE)

緑 (GREEN)	1123630-4
色 (COLOR)	型番 (P/N)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		OWN CHK E. Sasaki 30 JAN 98	AMP 日本エー・エム・ピー株式会社 Kawasaki, Japan	
DIMENSIONS: 単位 純 mm		APVD 2. H. Sasaki 30 JAN 98	NAME .04011 SRS MULTI-LOCK CONN. MK-II 48Pos. CAP ASSY	
TOLERANCES UNLESS OTHERWISE SPECIFIED		PRODUCT SPEC 108-5452	.04011 シリーズ マルチロック コネクタ MK-II	
一般公差 10% ±0.2 30% ±0.25 100% ±0.3 ANGLE ±0.3°		APPLICATION SPEC 取付適用規格	48極 キャップハウジング アッセンブリ	
MATERIAL HOUSING : PBT CONTACT : BRASS コンダクト : 黄銅		FINISH 仕上 PRE-TIN 錫めつき済	WEIGHT 16.8g	SIZE A2
		CUSTOMER DRAWING	CAGE CODE 00779	DRAWING NO C=1123630
			SCALE 2-1	SHEET 1
			OF 1	REV 0