

ADAPTERS, IN-SERIES

Type N , DC - 18 GHz, Precision

SPECIFICATIONS:

Models: 5103, 5104, 5105

RoHS
Compliant

Electrical:


Frequency Range _____ DC - 18.0 GHz
VSWR
DC - 4 GHz _____ 1.04:1 Max.
4 - 8 GHz _____ 1.07:1 Max.
8 - 18 GHz _____ 1.12:1 Max.
Impedance _____ 50 Ohms
Operating Temp Range _____ -65°C to +125°C

Mechanical:


Connectors _____ Passivated Stainless Steel
Mates with MIL-STD-348
Conductors _____ Gold Plated Beryllium Copper

AEROFLEX
A passion for performance.


Model Number: **5105**
Male/Female Connectors



Model Number: **5104**
Male/Male Connectors



Model Number: **5103**
Female/Female Connectors



Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

5105: REV D

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmet@aeroflex.com