


specifications

The wiring duct cutter shall smoothly cut slotted plastic wiring duct and duct cover leaving a square, clean edge. The tool shall cut precisely and evenly in a single stroke with minimal force eliminating uneven cuts or burrs. The adjustable stop with integrated measuring scale shall provide precision adjustment up to 39.4 inches (1000mm) to guarantee both wiring duct and cover are cut to exact lengths.



technical information

Material:	Steel
Weight:	44 lbs./20 kg
Color:	Black
Compatibility:	Cuts PANDUCT® Slotted Wiring Duct from .5" x .5" to 4" x 5" (12mm x 12mm to 100mm x 125mm); covers to 4" (100mm)

key features and benefits

Manual hand operation	No chips, dust, or noise when compared to power cutting tools
Precision cutting blade	No burrs or uneven cuts
Integrated measuring scale	Reduces waste due to inaccurate cuts
Adjustable cut-length stop	Accurate measurement and consistent cutting of lengths up to 39.4" (1000mm)
Safety cover	Protects operator from inadvertent contact with blade

applications

The PANDUCT® BDCT is a single stroke wiring duct cutter designed for use in panel shops to smoothly cut slotted plastic wiring duct and cover with minimal effort. The cutter's

powerful lever action cuts precisely and evenly leaving square, clean edges. This solution provides accurate cuts to eliminate time-consuming cutting by hand.

PANDUCT® Wiring Duct Cutting Tool

Bench mount cutting tool: BDCT

Wiring Duct Bases (smallest to largest size)

Type G	G.5X.5**6 to G4X5**6
Type F	F.5X.5**6 to F4X5**6
Type H	H1.5X2**6 to H4X4**6
Type MC	MC25X25**2 to MC100X100**2
Type NE	NE.5X.5WH6 to NE4X5WH6
Type NNC	NNC25X25**2 to NNC100X100**2
Type FL	FL12X12LG-A to FL50X50LG-A

Covers


For Type G, Type F	C.5**6 to C4**6
For Type H	HC1.5**6 to HC4**6
For Type NE	NC.5WH6 to NC4WH6
For Type NNC	NC25**2 to NC100**2

Installation Tools


Duct cutting tool:	DCT
Duct notching tool (hand-held tool):	DNT-100
Duct finger cutting tool:	DFCT
Nylon rivet tool:	TNR
Nylon rivets:	NR1-C NR1-M

** = Color code of LG (Light Gray), WH (White), BL (Black), IB (Intrinsic Blue)

PANDUCT® Bench Mount Wiring Duct Cutting Tool



BDCT
Front View



BDCT
Side View with
Mounting Dimensions

Dimensions are in inches [Dimensions in brackets are metric]

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.3767.7011

PANDUIT LATIN AMERICA
Jalisco, Mexico
cs-la@panduit.com
Phone: 52.333.777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of *PANDUIT* product warranties, log on to www.panduit.com/warranty



For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference WDSP01

©2007 *PANDUIT* Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.
WW-WDSP01
8/2007