

MICRO SWITCH

A DIVISION OF HONEYWELL INTERNATIONAL COMPANY

FED. MFR. CODE 91929

SWITCH — BASIC

CATALOG LISTING

BZ-RW922-A2

S

M BZ-RW922-A2

DRAWING
NUMBER

2

5

3

4

REVISIONS

A	CO17714	L. E. B.	21 MAY 63
B	CO30688	D. B. W.	24 MAY 72
C	CO-73287-J	J. A. L.	22 NOV 93
D	CO-77588	MAM	29 MAR 94

REPLACES

RELEASE NO. SR6481

23 JULY 57

FT

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57


23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57

23 JULY 57



3X 6-32 UNC X (219)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER

NOTE -

- 1 - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA. ON 1.000 ± .002 CENTERS
- 2 - PLASTIC PARTS ARE MADE OF MINERAL FILLED PHENOLICS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ——— 12 OZ. MAX.
RELEASE FORCE ——— 4 OZ. MIN.
DIFFERENTIAL TRAVEL ——— .0005 — .0010
OVERTRAVEL ——— .100 MIN.

ELECTRICAL DATA

CONTACT ARRANGEMENT
S. P. D. T.
UNDERWRITERS' LAB. INC. LISTED RATING
10A - 125, 250 OR 480 VAC
1/8HP - 125 VAC; 1/4HP - 250 VAC

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.4) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT

