



LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
G	86				V	REV PER 0G3A-0561-01	08OCT02	JR



1 CIRCULAR MIL AREA RANGE: 375-450 MCM
2 TIN PL 0.00381 [.000150] MIN THK PER MIL-T-10727



NONE	326005-2
REQD	326005
SIGHT HOLE	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75		DR 03/09/90 DK SCHRUM	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
		CHK 23JAN95 MS FEHER			
FINISH 2	APPD 23JAN95 WJ VOCKROTH	NAME TERMINAL, AMPPOWER TM WIRE SIZE: 400 MCM			
	APPD 23JAN95 TL SHUTTER				
	PRODUCT SPEC 108-30200				
	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO 326005	
	WEIGHT .226 LB	SCALE 2:1		SHEET 1 OF 1	

