

RRE48 225x63R P/N C16-B0





Substitute for Y43-16

Voltage	Frequency	Current	Airflow	Speed rotation	Noise level	Rotation direction	Operating temperature	ErP 2013	ErP 2015
V	Hz	A	m³/h	RPM	dBA	↻	Min / Max		
48	50	2,36	-	1 245	68	R	-20°C / +70°C	NA	NA
48			732 CFM				-4°F / +158°F		



dBa : free let out

NA : Not Applicable



CE

Inlet cone

16214

- Weight : 1,5 Kg
- Nominal voltage 48VDC (36-57VDC)
- Reverse polarity protection
- Soft start
- Locked rotor protection
- Tachometer output (open collector)
- Controlled by 0-10VDC or PWM signal
- IP44 protection depending on installation and position as per EN60034-5
- G2.5 balancing
- Rotor : black paint
- PA 6/6 UL 94 V-0 plastic impeller
- Once the main power is switched on, 2 to 20 seconds are necessary for initialisation before fan rotation.

