

SEMELAB

Type No.	Reliability Option	Polarity	Package	V _{CEO}	I _C cont	h _{FE} @	V _{CE} /I _C	f _T	P _D
2N6384	SCREEN	NPN	TO3	60	10	1k-20k	3/5	20M	100
2N6385	SCREEN	NPN	TO3	80	10	1k-20k	3/5	20M	100
2N6386		NPN	TO220	40	8	1k-20k	3/3	20M	40
2N6387		NPN	TO220	60	10	1k-20k	3/5	20M	40
2N6388		NPN	TO220	80	10	1k-20k	3/5	20M	40
2N6394	HI-REL	NPN *	TO66	60	4	750-18k	3/2	4M	50
2N6395	HI-REL	NPN *	TO66	80	4	750-18k	3/2	4M	50
2N6396		NPNP	TO220	200	7.6		SCR		
2N6399		NPNP	TO220	800	7.6		SCR		
2N6406		PNP		60	2	50-250	2/0.1	50M	12
2N6407		PNP		80	2	50-250	2/0.1	50M	12
2N6408		NPN		60	2	50-250	2/0.1	50M	12
2N6409		NPN		80	2	50-250	2/0.1	50M	12
2N6413		NPN		60	4	40-250	3/0.2	50M	15
2N6414		PNP		40	4	40-250	3/0.2	50M	15
2N6415		PNP		60	4	40-250	3/0.2	50M	15
2N6422	HI-REL	PNP	TO66	300	2	8-80	2/1	10M	35
2N6423	HI-REL	PNP *	TO66	300	2	10-100	2/0.75	15M	35
2N6424	HI-REL	PNP *	TO66	225	0.25	40-200	10/0.1	10M	20
2N6425	HI-REL	PNP *	TO66	300	0.25	40-200	10/0.1	10M	20
2N6436	SCREEN	PNP	TO3	80	25	20-80	2/10	40M	200
2N6437	SCREEN	PNP	TO3	100	25	20-80	2/10	40M	200
2N6438	SCREEN	PNP	TO3	120	25	20-80	2/10	40M	200
2N6461	SCREEN	NPN	TO39	300	0.1	30-120	10/20m	200M	1
2N6462	SCREEN	NPN	TO39	300	0.1	100-300	10/20m	200M	1
2N6463	SCREEN	NPN	TO39	250	0.1	30-120	10/20m	200M	1
2N6464	SCREEN	NPN	TO39	250	0.1	100-300	10/20m	200M	1
2N6465	HI-REL	NPN	TO66	110	4	15-150	4/1.5	5M	23
2N6466	HI-REL	NPN	TO66	130	4	15-150	4/1.5	5M	23
2N6467	HI-REL	PNP	TO66	110	4	15-150	4/1.5	5M	23
2N6468	HI-REL	PNP	TO66	130	4	15-150	4/1.5	5M	23
2N6469	SCREEN	PNP	TO3	50	15	20-150	4/5	10M	71
2N6473		NPN	TO220	110	4	15-150	4/1.5	4M	16
2N6474		NPN	TO220	130	4	15-150	4/1.5	4M	16
2N6475		PNP	TO220	110	4	15-150	4/1.5	4M	16
2N6476		PNP	TO220	130	4	15-150	4/1.5	4M	16
2N6477		NPN	TO220	80	7	20-100	4/2.5	2.5M	50
2N6478		NPN	TO220	160	7	20-100	4/2.5	2.5M	50
2N6486		NPN	TO220	50	15	20-150	4/5	5M	30
2N6487		NPN	TO220	70	15	20-150	4/5	5M	30
2N6488		NPN	TO220	90	15	20-150	4/5	5M	30
2N6489		PNP	TO220	50	15	20-150	4/5	5M	30
2N6490		PNP	TO220	70	15	20-150	4/5	5M	30
2N6491		PNP	TO220	90	15	20-150	4/5	5M	30
2N6496	SCREEN	NPN	TO3	130	15	12-100	2/8	60M	80

* Die available to meet this electrical specification