

Cable Gland *Standard Straight-Through - Stainless Steel*

Material:

- Body: Stainless Steel 1.4404 / INOX 316L
- Seal: Neoprene
- Clamping insert: Polyamide 6
- Sealing ring for outer thread: Nitril

Technical properties:

- Seal rings included
- Maximum strain relief through clamp range
- Gas tight- and watertight



Metric Thread


M 12 x 1.5	1.5-5	4220860	100
M 12 x 1.5	4.5-6.5	4220850	100
M 16 x 1.5	2.5-7	4220861	50
M 16 x 1.5	5-9.5	4220851	50
M 20 x 1.5	4-10	4220862	50
M 20 x 1.5	8-13	4220852	50
M 25 x 1.5	5-13	4220863	25
M 25 x 1.5	9-16	4220853	25
M 32 x 1.5	7-17	4220864	20
M 32 x 1.5	12-21	4220854	20
M 40 x 1.5	10-22	4220865	10
M 40 x 1.5	16-27	4220855	10
M 50 x 1.5	17-29	4220866	5
M 50 x 1.5	23-35	4220856	5
M 63 x 1.5	28-40	4220867	5
M 63 x 1.5	36-48	4220857	5

PROTECTION
IP68
RATING

Temperature Range

-25 to 100°C
(-13 to 212°F)

Thread Size	H mm	E mm	Dimensions			ØP mm	ØThread mm
			L mm	ØC mm			
M12x1.5	14	5	25	6.6		6.6	12
M16x1.5	17	5	28	9.7		10	16
M20x1.5	22	6	32	13.2		13.5	20
M25x1.5	27	7	35	16.2		16.5	25
M32x1.5	34	8	38	21.5		22	32
M40x1.5	42	8	41	27.5		28	40
M50x1.5	55	9	46	35.5		36	50
M63x1.5	65	10	54	48.5		50	63



Locknuts sold separately, see page 24.