



## Part Number: 130040-0010

Mini-Change® A-Size Single-Ended Cordset, Female-Pigtail, Straight, 4 Poles, Length 0.50m, Nickel (Ni) Plated Brass Shell, PVC Wire Leads

Image not available

Status:	<b>OBsolete</b>
Replacement:	Contact Molex
Series:	<a href="#">130040</a>
Category:	Industrial Cordsets
Overview:	<a href="#">Brad® Mini-Change® Products</a>
Old Part Number:	@1R4000A42M005

Series image - Reference only

## Product Environmental Compliance

[EU RoHS](#): RoHS Compliant by Exemption

[China RoHS](#):

[REACH SVHC](#): Not Reviewed

[Low-Halogen Status](#): Not Reviewed

## Part Detail

### General

Status	<b>Obsolete</b>
Category	Industrial Cordsets
Series	<a href="#">130040</a>
Comments	A-Size (7/8" - 16 UN-2A)
Connector End A	Mini-Change®
Connector End B	Pigtail
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	<a href="#">Brad® Mini-Change® Products</a>
Product Name	Mini-Change®
Type	Single Ended
UPC	78172504949

### Physical

Cable Diameter	N/A
Cable Length	0.50m
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	18
Wire/Cable Type	N/A

### Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	7A
Voltage - Maximum	300V

### Material Info

Old Part Number	@1R4000A42M005
-----------------	----------------

**Reference - Drawing Numbers**

Sales Drawing

SD-130040-001

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)