

UNPUBLISHED COPY NOT TO BE
REPRODUCED NOR PUBLISHED
WITHOUT WRITTEN PERMISSION
OF AMP INCORPORATED.

PRODUCT WITHOUT WRITTEN AMP INCORPORATED.

400 MAX. 187

56

55

110

"B"

"A"


✓ SPIROL PIN(TYP)
AMP PART NO 88234-3

6-32 UNC
DOUBLE LEAD.

__RIMP-SNAP CONTACT P/N 530750#22-26 AWG.
(ORDERED SEPARATELY)

- HOUSING MAT'L: GLASS FILLED POLYESTER
COLOR- BLUE

SECT. A-A



4. OBS PART NO.

AMP 1471-6 (7-73)

CUSTOMER DRAWING

AWING MADE IN THIRD ANGLE PROJECTION

© COPYRIGHT 1977 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

UNPUBLISHED COPY NOT
REPRODUCED FOR PUBLICATION
WITHOUT WRITTEN PERMISSION
OF AMP INCORPORATED.

LCC		DIST	
DF		FO	
REVISIONS			
ZONE	LTR	DESCRIPTION	DATE
SEE SHEET 1			APPROVED

M55302/113-87	M	M	1/56	55/110	5.400	54	6.065	6.355	3-530752-6
-86	M	F	↑	↑	↑	↑	↑	↑	3- -5
-85	F	M	↓	↓	↓	↓	↓	↓	3- -4
-84	F	F	1/56	55/110	5.400	54	6.065	6.355	3- -3
-79	M	M	1/51	50/100	4.900	49	5.565	5.855	3- -2
-78	M	F	↑	↑	↑	↑	↑	↑	3- -1
-77	F	M	↓	↓	↓	↓	↓	↓	3- -0
-76	F	F	1/51	50/100	4.900	49	5.565	5.855	2- -9
-71	M	M	1/46	45/90	4.400	44	5.065	5.355	2- -8
-70	M	F	↑	↑	↑	↑	↑	↑	2- -7
-69	F	M	↓	↓	↓	↓	↓	↓	2- -6
-68	F	F	1/46	45/90	4.400	44	5.065	5.355	2- -5
-63	M	M	1/41	40/80	3.900	39	4.565	4.855	2- -4
-62	M	F	↑	↑	↑	↑	↑	↑	2- -3
-61	F	M	↓	↓	↓	↓	↓	↓	2- -2
-60	F	F	1/41	40/80	3.900	39	4.565	4.855	2- -1
-55	M	M	1/31	30/60	2.900	29	3.565	3.855	2- -0
-54	M	F	↑	↑	↑	↑	↑	↑	1- -9
-53	F	M	↓	↓	↓	↓	↓	↓	1- -8
-52	F	F	1/31	30/60	2.900	29	3.565	3.855	1- -7
-47	M	M	1/26	25/50	2.400	24	3.065	3.355	1- -6
-46	M	F	↑	↑	↑	↑	↑	↑	1- -5
-45	F	M	↓	↓	↓	↓	↓	↓	1- -4
-44	F	F	1/26	25/50	2.400	24	3.065	3.355	1- -3
-39	M	M	1/21	20/40	1.900	19	2.565	2.855	1- -2
-38	M	F	↑	↑	↑	↑	↑	↑	1- -1
-37	F	M	↓	↓	↓	↓	↓	↓	1- -0
-36	F	F	1/21	20/40	1.900	19	2.565	2.855	-9
-31	M	M	1/16	15/30	1.400	14	2.065	2.355	-8
-30	M	F	↑	↑	↑	↑	↑	↑	-7
-29	F	M	↓	↓	↓	↓	↓	↓	-6
-28	F	F	1/16	15/30	1.400	14	2.065	2.355	-5
-10	M	M	1/36	35/70	3.400	34	4.065	4.355	-4
-09	M	F	↑	↑	↑	↑	↑	↑	-3
-08	F	M	↓	↓	↓	↓	↓	↓	-2
M55302/113-07	F	F	1/36	35/70	3.400	34	4.065	4.355	530752-1
MILITARY PART NO.	GROOVE	TONGUE	KEYING	CAVITY IDENT.	D	C	B	A	ASSEMBLY PART NO.

UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.
TOLERANCES ON:
DECIMALS ±
ANGLES ±

MATERIAL

FINISH

CONTRACT NO

DR
M. Smith 7-11-77
CHK

APPD
K. Williams 7-12-77

APPD
K. Shaw 7-13-77

DSGN APPD

OTHER APPD

AMP INCORPORATED
Harrisburg, Pa.

NAME
PIN HEADER HOUSING ASSY.
FOR CRIMP-SNAP BOX PIN
CONTACTS.

SIZE	CODE IDENT NO	DRAWING NO	REV
C	00779	530752	F
SCALE			SHEET 2 OF 2

CUSTOMER DRAWING