


Shellsize	A	B	C	ØD	E	F	G ^{1/3}	Cable Ø	Part-N0.
1	40.76	25.0	SW 22	24.6	51.0	22.0	77.0	5 - 10	165X14869X
2	49.06	33.3	SW 24	26.5	51.0	22.0	79.0	6 - 12	165X14879X
3	62.80	47.04	SW 24	26.5	59.5	22.0	87.5	6 - 12	165X14889X
4	78.86	63.5	SW 33	36.2	67.0	22.0	99.0	9 - 16	165X14899X
5	76.46	61.1	SW 42	47.0	67.0	24.8	107.0	13 - 20	165X14909X

Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		dim. in mm
2004	date	
drawn	25.11.	name
appd.	25.11.	Mickenbecker
norm		
d-old		

scale:	1:1
material:	SEE NOTES
WATER RESISTANT D-SUB HOOD 9-50pos. with short screw	
dwg no:	AutoCAD 2004
16K1A1289	
part no:	SEE TABLE
DIN-A	3
sh:	1/1

used for: D-SUB



SHORT SCREW
INCL. WASHER AND O-RING