





m/m

CONTACT
POINT



FEATURES

Double tuning fork type contact guarantees high reliability.
2.0MM pitch Low-Profile mini type Match to 0.50mm sq. posts.

MATERIAL

.InsulatorP.B.T.(UL 94v-0)
.ContactGold Plated
.Terminal5191 Phosphor Bronze

SPECIFICATIONS

.Current Rating: 3 amperes MAX
.Contact Resistance: 30m Ω MAX
.Insulation Resistance: 1000 megohms MAX
.Dielectric Withstanding Voltage: AC 650 volts RMS at sea level

* TOLERANCE:
INSULATOR: ± 0.15
TERMINAL: ± 0.05

RoHS Compliant		HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准	SCALE 比例	TOLERANCE 容許公差	PART NAME 品名
DWG. 製圖	UNIT 單位	SIZE 紙張尺寸	2.0mm MINI JUMPER 2P H:5.0mm
DATE 制表日	PAGE 張數	REV. 版次	CLOSE TYPE GOLD PLATING BLACK
2010/2/12	1 OF 1	A	COLOR ROHS LOW-LEAD
		PART NO.	料號
		C9700-02CBGB00R	