


SWITCHES STANDARD TOGGLE

SPECIFICATIONS:

Current Rating:		15A @ 125V AC, 10A @ 250V AC			
Insulation Resistance:		100 Meg ohms			
Dielectric Strength:		1000V (min.)			
Base Material:		Phenolic			
Actuator & Bushing Material:		Brass/Nickel Plate			
Terminal Type:		Screw (#6-32 NC-2 Thread)			
Part No.	Type	Action			Actuator
30-10243	4PDT	ON	OFF	ON	Metal
30-10245	4PDT	ON	-	OFF	Metal
30-10376	4PDT	ON	-	ON	Metal


HEAVY DUTY BAT HANDLE TOGGLE SWITCHES - 4PDT



SEALED HEAVY DUTY BAT HANDLE TOGGLE SWITCHES SPDT, TWO CIRCUIT


SPECIFICATIONS:

Current Rating:		20A @ 125V AC, 10A @ 277V AC 21A @ 12-14V DC,			
Initial Contact Resistance:		50 Meg ohm (Max.)			
Insulation Resistance:		100 Meg ohm (Min.) @ 500 V DC			
Dielectric Strength:		1,000V AC for (Min)			
Base Material:		Phenolic			
Actuator & Bushing:		Brass Nickle Plated			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-3050	SPST	ON	-	OFF	Metal
30-3057	DPST	ON	-	OFF	Metal



HEAVY DUTY BAT HANDLE TOGGLE SWITCH SPDT, TWO CIRCUIT

Current Rating:		15A @ 125V AC, 10A @ 250V AC 3/4 HP @ 125-250V AC,			
Initial Contact Resistance:		50 Meg ohm (Max.)			
Insulation Resistance:		100 Meg ohm (Min.)			
Dielectric Strength:		1,000V for (Min)			
Base Material:		Phenolic			
Actuator & Bushing:		Brass Nickle Plated			
Terminal Type:		.250" Quick Connect			
Part No.	Type	Action			Actuator
30-340	SPDT	(ON)	ON	OFF	Metal



TOGGLE SWITCH SAFETY GUARD


Features
Rugged Spring-loaded Design
Black Steel Base w/ Red urea Plastic Cover
Fits ALL Metal Lever toggles w/ 15/32 X 32 Bushing

Part No. 30-1250



TOGGLE SWITCH BOOT

Rubber Boot
Thread Size: 15/32-32



Part No. 30-1320