





$\phi .125$
3.2
(4 PLCS)

.XXX = in
XX.X = mm (REF)

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₁	REVISED	6/17/96	6/24/96

HOUSING	BRASS PER ASTM-B-16 , HALF HARD		NICKEL PLATE QQ-N-290		
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457		N/A		
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197 , ALLOY C17300 , CONDITION H		GOLD PLATE PER MIL-G-45204		
COMPONENT		MATERIAL		FINISH	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		DRAWN BY K.L.	DATE 8-3-71	 <i>AMP Incorporated</i> 140 Fourth Avenue Waltham, MA 02451-7599	
FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		CHECKED BY P.R.B.	8-3-71		
		APPD BY B.W.C.	8-3-71		
These drawings and speci- fications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale o f item(s) without written permission.		USE ASSY PROCEDURE NO. A.P. <u>N/A</u>		TITLE "BNC" FLANGE MOUNT JACK RECEPTACLE - STRAIGHT TERMINAL	
		SIZE B	CODE IDENT NO. 26805	3252-1201-10	REV 01 ₁
		SCALE 4:1			SHEET 1 OF 1

NOTES:
1. CAPTURED CENTER CONTACT

CUSTOMER DRAWING

AMP PART # 1058016-1
SHEET 1 OF 1 REV A