





Speaker Jack

151-0300-E

KOBI CONN

Speaker Jack



Dimensions: In.

SPECIFICATIONS

Type:	PCB Mount, Printed Circuit
Contact Resistance:	30mΩ max.
Insulation Resistance:	100MΩ min.
Dielectric Strength:	500VAC (50/60Hz) for 1 Minute
Temperature Increase:	30°C max. (DC 4A)
Lead Wire Holding Force:	.5Kg min.
Knob Handling Force:	3KG max.
Insertion Hole:	2mm min.
Terminal Strength:	3Kg max.
RoHS Compliant	

MATERIALS

Body:	ABS Plastic
Contacts:	Tin Plated
Buttons:	Color Coded (Black & Red)

Date Last Revised: 8-23-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-301047

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[151-0300-E](#)