






PRINT DIST. DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

NUMBER C-174681
METRIC
3-2 ANGLE PROJECTION



NOTES,

- 1 MATERIAL AND FINISH
PLUG HOUSING
THERMOPLASTIC (UL94V-0) COLOR: BLACK
REC. CONTACT
PHOS-BRONZE FINISH: OVER NICKEL
MATING END: 0.0002 MIN. OR 0.00075 MIN. GOLD
TERMINATION END: TIN-LEAD OVER SEALING TREATMENT.
- 2 P.C.B LAYOUT AND P.C.B TREATMENT (REF.)
USE A P.C.B SURFACE ARE TREATED WITH SOLDER RESIST.



3 KINK POSITIONS (4 POSITIONS)

Au PL. 0.00075 MIN.	96	49	59.69	63.86	71.00	47	96	6-174681-8
	68	35	41.91	46.08	53.22	33	68	6-174681-7
	48	25	29.21	33.38	40.52	23	48	6-174681-6
	34	18	20.32	24.49	31.63	16	34	6-174681-5
Au PL. 0.0002 MIN.	96	49	59.69	63.86	71.00	47	96	174681-8
	68	35	41.91	46.08	53.22	33	68	174681-7
	48	25	29.21	33.38	40.52	23	48	174681-6
	34	18	20.32	24.49	31.63	16	34	174681-5
REMARK	CIRCUIT NO.	DIMENSION	n	POS.	PART NO.			

B REVISED ECN: J-1347 Y.S. R/V 7/19		WIRE RANGE		INSULATION DIA		NAME	
A ADD Au 0.75 3-10-88 Y.S. R/V 1/88		MATERIAL		FINISH		① PLUG ASS, Y VERTICAL (W/KINK)	
O ECN: J-10187 Y.S. R/V 1/88		DR. Y.G. SATO 12/23/87 DE.		APP. T. SATO 1/23/88		② FOR AMPLITE OSO SERIES 18-TO-B CONN.	
LTR REVISION RECORD		DR CHK DATE		CHK. R. NISHIMURA		GENERAL TOLERANCE	
						0-10 10 30 100	
						0.25 0.25 0.25 0.25	
						ANGLES 25°	
						SIZE LOC NUMBER	
						A3 J C-174681	
						SCALE 2-1 REV. B SHEET 10F1	

CUSTOMER DRAWING

REV. 10-88