




10° TYP.

MATING FACE

RAISED CAVITY IDENTIFICATION

3,0 DIA. TYP.

7,9

2,5R.TYP.

33,3

39,1

9

18

26

10

19

NOTES:

1 THIS RECEPTACLE ACCEPTS SIZE 22 REC. CONTACTS.

2 RETENTION TINES ARE AN INTEGRAL PART OF INSERT.

3 CONTACT INSERTION/REMOVAL TOOL TE P.N. 91285-1 IS RECOMMENDED FOR USE WITH THESE CONNECTORS:

0,8

10,9 MAX.

24,7

FRONT SHELL
STEEL,BRIGHT TINPLATED.

REAR SHELL,STEEL
BRIGHT TINPLATED.

TE DATE CODE
TE PARTNO.
INK STAMPED

27,5

6,2

10,9

10,7

12,5

INSERTS:NYLON
GLASS-FILLED
SELF-EXTINGUISHING
COLOR: BLACK

CLINCH
SECTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

WIRE RANGE -

INSUL.RANGE -

DWN J.V.D.HEIJDEN. 07-12-88

CHK C.v.TILBURG. 02-01-89

APVD L.v.SOEST. 04-01-89

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

SEE DRAWING

FINISH

SEE DRAWING

MATERIAL

216165-1

PARTNUMBER

STE TE Connectivity

NAME

HDP-22 REC. CONNECTOR,
SIZE 2, (26 POSITION)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-216165

SCALE

NTS

SHEET

1 OF 1

REV

B