

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.





All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
55308-XXX

PLATING OPTION
3= 0.76 µm GOLD
5= 1.27 µm GOLD


HOLD DOWN OPTION
1= OUTSIDE
2= INSIDE

TERMINAL LOADING
1 = FULLY LOADED 6 POS
2 = ONLY POS 2.3.4.5 LOADED
3 = ONLY POS 1.2.5.6 LOADED






RECOMMENDED PIPET
SCALE 2

INSIDE VERSION



OUTSIDE VERSION




REFERENCE PLAN
DEFINED BY THE
BEARING SURFACE

NOTES:

- 1 - MATERIAL: HOUSING: HIGH TEMP. PLASTIC, COLOR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE
SOLDER TAIL: 90/10 SnPb 2 µm MIN.
NO RAW EDGES EXCEPT SOLDER TAIL TIPS.
- 3 - PACKAGING IN TAPE & REEL SEE TA858.
- 4 - DIMENSION MEASURED FROM "B" TO THE TOP OF PRODUCT
- 5 - RECOMMENDED VACCUM PIPET

A FCI www.fciconnect.com			surface - ✓ ISO 1302		tolerance ±0.13 ±2 °		projection 		mm 	
Dr	D LEGRAND	02.05.23	Product family			MODULAR JACK			size	Scale
Eng	F TISSERAND	02.05.23	Spec ref						A3	5:2
Chr	F TISSERAND	02.05.23	Material			SEE NOTES			ECN	F20562
Appr	F TISSERAND	02.05.23								
title	HORIZONTAL L.P. SMT					dwg no		55308		Rev.
	6 POSITIONS									
catalog no					SEE TABLE		CUSTOMER COPY			sheet 1 of 2

ltr	ecn no	dr	date
D	F20300	DLE	02.04.23
E	F20520	DLE	02.09.06
F	F20562	BLE	02.10.16
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.




A

B

C


D


RECOMMENDED PCB FOOT PRINT
FOR 6 POSITIONS OUTSIDE



RECOMMENDED PANEL CUTOUT

RECOMMENDED PCB FOOT PRINT
FOR 6 POSITIONS INSIDE



 www.fciconnect.com			surface 	tolerance ±0.13 ±2°	projection 	mm 
Dr	D LEGRAND	02.05.23	Product family	MODULAR JACK	size A3	Scale 5:1
Eng	F TISSERAND	02.05.23	Spec ref			
Chr	F TISSERAND	02.05.23	Material	SEE NOTES	ECN	F20562
Appr	F TISSERAND	02.05.23				
title HORIZONTAL L.P. SMT 6 POSITIONS				dwg no 55308		Rev. F
catalog no SEE TABLE				CUSTOMER COPY		sheet 2 of 2