

EAO – Your Expert Partner for Human Machine Interfaces

10-2H12.314B - Bi-colour LED

10-2H12.314B - Bi-colour LED



Attention: The preview is based on a sample product. This can differ from your current configuration.

Other Attributes

Weight	0.002 kg
Operation current	15 mA $\pm$ 15 %
Operating voltage	24 V DC +10 %

Illumination

Socket	BA9s
LED colour	Bi-colour LED red/yellow


Optics

Lumi. intensity	1200/550 mcd
Dom. wavelength	625/589 nm

EAO – Your Expert Partner for Human Machine Interfaces

10-2H12.314B - Bi-colour LED

Dimensions



Additional information

The max. overall length of the lamp may not exceed 25mm

Electrical and optical data are measured at 25 °C

The specified 6 VDC, 24 VDC Bi-colour; 130 VAC, 130 DC und 230 VAC versions are built with a protection diode

If the 24VDC Bi-colour lamp is driven with normal polarity (plus on middle contact of the lamp) the first mentioned colour will light up, with inverted polarity the second colour will light up

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination