

FLEX STACK

(2.54 mm) .100"

TLW-118-06-T-D

MTLW-130-05-G-S-110


TLW, MTLW SERIES

LOW-PROFILE .025" SQ POST HEADERS

Board Mates:
BSW, CES, SLW, HLE


FEATURES

These headers provide the ultimate low-profile (0.64 mm) .025" square post board stacking system. The high quality Phosphor Bronze terminals are available with a standard short post height (TLW Series) for mating with low-profile sockets, or the post height can be Modified (MTLW Series) to accommodate IDC assemblies and other applications.




TLW - **1** **NO. PINS PER ROW**

01 thru 40
= Single Row




01 thru 36
= Double Row



LEAD STYLE

Specify
LEAD STYLE
from chart



LEAD STYLE	A	C
-01	N/A	(5.84) .230
-05	(4.32) .170	(2.67) .105
-06	(3.43) .135	(2.67) .105

PLATING OPTION

-F
= Gold flash on post, Matte Tin on tail

-G
= 10 μ" (0.25 μm) Gold on post, Gold flash on tail

-T
= Matte Tin

ROW OPTION

-S
= Single Row

-D
= Double Row

OTHER OPTION

-RA
= Right-angle
(-01 Lead Style only)

-“XX”
= Polarized Position
Specify position for omitted pin.

ALSO AVAILABLE
(MOQ Required)

- Other platings

SPECIFICATIONS

For complete specifications see www.samtec.com?TLW or www.samtec.com?MTLW

Insulator Material: Black Liquid Crystal Polymer
Terminal Material: Phosphor Bronze
Plating: Au or Sn over 50 μ" (1.27 μm) Ni

Current Rating (TLW/SLW): 5.2 A per pin (2 pins powered)
Operating Temp Range: -55 °C to +105 °C with Tin
-55 °C to +125 °C with Gold

RoHS Compliant: Yes
Lead-Free Solderable: Yes

RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality




Note:
Some lengths, styles and options are non-standard, non-returnable. MTLW Series is non-standard, non-returnable.

MTLW - **1** **NO. PINS PER ROW**

01 thru 40
= Single Row




01 thru 36
= Double Row



LEAD STYLE

Specify
LEAD STYLE
from chart



LEAD STYLE	OAL
-05	(8.51) .335
-06	(7.62) .300
-07	(10.92) .430
-08	(13.46) .530
-09	(18.54) .730
-10	(21.08) .830
-22	(16.00) .630
-23	(11.30) .445
-24	(12.19) .480

PLATING OPTION

-S
= Single Row

-D
= Double Row

ROW OPTION

-S
= Single Row

-D
= Double Row

POST HEIGHT

-“XXX”
= Post Height Dimension (In inches)

-F
= Gold flash on post, Matte Tin on tail

-L
= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail

-G
= 10 μ" (0.25 μm) Gold on post, Gold flash on tail

-T
= Matte Tin

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.