


2 and 3-Wire Cordsets, Standard

- NEMA 1, 3, 4, 6P
- IEC IP67 Protection
- 300 V, 9 A



Connector Style	Female Part Number	Male Part Number	Features	Pinout
RKM ..**	RKM 20- *M WKM 20- *M	RSM 20- *M WSM 20- *M	AWM PVC Yellow 2x18 AWG, 105°C, 7.2 mm OD, Cable #RF50511-*M†, flexlife®	Female Male
WKM ..**	RKM 30-*M WKM 30-*M	RSM 30-*M WSM 30-*M	AWM PVC Yellow, 3x18 AWG, 105°C, 7.2 mm OD, Cable #RF50512-*M†, flexlife	Female
RSM ..**	RKM 30-*M/S90 WKM 30-*M/S90	RSM 30-*M/S90 WSM 30-*M/S90	AWM TPU Yellow, 3x18 AWG, 90°C, 7.2 mm OD, Cable #RF50545-*M†, Cut Abrasion Immune	
RSM ..**	RKM 30-*M/S101 WKM 30-*M/S101	RSM 30-*M/S101 WSM 30-*M/S101	AWM TPE Yellow, 3x18 AWG, 105°C, 5.9 mm OD, Cable #RF51173-*M†, flexlife-20, high flex over 20 million cycles	
WSM ..**	RKM 311-*M WKM 311-*M	RSM 311-*M WSM 311-*M	AWM PVC Yellow, 3x18 AWG, 105°C, 7.2 mm OD, Cable #RF50520-*M†, flexlife	Male
WSM ..**	RKM 311-*M/S600 WKM 311-*M/S600	RSM 311-*M/S600 WSM 311-*M/S600	SJOOW CPE, Yellow, 3x18 AWG, 105°C, 8.0 mm OD, Cable #RF50658-*M†, Weld Flash Immune, Flame Immune	

* Length in Meters. Standard cable lengths are 2, 4, 5, 6, 8 and 10 meters. Consult factory for other lengths.

** Standard coupling nut material is nickel plated brass "RKM .."; "RK .." indicates nylon, "RKV .." indicates stainless steel, and "RKVH .." indicates stainless steel hex.

† See Section N for **reelfast**® cable information.