




MXL Rubber Timing Belts

0.080" (2.032mm) pitch



Rubber back/teeth, glass fibre
reinforced, nylon fabric tooth
facing to DIN / ISO 5296

RS Stock Number	Width (in.)	Width (mm)	Length (in.)	Length (mm)	No. Teeth
7785039	0.25" (1/4)	6	4.56	115.82	57
7785032	0.25" (1/4)	6	4.80	121.92	60
7785036	0.25" (1/4)	6	5.36	136.14	67
7785045	0.25" (1/4)	6	6.40	162.56	80
7785048	0.25" (1/4)	6	6.80	172.72	85
7785042	0.25" (1/4)	6	7.20	182.88	90
7785051	0.25" (1/4)	6	7.52	191.01	94
7785054	0.25" (1/4)	6	7.60	193.04	95
7785058	0.25" (1/4)	6	8.00	203.20	100
7785067	0.25" (1/4)	6	8.24	209.30	103
7785060	0.25" (1/4)	6	8.40	213.36	105
7785064	0.25" (1/4)	6	9.12	231.65	114
7785073	0.25" (1/4)	6	9.20	233.68	115
7785076	0.25" (1/4)	6	10.08	256.03	126
7785070	0.25" (1/4)	6	10.40	264.16	130
7785089	0.25" (1/4)	6	12.00	304.80	150
7785082	0.25" (1/4)	6	12.80	325.12	160
7785086	0.25" (1/4)	6	13.20	335.28	165
7785095	0.25" (1/4)	6	15.20	386.08	190

7785098	0.25" (1/4)	6	16.00	406.40	200
7785092	0.25" (1/4)	6	20.48	520.19	256
7785102	0.25" (1/4)	6	25.20	640.08	315