



Inductor

Order code	TCK-116
Inductance	10 μ H $\pm$ 20% (100 kHz / 250 mV)
Rated current	2.3 A max.
DCR	200 m Ω
Operating temperature	-40 to +125°C

Impedance curve



Dimensions [mm]

A	5.4 max.
B	4.7 $\pm$ 0.3
C	2.2 max.
D	2.0 $\pm$ 0.3
E	1.0 $\pm$ 0.3
F	2.5
G	3.0
H	7.0