






ORDER NUMBER	NUMBER OF POSITIONS	"L" MAX.	
		MM.	INCH.
5164897-2	2	5,0	.197
1 OBSOLETE	3	7,5	.295
	4	10,0	.394
1 OBSOLETE	5	12,5	.492
	6	15,0	.591
1 OBSOLETE	7	17,5	.689
	8	20,0	.787
1 OBSOLETE	9	22,5	.886
	10	25,0	.984
1 OBSOLETE	11	27,5	1.083
	12	30,0	1.181
1 OBSOLETE	13	32,5	1.280
	14	35,0	1.378
1 OBSOLETE	15	37,5	1.476
	16	40,0	1.575
1 OBSOLETE	17	42,5	1.673
	18	45,0	1.772
1 OBSOLETE	19	47,5	1.870
	20	50,0	1.969

MATERIAL: HOUSING: P.C., 90% GLASS FILLED.

CONTACT: BRASS

PLATING: TIN OVER NICKEL BARRIER

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



A1	ECO-09-026495	28NOV09	KK	AEG
ltr	rev. rec.	date dwn	apvd	

SEE TABLE.	SEE ABOVE.	SEE ABOVE.
ORDER NO.	MATERIAL	PLATING
CUSTOMER COPY FOR REFERENCE ONLY		
DR R. Coolen	DATE 01 MAR 05	©1988 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.
CHK	DATE	
DE	DATE	WIRE-RANGE INSUL-RANGE FIRST USED
APP	DATE	SCALE N.T.S.
NAME 2-20 POS. MALE HEADER ASS'Y. RIGHT ANGLED FOR MINI MATCH INTERCONNECTION SYSTEM, PITCH: 2,5 mm.		REV A1