

RS Brand Strap and cord comparison table

Date created: 2014/1/23

Strap

RS Stock No	Stud Size	Wrist Strap Size	Image
364-7832	4mm	Adjustable	
392-163	10mm		

RS Stock No	Stud Size	Wrist Strap Size	Image
364-7848	4mm	Fixation (Small)	
364-7854	4mm	Fixation (Large)	
552-882	10mm	Fixation (Small)	
552-876	10mm	Fixation (Large)	

RS Stock No	Stud Size	Wrist Strap Size	Image
364-7876	4mm	Adjustable	
253-6769	10mm		

RS Stock No	Stud Size	Wrist Strap Size	Image
363-2925	10mm	Adjustable	

Cord

RS Stock No	Stud Size	Cord Length	Lead Resistance	Image
129-4975	10mm	115mm	0M Ω	
287-7470	10mm	180mm	1M Ω	

RS Stock No	Stud Size	Cord Length	Lead Resistance	Image
250-4116	10mm	1.8m	1M Ω	

RS Stock No	Stud Size	Cord Length	Lead Resistance	Image
364-7882	4mm-Alligator	1.8m	1M Ω	
273-6701	10mm-Alligator	1.8m	1M Ω	

RS Stock No	Stud Size	Cord Length	Lead Resistance	Image
129-4969	10mm-10mm	1m	1M Ω	
129-4874	10mm-10mm	2m	1M Ω	

RS Stock No	Stud Size	Cord Length	Lead Resistance	Image
129-4931	10mm-10mm	1m	1M Ω	
287-7486	10mm-10mm	4.5m	1M Ω	

RS Stock No	Stud Size	Cord Length	Lead Resistance	Image
552-898	10mm-Alligator	1.8m	2M Ω	
287-7391	10mm-Alligator	3.6m	2M Ω	
364-7898	10mm-4mm	1.8m	1M Ω	
273-6717	10mm-10mm	1.8m	1M Ω	
291-9489	10mm-10mm	1.8m	2M Ω	
552-905	10mm-10mm	1.8m	4M Ω	