

**MNX ABS 100/75 LG**



Sample photo

**Order symbol:** ABS 100/75 LG  
**Product nbr:** 6082303  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

|                    |               |
|--------------------|---------------|
| <b>EAN:</b>        | 6418074022783 |
| <b>El. number:</b> |               |
| Finland:           | 3420505       |
| Denmark:           | 8212023110    |
| Italy:             | 7361015       |
| Sweden:            | 2535706       |
| Norway:            |               |

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions:            |  | Length                            | Width | Height |
|------------------------|--|-----------------------------------|-------|--------|
| mm:                    |  | 130                               | 80    | 75     |
| inch:                  |  | 5.1                               | 3.1   | 3.0    |
| Materials:             |  |                                   |       |        |
| Material:              |  | ABS                               |       |        |
| Base colour:           |  | RAL 7035                          |       |        |
| Cover colour:          |  | RAL 7035                          |       |        |
| Cover screws material: |  | Polyamide                         |       |        |
| Cover screws colour:   |  | Grey                              |       |        |
| Gasket material:       |  | TPE                               |       |        |
| Temperatures:          |  |                                   |       |        |
| Short term:            |  | -40 ... 80 °C                     |       |        |
| Continuous:            |  | -40 ... 60 °C                     |       |        |
| Short term:            |  | -40 ... 175 °F                    |       |        |
| Continuous:            |  | -40 ... 140 °F                    |       |        |
| Accessories:           |  |                                   |       |        |
| MIV 100                |  | Mounting plate (Galvanized steel) |       |        |
| MIN 5                  |  | DIN-15 Mounting rail              |       |        |
| MIN 10                 |  | DIN-15 Mounting rail              |       |        |
| MIV 5                  |  | DIN-35 Mounting rail              |       |        |
| MIV 10                 |  | DIN-35 Mounting rail              |       |        |
| FP A 100/130           |  | Front plate (Aluminium)           |       |        |
| HFP 130                |  | Front plate hinge series          |       |        |
| FP 22046               |  | Wall fastening lug (4 pcs)        |       |        |

