




FEATURES:

- Permits BNC male to be used with equipment having Western Electric 2.3 (.090) video plugs
- Video plug equivalent to WE-090

MATERIALS:

Body and Fittings: Brass per QQ-B-626, Alloy 360, ½ Hard.

BNC Center Contact: Beryllium Copper per QQ-C-530, Cond. H.T.

Video Center Contact: Brass per QQ-B-626, Alloy 360, ½ Hard.

Finish:

Body and Fittings: Tarnish Resistant

Center Contacts: Gold plate per MIL-C-39012

Marking: POMONA ELECTRONICS 5008

RATINGS:

Operating Temperature: +102°C. (+216°F.) Max.

Operating Voltage: 500 VRMS

Nominal Impedance: 75 Ohms

ORDERING INFORMATION: Model 5008

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ± .005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Made in USA